

CHIP COILS (CHIP INDUCTORS) LQW18CN =====000 REFERENCE SPECIFICATION

1. Scope

This reference specification applies to chip coils (chip inductors) LQW18CN_00 series for general electronic equipment.

2. Part Numbering

		•							
(Ex.)									
LQ	W	18	С	N	4N9	D	0	0	D
Product	Structure	Dimension	Application	Category	Inductance	Tolerance	Performance	Electrode	Packaging
ID		$(L \times W)$	and					specification	D: taping
			characteristic						*B: bulk

^{*}B: Bulk packing is also available (taping condition: however, products without reels are put in plastic bags).

3. Part Number and Rating


Operating temperature range	-40°C to +85°C
Storage temperature range	-40°C to +85°C

		Inductance			Self-resonant	
Customer Part number	Murata Part number	Nominal value (nH)	Tolerance	DC resistance (Ω max.)	frequency (MHz min.)	Rated current (mA)
	LQW18CN4N9D00D	4.9	D: ±0.5 nH	0.015	2300	2600
	LQW18CN15NJ00D	15	J: ±5%	0.025	2000	2200
	LQW18CN33NJ00D	33	J: ±5%	0.035	1800	1700
	LQW18CN55NJ00D	55	J: ±5%	0.045	1600	1500
	LQW18CN85NJ00D	85	J: ±5%	0.060	1380	1400
	LQW18CNR10K00D	100	K: ±10%	0.10	1260	1000
	LQW18CNR12J00D	120	J: ±5%	0.085	1200	1100
	LQW18CNR16J00D	160	J: ±5%	0.10	900	1000
	LQW18CNR21J00D	210	J: ±5%	0.15	720	800
	LQW18CNR27J00D	270	J: ±5%	0.16	660	750
	LQW18CNR33J00D	330	J: ±5%	0.25	600	630
	LQW18CNR39J00D	390	J: ±5%	0.28	570	620
	LQW18CNR47J00D	470	J: ±5%	0.45	555	500
	LQW18CNR56J00D	560	J: ±5%	0.48	540	450
	LQW18CNR65J00D	650	J: ±5%	0.52	510	430

4. Testing Conditions

Unless otherwise specified	Temperature: ordinary temperature (15°C to 35°C) Humidity: ordinary humidity [25% to 85% (RH)]
In case of doubt	Temperature: 20°C±2°C Humidity: 60% to 70% (RH) Atmospheric pressure: 86 kPa to 106 kPa

5. Appearance and Dimensions




Unit mass (typical value): 0.004 g

6. Marking

No marking.


7. Electrical Performance

No.	Item	Specification	Test method
7.1	Inductance	Meet chapter 3 ratings.	Measuring equipment: Keysight E4991A or the equivalent Measuring frequency: Inductance: 10 MHz SRF: Frequency when L value is 0 µH Measuring conditions: Measurement signal level: Approx. 0 dBm Measurement terminal distance: 1.0 mm Electrical length: 10.0 mm Measuring fixture: Keysight 16197A Position the chip coil under test as shown in the measuring example below and connect it to the electrode by applying weight. Measurement example:
	Self-resonant frequency	Meet chapter 3 ratings.	Measuring method: see "Electrical performance: Measuring method for inductance/Q" in the chapter
7.3	DC resistance	Meet chapter 3 ratings.	"14. Appendix". Measuring equipment: digital multimeter
	Rated current	Product temperature rise: 40°C max.	Apply the rated current specified in chapter 3.



8. Mechanical Performance

No.	Item	Specification	Test method
8.1	Shear test	No significant mechanical damage or no sign of electrode peeling off shall be observed.	Test substrate: glass-epoxy substrate Force application direction: Applying force: 8 N
8.2	Ponding tost	Ne significant machanical damage or ne	Holding time: 5 s±1 s Test substrate: glass-epoxy substrate (100 mm × 40
0.2	Bending test	No significant mechanical damage or no sign of electrode peeling off shall be observed.	mm × 0.8 mm) Pressurizing speed: 1 mm/s Deflection: 2 mm Holding time: 5 s
			R230 F Deflection 45
8.3	Vibration	Appearance shall have no significant mechanical damage.	Oscillation frequency: 10 Hz to 2000 Hz to 10 Hz, for approx. 15 min Total amplitude: total amplitude of 3.0 mm or acceleration amplitude of 196 m/s², whichever is smaller Test time: 3 directions perpendicular to each other, 2 h for each direction (6 h in total)
8.4	Solderability	90% or more of the outer electrode shall be covered with new solder seamlessly.	Flux: immersed in ethanol solution [including an activator with a chlorine conversion value of 0.06(wt)%] with a rosin content of 25(wt)% for 5 s to 10 s. Solder: Sn-3.0Ag-0.5Cu solder Pre-heating: 150°C±10°C/60 s Solder temperature: 240°C±3°C Immersion time: 3 s±1 s
8.5	Resistance to soldering heat	Appearance: No significant mechanical damage shall be observed. Inductance change rate: within ±5%	Flux: immersed in ethanol solution [including an activator with a chlorine conversion value of 0.06(wt)%] with a rosin content of 25(wt)% for 5 s to 10 s. Solder: Sn-3.0Ag-0.5Cu solder Pre-heating: 150°C±10°C/60 s to 90 s Solder temperature: 270°C±5°C Immersion time: 5 s±1 s Post-treatment: left at a room condition for 24 h±2 h




9. Environmental Performance

The product is soldered on a substrate for test.

No.	Item	Specification	Test method
9.1	Heat resistance	Appearance: No significant mechanical damage shall be observed. Inductance change rate: within ±5%	Temperature: 85°C±2°C Test time: 1000 h (+48 h, -0 h) Post-treatment: left at a room condition for 24 h±2 h
9.2	Cold resistance	Appearance: No significant mechanical damage shall be observed. Inductance change rate: within ±5%	Temperature: -40°C±2°C Test time: 1000 h (+48 h, -0 h) Post-treatment: left at a room condition for 24 h±2 h
9.3	Humidity	Appearance: No significant mechanical damage shall be observed. Inductance change rate: within ±5%	Temperature: 85°C±2°C Humidity: 80% (RH) to 85% (RH) Test time: 1000 h (+48 h, -0 h) Post-treatment: left at a room condition for 24 h±2 h
9.4	Temperature cycle	Appearance: No significant mechanical damage shall be observed. Inductance change rate: within ±5%	Single cycle conditions: Step 1: -40°C±2°C/30 min±3 min Step 2: ordinary temperature/10 min to 15 min Step 3: +85°C±2°C/30 min±3 min Step 4: ordinary temperature/10 min to 15 min Number of testing: 100 cycles Post-treatment: left at a room condition for 24 h±2 h

10. Specification of Packaging

10.1 Appearance and dimensions of tape (8 mm width/paper tape)



Α	1.0±0.06	
В	1.8±0.06	
t	1.1 max.	
	(in	mm)

Direction of Feed

10.2 Taping specifications


1 0 1		
Packing quantity (Standard quantity)	4000 pcs/reel	
Packing method	The products are placed in embossed cavities of a base tape and sealed by a top tape and a bottom tape.	
Feed hole position	The feed holes on the base tape are on the right side when the top tape is pulled toward the user.	
Joint	The base tape and the top tape are seamless.	
Number of missing products	Number of missing products within 0.1% of the number per reel or 1 pc., whichever is greater, and are not continuous. The specified quantity per reel is kept.	


10.3 Break down force of tape

Break down force of top tape	5 N min.
Break down force of bottom tape	5 N min.

10.4 Peeling off force of top tape


Speed of peeling off	300 mm/min
Peeling off force	0.1 N to 0.6 N (The lower limit is for typical value.)





10.5 Dimensions of leader section, trailer section and reel

A vacant section is provided in the leader (start) section and trailer (end) section of the tape for the product. The leader section is further provided with an area consisting only of the top tape. (See the diagram below.)



10.6 Marking for reel


Customer part number, Murata part number, inspection number (*1), RoHS marking (*2), quantity, etc.

Cactomer part nambor, marata pe	art namber, inepedien namber (1), rterie marking (2), quantity, etc.
*1 Expression of inspection No.:	(1) Factory code
0000 ♦♦♦	(2) Date
(1) (2) (3)	First digit: year/last digit of year
	Second digit: month/Jan. to Sep.→1 to 9, Oct. to Dec.→O, N, D
	Third, Fourth digit: day
	(3) Serial No.
*2 Expression of RoHS marking:	(1) RoHS regulation conformity
ROHS- Y (△)	(2) Murata classification number
(1) (2)	
., (,	

10.7 Marking on outer box (corrugated box)

Customer name, purchasing order number, customer part number, Murata part number, RoHS marking (*2), quantity, etc.

10.8 Specification of outer box



Dimensions of outer box (mm)			Standard reel quantity in outer box (reel)	
W	D	Н	in outer box (reei)	
186	186	93	5	
* Above outer box size is typical. It depends on a quantity of an order.				

11. ACaution

Restricted Please contact us before using our products for the applications listed below which require especially high applications reliability for the prevention of defects which might directly cause damage to the third party's life, body or property. (1) Aircraft equipment (6) Transportation equipment (vehicles, trains, ships, etc.) (2) Aerospace equipment (7) Traffic signal equipment (3) Undersea equipment (8) Disaster/crime prevention equipment (4) Power plant control equipment (9) Data-processing equipment (5) Medical equipment (10) Applications of similar complexity and/or reliability requirements to the applications listed in the above




12. Precautions for Use

This product is for use only with reflow soldering. It is designed to be mounted by soldering. If you want to use other mounting method, for example, using a conductive adhesive, please consult us beforehand.

12.1 Land dimensions

The following diagram shows the recommended land dimensions for reflow soldering.

The land dimensions are designed in consideration of electrical characteristics and mountability. Use of other land dimensions may preclude achievement of performance. In some cases, it may result in poor solderability, including positional shift. If you use other land pattern, consider it adequately.




12.2 Flux and solder used

Flux	 Use a rosin-based flux that includes an activator with a chlorine conversion value of 0.06(wt)% to 0.1(wt)%. Do not use a highly acidic flux with a halide content exceeding 0.2(wt)% (chlorine conversion value). Do not use a water-soluble flux.
Solder	 Use Sn-3.0Ag-0.5Cu solder. Standard thickness of solder paste: 100 μm to 150 μm

If you want to use a flux other than the above, please consult our technical department.

12.3 Soldering conditions (reflow)

- Pre-heating should be in such a way that the temperature difference between solder and product surface is limited to 100°C max.
- Cooling into solvent after soldering also should be in such a way that the temperature difference is limited to 100°C max. Insufficient pre-heating may cause cracks on the product, resulting in the deterioration of product quality.
- Standard soldering profile and the limit soldering profile is as follows.
 The excessive limit soldering conditions may cause leaching of the electrode and/or resulting in the deterioration of product quality.



	Standard profile	Limit profile	
Pre-heating	150°C to 180°C/90 s±30 s 150°C to 180°C/90		
Heating	Above 220°C/30 s to 60 s	Above 230°C/60 s max.	
Peak temperature	245°C±3°C	260°C/10 s	
Number of reflow cycles	2 times	2 times	



12.4 Reworking with soldering iron


The following requirements must be met to rework a soldered product using a soldering iron.

Item	Requirement	
Pre-heating	150°C/approx. 1 min	
Tip temperature of soldering iron	350°C max.	
Power consumption of soldering iron	80 W max.	
Tip diameter of soldering iron	ø3 mm max.	
Soldering time	3 s (+1 s, -0 s)	
Number of reworking operations	2 times max.	

^{*} Avoid a direct contact of the tip of the soldering iron with the product. Such a direction contact may cause cracks in the ceramic body due to thermal shock.

12.5 Solder volume

Solder shall be used not to increase the volume too much.



An increased solder volume increases mechanical stress on the product. Exceeding solder volume may cause the failure of mechanical or electrical performance.


12.6 Product's location

The following shall be considered when designing and laying out PCBs.

(1) PCB shall be designed so that products are not subject to mechanical stress due to warping the board.

[Products direction]

Products shall be located in the sideways direction (length: a < b) to the mechanical stress.




(2) Components location on PCB separation


It is effective to implement the following measures, to reduce stress in separating the board.

It is best to implement all of the following three measures; however, implement as many measures as possible to reduce stress.

Contents of measures	Stress level	
(1) Turn the mounting direction of the component parallel to the board separation surface.	A > D*1	
(2) Add slits in the board separation part.	A > B	
(3) Keep the mounting position of the component away from the board separation surface.	A > C	
*1.4 \rightarrow D is valid when stress is added vertically to the perforation as with hand separation		

¹ A > D is valid when stress is added vertically to the perforation as with hand separation. If a cutting disc is used, stress will be diagonal to the PCB, therefore A > D is invalid.






(3) Mounting components near screw holes

When a component is mounted near a screw hole, it may be affected by the board deflection that occurs during the tightening of the screw.

Mount the component in a position as far away from the screw holes as possible.



12.7 Handling of substrate

After mounting products on a substrate, do not apply any stress to the product caused by bending or twisting to the substrate when cropping the substrate, inserting and removing a connector from the substrate or tightening screw to the substrate. Excessive mechanical stress may cause cracking in the product.



12.8 Cleaning

The product shall be cleaned under the following conditions.

- (1) The cleaning temperature shall be 60°C max. If isopropyl alcohol (IPA) is used, the cleaning temperature shall be 40°C max.
- (2) Perform ultrasonic cleaning under the following conditions. Exercise caution to prevent resonance phenomenon in mounted products and the PCB.

Item	Requirement		
Power	20 W/L max.		
Time	5 min max.		
Frequency	28 kHz to 40 kHz		

(3) Cleaner

Alcohol-based cleaner: IPA

Aqueous agent: PINE ALPHA ST-100S

- (4) There shall be no residual flux or residual cleaner. When using aqueous agent, rinse the product with deionized water adequately and completely dry it so that no cleaner is left.
- * For other cleaning, consult our technical department.

12.9 Storage and transportation

Storage period	Use the product within 12 months after delivery. If you do not use the product for more than 12 months, check solderability before using it.
Storage conditions	 The products shall be stored in a room not subject to rapid changes in temperature and humidity. The recommended temperature range is -10°C to +40°C. The recommended relative humidity range is 15% to 85%. Keeping the product in corrosive gases, such as sulfur, chlorine gas or acid, oxidizes the electrode, resulting in poor solderability or corrosion of the coil wire of the product. Do not keep products in bulk packaging. Doing so may cause collision between the products or between the products and other products, resulting in core chipping or wire breakage. Do not place the products directly on the floor; they should be placed on a palette so that they are not affected by humidity or dust. Avoid keeping the products in a place exposed to direct sunlight, heat or vibration.
Transportation	Excessive vibration and impact reduces the reliability of the products. Exercise caution when handling the products.





12.10 Resin coating

The inductance value may change due to high cure-stress of resin to be used for coating/molding products.

A wire breakage issue may occur by mechanical stress caused by the resin, amount/cured shape of resin, or operating condition etc. Some resin contains some impurities or chloride possible to generate chlorine by hydrolysis under some operating condition may cause corrosion of wire of coil, leading to wire breakage.

So, please pay your careful attention when you select resin in case of coating/molding the products with the resin. Prior to use the coating resin, please make sure no reliability issue is observed by evaluating products mounted on your board.

12.11 Handling of product

- Sharp material such as a pair of tweezers or other material such as bristles of cleaning brush, shall not be touched to the winding portion to prevent the breaking of wire.
- Mechanical shock should not be applied to the products mounted on the board to prevent the breaking of the core.

12.12 Handling with mounting equipment

- With some types of mounting equipment, a support pin pushes up the product from the bottom of the base (paper) tape when the product is sucked with the pick-up nozzle.
- When using this type of equipment, detach the support pin to prevent the breaking of wire on the product.
- In some cases, the laser recognition function of the mounting equipment may not recognize this product correctly. Please contact us when using laser recognition. (There is no problem with the permeation and reflection type.)

13. **A**Note


- (1) Please make sure that your product has been evaluated in view of your specifications with our product being mounted to your product.
- (2) You are requested not to use our product deviating from the reference specifications.
- (3) The contents of this reference specification are subject to change without advance notice. Please approve our product specifications or transact the approval sheet for product specifications before ordering.

14. Appendix

Electrical performance: Measuring method for inductance/Q (Q measurement is applicable only when the Q value is included in the rating table.)

Perform measurement using the method described below. (Perform correction for the error deriving from the measuring terminal.)

(1) Residual elements and stray elements of the measuring terminal can be expressed by the F parameter for the 2-pole terminal as shown in the figure below.



(2) The product's impedance value (Zx) and measured impedance value (Zm) can be expressed as shown below, by using the respective current and voltage for input/output.

$$Zm = \frac{V_1}{I_1} \qquad Zx = \frac{V_2}{I_2}$$

(3) Thus, the relationship between the product's impedance value (Zx) and measured impedance value (Zm) is as follows.

$$Zx = \alpha \frac{Zm - \beta}{1 - Zm\Gamma}$$
Here,
$$\alpha = D/A = 1$$

$$\beta = B/D = Zsm - (1 - Yom Zsm) Zss$$

$$\Gamma = C/A = Yom$$

$$Zsm: measured impedance of short chip$$

$$Zss: residual impedance of short chip (0.771 nH)$$

$$Yom: measured admittance when measuring terminal is open$$

Spec No.: JELF243A 0082K-01

Reference Only

P10/10

(4) Calculate inductance Lx and Qx using the equations shown below.

$Lx = \frac{Im (Zx)}{2\pi f}$	Lx: inductance of chip coil
$Qx = \frac{Im (Zx)}{Re (Zx)}$	Qx: Q of chip coil f: measuring frequency

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Murata:

LQW18CN15NJ00D	LQW18CN33NJ00D	LQW18CN4N9D00D	LQW18CN55NJ00D	LQW18CN85NJ00D
LQW18CNR10K00D	LQW18CNR12J00D	LQW18CNR16J00D	LQW18CNR21J00D	LQW18CNR27J00D
LQW18CNR33J00D	LQW18CNR39J00D	LQW18CNR47J00D	LQW18CNR56J00D	LQW18CNR65J00D
LQW18CN15NJ0ZD	LQW18CN33NJ0ZD	LQW18CN4N9D0ZD	LQW18CN55NJ0ZD	LQW18CN85NJ0ZD
LQW18CNR10K0ZD	LQW18CNR12J0ZD	LQW18CNR16J0ZD	LQW18CNR21J0ZD	LQW18CNR27J0ZD
LQW18CNR33J0ZD	LQW18CNR39J0ZD	LQW18CNR47J0ZD	LQW18CNR56J0ZD	LQW18CNR65J0ZD