



1.0A HIGH VOLTAGE SCHOTTKY BARRIER RECTIFIER

Features

- Guard Ring Die Construction for Transient Protection
- Ideally Suited for Automated Assembly
- Low Power Loss, High Efficiency
- Surge Overload Rating to 30A Peak
- For Use in Low Voltage, High Frequency Inverters, Free Wheeling, and Polarity Protection Application
- High Temperature Soldering: +260°C/10 Second at Terminal
- Lead Free Finish/RoHS Compliant (Note 1)
- Green Molding Compound (No Halogen and Antimony) (Note 2)

Mechanical Data

- Case: SMA / SMB
- Case Material: Molded Plastic. UL Flammability Classification Rating 94V-0
- Moisture Sensitivity: Level 1 per J-STD-020
- Terminals: Lead Free Plating (Matte Tin Finish). Solderable per MIL-STD-202, Method 208 ⁶³
- Polarity: Cathode Band or Cathode Notch
- Weight: SMA 0.064 grams (Approximate)
 SMB 0.093 grams (Approximate)

SMA / SMB





Top View

Bottom View

Ordering Information (Note 3)

Part Number	Compliance	Case	Packaging
B1x-13-F	AEC-Q101	SMA	5,000/Tape & Reel
B1xQ-13-F	Automotive	SMA	5,000/Tape & Reel
B1xB-13-F	AEC-Q101	SMB	3,000/Tape & Reel
B1xBQ-13-F	Automotive	SMB	3,000/Tape & Reel


^{*}x = Device type, e.g. B180-13-F (SMA package); B1100B-13-F (SMB package).

Notes:

- 1. EU Directive 2002/95/EC (RoHS) & 2011/65/EU (RoHS 2) compliant. All applicable RoHS exemptions applied.
- See http://www.diodes.com/quality/lead_free.html for more information about Diodes Incorporated's definitions of Halogen- and Antimony-free, "Green" and Lead-free.
- 3. For packaging details, go to our website at http://www.diodes.com.

Marking Information

SMA / SMB



XXX = Product Type Marking Code, ex: B170 (SMA package)
XXXX = Product Type Marking Code, ex: B190B (SMB package)

| | = Manufacturers' Code Marking
YWW = Date Code Marking
Y = Last Digit of Year (ex: 5 for 2015)
WW = Week Code 01 to 52



Maximum Ratings (@T_A = +25°C unless otherwise specified.)

Single phase, half wave, 60Hz, resistive or inductive load. For capacitance load, derate current by 20%.

Characteristic	Symbol	B170/B	B180/B	B190/B	B1100/B	Unit
Peak Repetitive Reverse Voltage Working Peak Reverse Voltage DC Blocking Voltage	V _{RRM} V _{RWM} V _R	70	80	90	100	V
RMS Reverse Voltage	V _{R(RMS)}	49	56	63	70	V
Average Rectified Output Current @ T _T = +125°C	lo		1.	.0	•	Α
Non-Repetitive Peak Forward Surge Current 8.3ms Single Half Sine-Wave Superimposed on Rated Load		30				Α
Repetitive Peak Reverse Current	I _{RRM}		1.	.0		Α

Thermal Characteristics


Characteristic	Symbol	B170/B	B180/B	B190/B	B1100/B	Unit
Typical Thermal Resistance Junction to Terminal (Note 4)	$R_{\theta JT}$	25			°C/W	
Operating and Storage Temperature Range		-65 to +150			°C	


Electrical Characteristics @T_A = 25°C unless otherwise specified

Characteristic	Symbol	Min	Тур	Max	Unit	Test Condition	
Forward Voltage Drop	V _F	-	-	0.79		$I_F = 1.0A, T_A = +25^{\circ}C$	
Tolward Vollage Drop				0.69		$I_F = 1.0A, T_A = +100$ °C	
Leakage Current (Note 5)	I _R		-	-	0.5	mA	@ Rated V _R , T _A = +25°C
Leakage Current (Note 5)		-	-	5.0	IIIA	@ Rated V _R , T _A = +100°C	
Total Capacitance	Ст	-	-	80	pF	$V_R = 4V, f = 1MHz$	


Notes:

- 4. Valid provided that terminals are kept at ambient temperature. 5. Short duration pulse test used to minimize self-heating effect.













Fig. 4 Max Non-Repetitive Peak Forward Surge Current

Package Outline Dimensions

Please see AP02002 at http://www.diodes.com/datasheets/ap02002.pdf for the latest version.




SMA				
Dim	Min	Max		
Α	2.29	2.92		
В	4.00	4.60		
С	1.27	1.63		
D	0.15	0.31		
Е	4.80	5.59		
G	0.05	0.20		
Н	0.76	1.52		
J	1.96	2.40		
All Dimensions in mm				

SMB			
Dim	Min	Max	
Α	3.30	3.94	
В	4.06	4.57	
C	1.96	2.21	
D	0.15	0.31	
Е	5.00	5.59	
G	0.05	0.20	
H	0.76	1.52	
J	2.00	2.50	
All Dimensions in mm			

Suggested Pad Layout

Please see AP02001 at http://www.diodes.com/datasheets/ap02001.pdf for the latest version.



SMA

Dimensions	Value (in mm)		
С	4.00		
G	1.50		
X	2.50		
X1	6.50		
Y	1.70		

SMB

Dimensions	Value (in mm)
C	4.30
G	1.80
Х	2.50
X1	6.80
Y	2.30



IMPORTANT NOTICE

DIODES INCORPORATED MAKES NO WARRANTY OF ANY KIND, EXPRESS OR IMPLIED, WITH REGARDS TO THIS DOCUMENT, INCLUDING, BUT NOT LIMITED TO, THE IMPLIED WARRANTIES OF MERCHANTABILITY AND FITNESS FOR A PARTICULAR PURPOSE (AND THEIR EQUIVALENTS UNDER THE LAWS OF ANY JURISDICTION).

Diodes Incorporated and its subsidiaries reserve the right to make modifications, enhancements, improvements, corrections or other changes without further notice to this document and any product described herein. Diodes Incorporated does not assume any liability arising out of the application or use of this document or any product described herein; neither does Diodes Incorporated convey any license under its patent or trademark rights, nor the rights of others. Any Customer or user of this document or products described herein in such applications shall assume all risks of such use and will agree to hold Diodes Incorporated and all the companies whose products are represented on Diodes Incorporated website, harmless against all damages.

Diodes Incorporated does not warrant or accept any liability whatsoever in respect of any products purchased through unauthorized sales channel. Should Customers purchase or use Diodes Incorporated products for any unintended or unauthorized application, Customers shall indemnify and hold Diodes Incorporated and its representatives harmless against all claims, damages, expenses, and attorney fees arising out of, directly or indirectly, any claim of personal injury or death associated with such unintended or unauthorized application.

Products described herein may be covered by one or more United States, international or foreign patents pending. Product names and markings noted herein may also be covered by one or more United States, international or foreign trademarks.

This document is written in English but may be translated into multiple languages for reference. Only the English version of this document is the final and determinative format released by Diodes Incorporated.

LIFE SUPPORT

Diodes Incorporated products are specifically not authorized for use as critical components in life support devices or systems without the express written approval of the Chief Executive Officer of Diodes Incorporated. As used herein:

- A. Life support devices or systems are devices or systems which:
 - 1. are intended to implant into the body, or
 - 2. support or sustain life and whose failure to perform when properly used in accordance with instructions for use provided in the labeling can be reasonably expected to result in significant injury to the user.
- B. A critical component is any component in a life support device or system whose failure to perform can be reasonably expected to cause the failure of the life support device or to affect its safety or effectiveness.

Customers represent that they have all necessary expertise in the safety and regulatory ramifications of their life support devices or systems, and acknowledge and agree that they are solely responsible for all legal, regulatory and safety-related requirements concerning their products and any use of Diodes Incorporated products in such safety-critical, life support devices or systems, notwithstanding any devices- or systems-related information or support that may be provided by Diodes Incorporated. Further, Customers must fully indemnify Diodes Incorporated and its representatives against any damages arising out of the use of Diodes Incorporated products in such safety-critical, life support devices or systems.

Copyright © 2015, Diodes Incorporated

www.diodes.com