

## MA Varistor Series



### Agency Approvals

Agency	Agency File Number
	None

### Additional Information



**Datasheet**



**Resources**



**Samples**

### Description

The MA Series of transient surge suppressors are axial lead Metal Oxide Varistors (MOVs) for use in a wide variety of board level industrial and commercial electronic equipment. They are intended to protect components and signal/data lines from low energy transients where the small axial lead package is required.

The MA Series is offered with standard ('S' suffix) or tightened ('B' suffix) clamping voltage.

See MA Series Device Ratings and Specifications Table for part number and brand information.

### Features

- Lead-free, Halogen-Free and RoHS compliant.
- 3mm diameter disc size
- Small axial lead package
- Wide operating voltage range:  
 $V_{M(AC)RMS}$  9V to 264V  
 $V_{M(DC)}$  13V to 365V
- Available in tape and reel or bulk packaging
- No derating up to 85°C ambient
- New black epoxy offers improved performance for high temperature Lead-free wave soldering process.

### Absolute Maximum Ratings

• For ratings of individual members of a series, see Device Ratings and Specifications chart

Continuous	MA Series	Units
Steady State Applied Voltage:		
AC Voltage Range ( $V_{M(AC)RMS}$ )	9 to 264	V
DC Voltage Range ( $V_{M(DC)}$ )	13 to 365	V
Transient:		
Peak Pulse Current ( $I_{TM}$ )		
For 8/20 $\mu$ s Current Wave(See Figure 2)	40 to 100	A
Single-Pulse Energy Range		
For 2ms Current Square Wave ( $W_{TM}$ )	0.06 to 1.7	J
Operating Ambient Temperature Range ( $T_A$ )	-55 to +85	°C
Storage Temperature Range ( $T_{STG}$ )	-55 to +125	°C
Temperature Coefficient ( $\alpha V$ ) of Clamping Voltage ( $V_C$ ) at Specified Test Current	<0.01	%/°C
Hi-Pot Encapsulation (COATING Isolation Voltage Capability) Dielectric must withstand indicated DC voltage for one minute per MIL-STD 202, Method 301)	1000	V
COATING Insulation Resistance	1000	M $\Omega$

*CAUTION: Stresses above those listed in "Absolute Maximum Ratings" may cause permanent damage to the device. This is a stress only rating and operation of the device at these or any other conditions above those indicated in the operational sections of this specification is not implied.*

### MA Series Ratings & Specifications

Part Number	Brand (mm)	Maximum Rating (85°C)				Specifications (25°C)					
		Continuous		Transient		Varistor Voltage at 1mA DC Test Current			Max Clamping Volt $V_C$ at 2.0A (8/20 $\mu$ s)	Typical Capacitance	
		$V_{RMS}$	$V_{DC}$	Energy (10/1000 $\mu$ s)	Peak Current (8/20 $\mu$ s)						
		$V_{M(AC)}$	$V_{M(DC)}$	$W_{TM}$	$I_{TM}$	Min	$V_{N(DC)}$	Max	$V_C$	$f = 1\text{MHz}$	
		(V)	(V)	(J)	(A)	(V)	(V)	(V)	(A)	(pF)	
V18MA1A	18A	9	13	0.06	40	14	18	23	49	550	
V18MA1B	18B	10	14	0.07	40	15	18	21	44	550	
V18MA1S	18S	10	14	0.06	40	15	18	21	49	550	
V22MA1A	22A	10	15	0.09	40	16	22	28	55	410	
V22MA1B	22B	14	18	0.10	40	19	22	26	51	410	
V22MA1S	22S	14	18	0.09	40	19	22	26	55	410	
V27MA1A	27A	13	19	0.10	40	21	27	34	67	370	
V27MA1B	27B	17	22	0.11	40	24	27	31	59	370	
V27MA1S	27S	17	22	0.10	40	24	27	31	67	370	
V33MA1A	33A	18	23	0.13	40	26	33	40	73	300	
V33MA1B	33B	20	26	0.15	40	29.5	33	36.5	67	300	
V33MA1S	33S	20	26	0.14	40	29.5	33	36.5	73	300	
V39MA2A	39A	22	28	0.16	40	31	39	47	86	250	
V39MA2B	39B	25	31	0.18	40	35	39	43	79	250	
V39MA2S	39S	25	31	0.17	40	35	39	43	86	250	
V47MA2A	47A	27	34	0.19	40	37	47	57	99	210	
V47MA2B	47B	30	38	0.21	40	42	47	52	90	210	
V47MA2S	47S	30	38	0.19	40	42	47	52	99	210	
V56MA2A	56A	32	40	0.23	40	44	56	68	117	180	
V56MA2B	56B	35	45	0.25	40	50	56	62	108	180	
V56MA2S	56S	35	45	0.23	40	50	56	62	117	180	
V68MA3A	68A	38	48	0.26	40	54	68	82	138	150	
V68MA3B	68B	40	56	0.30	40	61	68	75	127	150	
V68MA3S	68S	40	56	0.27	40	61	68	75	138	150	
V82MA3A	82A	45	60	0.33	40	65	82	99	163	120	
V82MA3B	82B	50	66	0.37	40	73	82	91	150	120	
V82MA3S	82S	50	66	0.34	40	73	82	91	163	120	
V100MA4A	100	57	72	0.40	40	80	100	120	200	100	
V100MA4B	101	60	81	0.45	40	90	100	110	185	100	
V100MA4S	102	60	81	0.42	40	90	100	110	200	100	
V120MA1A	120	72	97	0.40	100	102	120	138	220	40	
V120MA2B	121	75	101	0.50	100	108	120	132	205	40	
V120MA2S	122	75	101	0.46	100	108	120	132	220	40	
V150MA1A	150	88	121	0.50	100	127	150	173	255	32	
V150MA2B	151	92	127	0.60	100	135	150	165	240	32	
V180MA1A	180	105	144	0.60	100	153	180	207	310	27	
V180MA3B	181	110	152	0.70	100	162	180	198	290	27	
V220MA2A	220	132	181	0.80	100	187	220	253	380	21	
V220MA4B	221	138	191	0.90	100	198	220	242	360	21	
V270MA2A	270	163	224	0.90	100	229	270	311	460	17	
V270MA4B	271	171	235	1.00	100	243	270	297	440	17	
V330MA2A	330	188	257	1.00	100	280	330	380	570	14	
V330MA5B	331	200	274	1.10	100	297	330	363	540	14	
V390MA3A	390	234	322	1.20	100	331	390	449	670	12	
V390MA6B	391	242	334	1.30	100	351	390	429	640	12	
V430MA3A	430	253	349	1.50	100	365	430	495	740	11	
V430MA7B	431	264	365	1.70	100	387	430	473	700	11	

NOTE: Average power dissipation of transients not to exceed 200mW.

### Power Dissipation Ratings




Figure 1

Should transients occur in rapid succession, the average power dissipation required is simply the energy (watt-seconds) per pulse times the number of pulses per second. The power so developed must be within the specifications shown on the Device Ratings and Specifications table for the specific device. Furthermore, the operating values need to be derated at high temperatures as shown above. Because varistors can only dissipate a relatively small amount of average power they are, therefore, not suitable for repetitive applications that involve substantial amounts of average power dissipation.

### Peak Pulse Current Test Waveform




Figure 2

- $O_1$  = Virtual Origin of Wave
- $T$  = Time from 10% to 90% of Peak
- $T_1$  = Rise Time =  $1.25 \times T$
- $T_2$  = Decay Time

**Example** - For an  $8/20 \mu\text{s}$  Current Waveform:

- $8 \mu\text{s} = T_1 = \text{Rise Time}$
- $20 \mu\text{s} = T_2 = \text{Decay Time}$

### Repetitive Surge Capability

#### V18MA - V100MA




Figure 3

#### V120MA1A/S - V430MA3A





Figure 4

NOTE: If pulse ratings are exceeded, a shift of  $V_{\text{NIDC}}$  (at specified current) of more than +/-10% could result. This type of shift, which normally results in a decrease of  $V_{\text{NIDC}}$ , may result in the device not meeting the original published specifications, but it does not prevent the device from continuing to function, and to provide ample protection.


**Maximum Clamping Voltage**

**V18MA1A/S - V100MA4A/S**




**Figure 5**

**V18MA1B - V100MA4B**




**Figure 6**

**V120MA1A/S - V430MA3A**



**Figure 7**


**V120MA2B - V430MA7B**



**Figure 8**


**Wave Solder Profile**

**Non Lead-free Profile**




**Figure 9**

**Lead-free Profile**



**Figure 10**


## Product Dimensions



Symbol	Inches		Millimeters	
	Min	Max	Min	Max
$\varnothing b$	0.024	0.026	0.61	0.66
$\varnothing D$	0.118	0.177	3.0	4.5
$H$	0.177	0.276	4.5	7.0
$L$	1.740	1.220	27.3	31.0

Typical Weight = 0.5g

## Tape and Reel Dimensions



Conforms to EIA Standard RS-296-E


## Physical Specifications

<b>Lead Material</b>	Tin-plated Copper clad steel
<b>Soldering Characteristics</b>	Solderability per MIL-STD-202, Method 208
<b>Insulating Material</b>	Cured, flame retardant epoxy polymer meets UL94V-0 requirements
<b>Device Labeling</b>	Marked with LF, voltage and date code

## Environmental Specifications

<b>Operating/Storage Temperature</b>	-40°C to +85°C
<b>Passive Aging</b>	+85°C, 1000 hours +/-10% typical voltage change
<b>Humidity Aging</b>	+85°C, 85% RH, 1000 hours +/-10% typical voltage change
<b>Thermal Shock</b>	+85°C to -40°C 5 times +/-10% typical voltage change
<b>Solvent Resistance</b>	MIL-STD-202, Method 215
<b>Moisture Sensitivity</b>	Level 1, J-STD-020

## Part Numbering System



**Disclaimer Notice - Information furnished is believed to be accurate and reliable. However, users should independently evaluate the suitability of and test each product selected for their own applications. Littelfuse products are not designed for, and may not be used in, all applications. Read complete Disclaimer Notice at [www.littelfuse.com/disclaimer-electronics](http://www.littelfuse.com/disclaimer-electronics).**

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

## Littelfuse:

[V27MT1B](#) [V120MT1A](#) [V39MT2B](#) [V56MT2A](#) [V39MA2S](#) [V100MA4B](#) [V180MT1A](#) [V18MA1B](#) [V68MA3A](#) [V22MT1B](#)  
[V47MA2B](#) [V39MA2A](#) [V430MA7B](#) [V120MA2B](#) [V33MA1B](#) [V270MA4B](#) [V22MA1B](#) [V390MA6B](#) [V150MT2B](#) [V33MA1A](#)  
[V180MT3B](#) [V390MT6B](#) [V270MT4B](#) [V120MT2B](#) [V82MA3B](#) [V430MT3A](#) [V56MA2S](#) [V180MA1A](#) [V68MT3A](#)  
[V33MT1B](#) [V47MT2B](#) [V27MA1B](#) [V56MA2B](#) [V82MT3B](#) [V18MA1A](#) [V18MA1S](#) [V220MA4B](#) [V27MA1S](#) [V39MA2B](#)  
[V22MA1S](#) [V27MA1A](#) [V39MT2A](#) [V68MA3B](#) [V22MA1A](#) [V390MA3A](#) [V100MT4B](#) [V430MT7B](#) [V150MA1A](#) [V220MT2A](#)  
[V47MA2S](#) [V120MA1A](#) [V220MA2A](#) [V33MA1S](#) [V68MT3B](#) [V180MA3B](#) [V18MT1B](#) [V330MT2A](#) [V47MA2A](#)  
[V330MT5B](#) [V390MT3A](#) [V330MA2A](#) [V430MA3A](#) [V150MA2B](#) [V270MA2A](#) [V100MA4A](#) [V270MT2A](#) [V56MA2A](#)  
[V220MT4B](#) [V330MA5B](#) [V47MT2A](#) [V56MT2B](#) [V82MA3A](#) [V33MT1A](#) [V330MAX1131](#) [V100MA4S](#) [V120MA2S](#)  
[V68MA3S](#) [V82MA3S](#) [V82MT3S](#)