



Designers' Choice

# "AUTO" FUSE CLIPS & HOLDERS


- Available for **standard** and **mini** blade fuses
- Thru hole PC mountable, maintains position during wave soldering
- Space saving, low profile designs
- Horizontal and vertical **mini** blade clip for Littelfuse ATO 297 series and Bussmann ATM fuses
- Withstands the rigors of shock and vibration
- Horizontal and vertical **standard** blade clips for Littelfuse ATO 257 series and Bussmann ATC fuses
- Holds fuse securely, even after multiple insertions
- Orientation legs assure proper PC installation

**Voltage Rating:** 500VAC  
**Current Rating:** 15 Amps


## PC AUTOMOTIVE BLADE FUSE CLIPS




.016 Brass, Nickel Plate




Mounting Detail For Two Clips




CAT. NO. 3522 - Vertical



.012 Brass, Nickel Plate



Mounting Detail For Two Clips




CAT. NO. 3550 - Horizontal




.016 Brass, Nickel Plate

- Low Profile



Mounting Detail For Two Clips




CAT. NO. 3564 - Vertical


### FOR .110 x .032 MINI BLADE FUSES




.012 Brass, Nickel Plate




Mounting Detail For Two Clips




CAT. NO. 3544 - Vertical



.012 Brass, Nickel Plate



Mounting Detail For Two Clips



CAT. NO. 3549 - Horizontal

## PC AUTOMOTIVE BLADE FUSE HOLDERS


- Thru hole PC mountable, maintains position during wave soldering
- Holder design prevents solder wicking
- Withstands the rigors of shock and vibration
- Holds fuse securely, even after multiple insertions
- Suitable for 15 Amp applications

### SPECIFICATIONS


**Contacts:** Brass, Nickel Plate; **Insulator:** Glass Filled Nylon, UL Rated 94V-0  
**Current Rating:** 15 Amps; **Voltage Rating:** 500VAC  
**Temperature Rating:** -58°F to +292°F (-50°C to +145°C)

### FOR .205 x .025 STANDARD BLADE FUSES

For Littelfuse ATO 257/Bussman ATC or equivalent




Mounting Detail




CAT. NO. 3522-2

### FOR .110 x .032 MINI BLADE FUSES

For Littelfuse ATO 297/Bussman ATC or equivalent




Mounting Detail



CAT. NO. 3544-2

## MODULAR PC AUTOMOTIVE BLADE FUSE HOLDER

For Littelfuse ATO 257/Bussmann ATC or equivalent




CAT. NO. 3560


- Designed for standard auto blade fuses
- Fully insulated compact design
- Mounts easily in pre-drilled or punched hole
- Holder has pocket to hold spare fuse
- Safety lever release clip will not open under shock or vibration
- Fuses are installed and removed easily
- May be used individually or easily interlocked for multiple mounting

### SPECIFICATIONS


**Contacts:** Brass, Tin Plate **Body:** Nylon, UL Rated 94V-0  
**Dielectric Strength:** (60 seconds) 1500VAC/min.  
**Current Rating:** 30 Amps



Mounting Detail



Mounting Detail For Two Holders






Designers' Choice

# PC QUICK-FIT TERMINALS


## .110 / .187 / .205 / .250 PC QUICK-FIT FEMALE TYPES

### .110 HORIZONTAL





**MATERIAL:**  
.012 Brass, Nickel Plate

CAT. NO.	ACCEPTS TAB
3545	.110 × .020
3549	.110 × .032




### .205 HORIZONTAL




**MATERIAL:**  
.012 Brass, Nickel Plate

CAT. NO.	ACCEPTS TAB
3546	.205 × .020
3550	.205 × .025




### .250 HORIZONTAL





**MATERIAL:**  
.016 Brass, Nickel Plate

CAT. NO.	ACCEPTS TAB




### .110 VERTICAL




**MATERIAL:**  
.012 Brass, Nickel Plate

CAT. NO.	ACCEPTS TAB
3534	.110 × .020




### .205 VERTICAL




**MATERIAL:** Brass, Nickel Plate

CAT. NO.	ACCEPTS TAB	MAT'L THICK
3525	.205 × .020	.012
3522	.205 × .025	.016




### .250 VERTICAL





**MATERIAL:**  
.016 Brass, Nickel Plate

CAT. NO.	ACCEPTS TAB




### .187 VERTICAL




**MATERIAL:**  
.016 Brass, Tin Plate

CAT. NO.	ACCEPTS TAB
3548	.187 × .020
3551	.187 × .032




### QUICK-FIT FEMALES



**MATERIAL:** Tinned Brass


CAT. NO.	A DIM TAB SIZE	B DIM LENGTH	AWG SIZE	MAT'L THICK
1252	.110 × .020	.640	18-22	.010
1264	.187 × .020	.576	16-22	.013
4469	.205 × .020	.640	16-20	.013

### .250 QUICK-FIT VINYL BOOT



- Easily slips over terminal
- Insulated and protects


CAT. NO.	BOOT COLOR
4471	CLEAR
4472	RED
4473	BLUE
4474	YELLOW



## MALE "QUICK-FIT" INSERTION TOOL

Designed to install .250 male "Quick-Fit" terminals quickly and easily

- Insert terminal into slot, spring clip will hold terminal securely for positioning
- Align terminal with mounting holes and "press-fit" to secure firmly in place
- Lift tool to release terminal



CAT. NO. 1288