Metal switch medium stroke, snap-in, Switching Voltage up to 250V



MSM 22 SI snap in mounting

See below:

#### **Approvals and Compliances**

### **Description**

- Switches with snap-in mounting from the frontside
- Available in version Standard, lettered, with Point Illumination or Ring
- Further characteristics see MSM 22 data sheet

#### Characteristics

- Housing and actuator material: high-quality stainless steel
- Quick Assembly by snap-in mounting from the front side
- Short Mounting Depth, | for assembly with no access from rear side

#### References

Alternative: Standard version

# Weblinks

pdf data sheet, html datasheet, General Product Information, CAD-Drawings, Product News, Detailed request for product

#### **Technical Data**

| Electrical Data |                    |  |
|-----------------|--------------------|--|
| Data            | See MSM data sheet |  |

| Mechanical Data    |   |
|--------------------|---|
| Mounting           | Snap-in                                     |
| Mounting Diameter  | Ø 22 mm                                     |
| Drilling tolerance | max. 0.15 mm / Drilling edges free of burrs |
| Panel Thickness    | 1.5, 2.0, 2.5, 3.0mm                        |
| Mounting Force     | 50 - 100 N                                  |
| Data               | See MSM data sheet                          |
| Climatical Data    |   |
| Data               | See MSM data sheet                          |
| Material           |   |
| Housing            | Stainless Steel                             |
| Seal Ring          | NBR70                                       |
| Plastic Nut        | PA, UL94                                    |

### **Approvals and Compliances**

Detailed information on product approvals, code requirements, usage instructions and detailed test conditions can be looked up in Details about Approvals

SCHURTER products are designed for use in industrial environments. They have approvals from independent testing bodies according to national and international standards. Products with specific characteristics and requirements such as required in the automotive sector according to IATF 16949, medical technology according to ISO 13485 or in the aerospace industry can be offered exclusively with customer-specific, individual agreements by SCHURTER.

#### **Application standards**

Application standards where the product can be used

| Organization | Design                         | Standard       | Description   |
|--------------|--------------------------------|----------------|---|
| <u>IEC</u>   | Designed for applications acc. | IEC/UL 62368-1 | Audio/video, information and communication technology equipment - Part 1: Safety requirements |


## Compliances

The product complies with following Guide Lines

| Identification | Details | Initiator   | Description   |
|----------------|---------|-------------|---|
| ROHS           | RoHS    | SCHURTER AG | Directive RoHS 2011/65/EU, Amendment (EU) 2015/863  |
| REACH          | REACH   | SCHURTER AG | On 1 June 2007, Regulation (EC) No 1907/2006 on the Registration,<br>Evaluation, Authorization and Restriction of Chemicals 1 (abbreviated as<br>"REACH") entered into force. |


## Dimension [mm]

MSM 22 SI



## **Dimension**


SI 22



Drilling diagram

## **Assembly Instructions**

Mounting diagram



The assembly becomes effective by the force fitting of the switch into the drilling hole, whereas the 0-ring will be displaced. After inserting the switch through the drilling hole, the 0-ring expands and the switch is fixed in the drilling hole.

### **All Variants**

| Diameter | Switching<br>Current | Switching Voltage | Illumination, LED         | Housing Material | Panel<br>Thick- | Config.<br>Code | Order Number      |
|----------|----------------------|-------------------|---------------------------|------------------|-----------------|-----------------|-------------------|
| [mm]     | [A]                  | [VAC/ VDC]        |                           |                  |                 |                 |                   |
| 22       | 5/3A                 | 125/250 VAC       | Point Illumination, red   | Stainless Steel  | 1.5mm           |                 | 1241.6693.1121000 |
| 22       | 5/3A                 | 125/250 VAC       | Point Illumination, green | Stainless Steel  | 1.5mm           |                 | 1241.6693.1122000 |
| 22       | 5/3A                 | 125/250 VAC       | non-illuminated           | Stainless Steel  | 1.5mm           |                 | 1241.6695.1120000 |
| 22       | 5/3A                 | 125/250 VAC       | non-illuminated           | Stainless Steel  | 2mm             |                 | 1241.6699.1120000 |

Legend: Type: MSM

PI = Point Illumination

RI = Ring Illumination

Alu = Aluminium

ES = Stainless steel

Point illuminated versions without resistors, details see MSM data sheet

Further snap-in versions and customer-specific solutions on request. Special materials for use in salt and chlorinated environment on request.

Most Popular.

Availability for all products can be searched real-time:https://www.schurter.com/en/Stock-Check/Stock-Check-SCHURTER

Packaging unit

10 in box with insert (10 pcs.)

**Switches**