





E222871

UL Approved Illuminated Pushbutton

1/2 hp @ 125VAC/250VAC; T120
1/2 hp @ 125VAC/250VAC; T120 10.1A @ 277VAC resistive; T120
10.1A @ 125VAC inductive; T120
16A @ 125VAC/250VAC resistive; T120
6A@ 125VAC/250VAC general purpose; T120
5A @ 125VAC inductive; T120
100,000 cycles average

Contact Resistance	≤ 20mΩ initial
Actuation Force	500 ± 100gF
Actuation Travel	3.2 ± .25mm
Dielectric Strength	2,000Vrms min @ sea level contact to contact
	2,000Vrms min @ sea level to LED
Insulation Resistance	≥ 1,000MΩ min @ 500VDC
Sealing Degree	IP67
Operating Temperature	-40°C to 85°C
Storage Temperature	-40°C to 85°C

Materials

Actuator	Stainless Steel, Anodized Aluminum
LED Lens	Polycarbonate (PC)
Threaded Housing	Stainless Steel, Anodized Aluminum
Terminal Support	Polybutylene Terephthalate (PBT)
Snap Action Switch Base / Cover	Polybutylene Terephthalate (PBT), UL94-V0
Snap Action Switch Pin Plunger	Polybutylene Terephthalate (PBT), UL94-V0
Snap Action Switch Contacts	Silver Alloy
Snap Action Switch Terminals	Silver plated Copper Alloy
Snap Action Switch Support Frame	POM
Hardware	One Hex Nut & one "O" Ring supplied

Combining the LED illumination and metal body of the DH Series switch with the UL recognized switching capability of the VM3 Series snap-action switch.




Ordering Information


1 Corios DILLOS	4		N1	Г	C	Г	10	D
1. Series DHU25 DHU25 DHU28 DHU30	1		N	В	S	R	12	В
2. Number of Poles 1 = SPDT								
3. Bezel Style Blank = Standard Bezel H = Straight Bezel								
4. Latching Option N = Momentary L = Latching								
5. Actuator Style: A = Flush actuator, non-il B = Flush actuator, ring il C = Flush actuator, dot ill G = Flush actuator, Int'l s MR = Mushroom actuator	luminated uminated tandby symbol			entary				
6. Switch Finish S = Brushed Stainless St B = Black Anodized Alum G = Green Anodized Alumi R = Red Anodized Alumi U = Blue Anodized Alumi Y = Yellow Anodized Alumi	inum ninum num num							
7. First LED Color X = No LED								
8. LED Voltage Z = No LED 24 = 24 6 = 6V 110 = 1 12 = 12V 220 = 2 N = No internal resistor in	10V 220V	LED						
10. Terminal Option A = .187" Quick Connect B = .250" Quick Connect			•					




Dimensions - 25mm, Momentary




A - Flush, Non-Illuminated




B - Flush, Ring Illuminated






G - Flush, In'tl Standby Symbol




MR - Mushroom Actuator




Dimensions - 25mm, Latching




A - Flush, Non-Illuminated



B - Flush, Ring Illuminated






G - Flush, In'tl Standby Symbol



Dimensions - 28mm, Momentary





32.00 [1.26] Ø22.85 [.90] ILLUMINATED RING 35.00 0 [1.38] Ø17.50 [.69] Ø32.10 [1.26] 2.10 [.08] 11.00 MAX [.43] 28.80 [1.13] M28x1.5 18.50 [.73]


32.00 [1.26] Ø9.30 [.37] ILLUMINATED DOT 35.00 0 [1.38] Ø32.10 [1.26] 2.10 [.08] 11.00 MAX [.43] 28.80 [1.13] M28x1.5 18.50 [.73] C - Flush, Dot Illuminated


B - Flush, Ring Illuminated


Dimensions - 28mm, Latching













C - Flush, Dot Illuminated




Dimensions - 30mm, Momentary



A - Flush, Non-Illuminated




B - Flush, Ring Illuminated




C - Flush, Dot Illuminated


Dimensions - 30mm, Latching



A - Flush, Non-Illuminated




B - Flush, Ring Illuminated




C - Flush, Dot Illuminated





Schematic & Panel Cut-Out 25mm







28*mm*






30mm










Bezel Detail 25mm







28mm









30mm







Terminal Detail 25mm




A = .187"
utilizing part number VM3CQF1802L00


23.00 [.91] 0.80 TYP [.03] 8.81 [.35] 11.27 [.44] (2X) 2.80 X 0.50 [.11 X .02] 6.35 TYP [.25]

B = .250"
utilitizing part number VM3CQF1801L00

28mm




A = .187"
utilizing part number VM3CQF1802L00



B = .250"
utilitizing part number VM3CQF1801L00



Terminal Detail - continued 30mm



[.91] 0.80 TYP [.03] 8.81 [.35] 11.27 [.44] 8.60 [.34] (2X) 2.80 X 0.50 [.11 X .02] 6.35 TYP [.25]

23.00

B = .250" utilitizing part number VM3CQF1801L00

LED Characteristics

LED Ratings		Color						
		R	Υ	G	В	0	W	Units
Reverse Voltage	V_R	5	5	5	5	5	5	V
Forward Current (peak)	I _{FS}	120	120	160	160	120	160	mA
Reverse Current V _R = 5V	I _R	10	10	10	10	10	10	μA
Power Dissipation	P _T	80	80	120	120	80	120	mW
Forward Voltage (typ) I _F = 20mA	V _F	2.1	2.1	3.3	3.3	2.0	3.0	V
Luminous Intensity, I _F = 20mA	LI	120	120	170	100	120	700	mcd