更改内容	更改原因	更改标记	更改人	更改时间

Approved by:

Checked by:

Issued by:

SPECIFICATION

PRODUCT: SAW FILTER

MODEL: HDIF389A6M



SHOULDER ELECTRONICS LIMITED


1.SCOPE

SHOULDER'S SAW filter series have broad line up products meeting all broadcast standard including NTSC,PAL and SECAM systems. These filters are composed of two interdigital transducers on a single-crystal. piezoelectrical chip. they are used in electronic equipments such as TV and so on.


2.Construction

2.1 Dimension and materials

Manufacturer's name : SHOULDER ELECTRONICS Co. LTD(CHINA) Type : IF389A6M




0: year(0,1,2,3,4,5,6,7,8,9) B:product in this quarter(A:1~3,B:4~6,C:7~9,D:10~12)



Materials
PPS
Lithium niobate
Epoxy resin
Epoxy resin
Cu alloy+Au plate
AlSi alloy
AI

2.2. Circuit construction, measurement circuit



Test circuit for SIP-5 filter Input impedance of the symmetrical post-amplifier: 2 k Ω in parallel with 3 pF

3.Characteristics

Items	Conditions	Specifications
Standard atmospheric conditions	Unless otherwise specified , the standard rang of atmospheric conditions for making measurements and tests is as follows;Ambient temperature: 15° C to 35° C Relative humidity. 25% to 85% Air pressure: 86 kPa to 106 kPa	
Operating temperature rang	Operating temperature rang is the rang of ambient temperatures in which the filter can be operated continuously. -10° C $\sim +60^{\circ}$ C	There shall be no damage.
Storage temperature rang	Storage temperature rang is the rang of ambient temperatures at which the filter can be stored without damage. Conditions are as specified elsewhere in these specifications. -40° C ~ $+70^{\circ}$ C	
Reference temperature	+25°C	

3.1 Maximum Rating

DC voltage	VDC	12	V	Between any terminals
AC voltage	Vpp	10	V	Between any terminals

3.2 Electrical Characteristics

Source impedance		$Zs=50 \Omega$				
Load impedance		$Z_L=2K \Omega //3 pF$		$T_A=25$ °C		
		Freq	Min	typ	max	
Insertion att Reference		37.40MHz	15.3	17.3	19.3	dB
		38.90MHz	4.5	6.0	7.5	dB
		34.47MHz	0.5	2.0	3.5	dB
		33.40MHz	18.0	20.0	22.0	dB
			35.0	42.0	-	dB
Relative atte	enuation	31.40MHz	35.0	42.0	-	dB
		31.90MHz	39.0	49.0	-	dB
		32.40MHz	35.0	45.0	-	dB
			30.0	40.0	-	dB
		40.40MHz	35.0	42.0	-	dB
Sidelobe	25.00~31.90MHz		32.0	40.0		dB
	40.40~45.00MHz		32.0	38.0		dB
Temp	Temperature coefficient			-72		ppm/k

3.3 Environmental Performance Characteristics

Item		Conditio	on		Specifications
High temperature	80±2°C standard	cimen shall be store for 96±4h. Then it atmospheric cond	t shall be subject litions for 1h,	ted to after	
Low temperature	 which measurement shall be made within 1h. The specimen shall be store at a temperature of -20±3°C for 96±4h. Then it shall be subjected to standard atmospheric conditions for 1h, after which measurement shall be made within 1h. 				Mechanical characteristics and specifications in electrical
Humidity	40±2°C for 96 atmosph	The specimen shall be store at a temperature of $0\pm 2^{\circ}C$ with relative humidity of 90% to 96% for $96\pm 4h$. Then it shall be subjected to standard tmospheric conditions for 1h, after which neasurement shall be made within 1h.			characteristics shall be satisfied. There shall be no excessive change in appearance.
Thermal shock	The specimen shall be subjected to 8 continuous cycles each as shown below. Then it shall be subjected to standard atmospheric conditions for 1h, after which measurement shall be made within 1h.				
		Temperature	Duration		
	1 2	+25 °C=>−40 °C -40 °C	0.5h 4h		
	3	-40 °C=>+85 °C	2h		
	4	+85 °C	4h		
	5	+85 °C=>+25 °C	0.5h		
	6	+25 °C	1h		

Resistance to	Reflow soldering method	
Soldering	Peak: 255 ±5 °C, 220 ±5 °C, 40s	
heat	At electrode temperature of the specimen.	
	Temperature profile of reflow soldering Soldering 200 Pre-heating 100 50 1 to 2 min. 1 to 2 min. Pre-heating 2 min. or more	
	The specimen shall be passed through the reflow furnace with the condition shown in the above profile for 1 time. The specimen shall be stored at standard atmospheric conditions for 1h, after which the measurement shall be made. Test board shall be 1.6 mm thick. Base material shall be glass fabric base epoxy resin.	
Solder ability	Immerse the pins melt solder at $260^{\circ}C+5/-0^{\circ}C$ for 5 sec.	More then 95% of total area of the pins should be covered with solder

3.4 Mechanical Test

Items	Conditions	Specifications
Vibration	600-3300rpm amplitude 1.5mm	
	3 directions 2 H each	
Drop	On maple plate from 1 m high 3 times	
-		There shall be no
Lead pull	Pull with 1 kg force for 30 seconds	damage.
Lead bend	90° bending with 500g weigh 2 times	

3.5 Voltage Discharge Test

Item	Condition	Specifications
Surge	Between any two electrode	
	Toov TooopF 4Moham	There shall be no damage

3.6 Frequency response:

