

PCA9672

Remote 8-bit I/O expander for Fm+ I²C-bus with interrupt and reset

Rev. 3 — 27 May 2013

Product data sheet

1. General description

The PCA9672 provides general-purpose remote I/O expansion via the two-wire bidirectional I²C-bus (serial clock (SCL), serial data (SDA)).

The devices consist of eight quasi-bidirectional ports, 1 MHz 30 mA drive I²C-bus interface, three hardware address inputs and a reset input operating between 2.3 V and 5.5 V. 1 MHz I²C-bus Fast-mode Plus (Fm+) can support PWM dimming of LEDs, and higher I²C-bus drive 30 mA allows more devices to be on the bus without the need for bus buffers. The quasi-bidirectional port can be independently assigned as an input to monitor interrupt status or keypads, or as an output to activate indicator devices such as LEDs. The system master can read from the input port or write to the output port through a single register.

The low current consumption of 2.5 μ A (typical, static) is great for mobile applications and the latched output ports have 25 mA high current sink drive capability for directly driving LEDs.

The PCA9672 has two hardware address pins, allowing sixteen of each device to be on the same I²C-bus without the need for bus buffers, so there can be supporting up to 128 I/Os (for example, 128 LEDs).

The active LOW open-drain interrupt output (\overline{INT}) can be connected to the interrupt logic of the microcontroller and is activated when any input state differs from its corresponding input port register state. It is used to indicate to the microcontroller that an input state has changed and the device needs to be interrogated without the microcontroller continuously polling the input register via the I²C-bus.

The internal Power-On Reset (POR) and active LOW hardware reset pin ($\overline{\text{RESET}}$) initialize the I/Os as inputs with a weak internal pull-up 100 μA current source.

2. Features and benefits

- I²C-bus to parallel port expander
- 1 MHz I²C-bus interface (Fast-mode Plus I²C-bus)
- Operating supply voltage 2.3 V to 5.5 V with 5.5 V tolerant I/Os held to V_{DD} with 100 μA current source
- 8-bit remote I/O pins that default to inputs at power-up
- Latched outputs with 25 mA sink capability directly drive LEDs
- Total package sink capability of 200 mA
- Active LOW reset input
- Active LOW open-drain interrupt output



Remote 8-bit I/O expander for Fm+ I²C-bus with interrupt and reset

- Sixteen programmable slave addresses using two address pins
- Readable device ID (manufacturer, device type, and revision)
- Software reset
- Low standby current (2.5 μA typical)
- -40 °C to +85 °C operation
- ESD protection exceeds 2000 V HBM per JESD22-A114 and 1000 V CDM per JESD22-C101
- Latch-up testing is done to JEDEC standard JESD78 which exceeds 100 mA
- Packages offered: SO16, TSSOP16 and HVQFN16

3. Applications

- LED signs and displays
- Servers
- Keypads
- Industrial control
- Medical equipment
- PLCs
- Cellular telephones
- Mobile devices
- Gaming machines
- Instrumentation and test measurement

4. Ordering information

Table 1. Ordering information

Type number	Topside	Package		
	marking	Name	Description	Version
PCA9672BS	672	HVQFN1 6	plastic thermal enhanced very thin quad flat package; no leads; 16 terminals; body $3\times3\times0.85$ mm	SOT758-1
PCA9672D	PCA9672D	SO16	plastic small outline package; 16 leads; body width 7.5 mm	SOT162-1
PCA9672PW	PCA9672	TSSOP16	plastic thin shrink small outline package; 16 leads; body width 4.4 mm	SOT403-1

4.1 Ordering options

Table 2. Ordering options


Type number	Orderable part number	Package	Packing method	Minimum order quantity	Temperature range
PCA9672BS	PCA9672BS,118	HVQFN16	Reel 13" Q1/T1 *standard mark SMD	6000	T_{amb} = -40 °C to +85 °C
PCA9672D	PCA9672D,512	SO16	Standard marking * tube dry pack	1920	T_{amb} = -40 °C to +85 °C
	PCA9672D,518	SO16	Reel 13" Q1/T1 *standard mark SMD dry pack	1000	$T_{amb} = -40 ^{\circ}\text{C} \text{ to } +85 ^{\circ}\text{C}$
PCA9672PW	PCA9672PW,112	TSSOP16	Standard marking * IC's tube - DSC dry pack	2400	$T_{amb} = -40 ^{\circ}\text{C} \text{ to } +85 ^{\circ}\text{C}$
	PCA9672PW,118	TSSOP16	Reel 13" Q1/T1 *standard mark SMD	2500	$T_{amb} = -40 ^{\circ}\text{C} \text{ to } +85 ^{\circ}\text{C}$


A9672 All information provided in this document is subject to legal disclaimers.

© NXP B.V. 2013. All rights reserved.

Remote 8-bit I/O expander for Fm+ I2C-bus with interrupt and reset

5. Block diagram






Remote 8-bit I/O expander for Fm+ I2C-bus with interrupt and reset

6. Pinning information

6.1 Pinning



6.2 Pin description

Table 3. Pin description

Symbol	Pin		Description					
	SO16, TSSOP16	HVQFN16						
AD0	1	15	address input 0					
AD1	2	16	address input 1					
RESET	3	1	reset input (active LOW)					
P0	4	2	quasi-bidirectional I/O 0					
P1	5	3	quasi-bidirectional I/O 1					
P2	6	4	quasi-bidirectional I/O 2					
P3	7	5	quasi-bidirectional I/O 3					
V _{SS}	8	6 ^[1]	supply ground					
P4	9	7	quasi-bidirectional I/O 4					
P5	10	8	quasi-bidirectional I/O 5					
P6	11	9	quasi-bidirectional I/O 6					

PCA9672

All information provided in this document is subject to legal disclaimers.

© NXP B.V. 2013. All rights reserved.

Remote 8-bit I/O expander for Fm+ I²C-bus with interrupt and reset

	Table 3.	Pin	description	continued
--	----------	-----	-------------	-----------

Symbol	Pin		Description
	SO16, TSSOP16	HVQFN16	
P7	12	10	quasi-bidirectional I/O 7
INT	13	11	interrupt output (active LOW)
SCL	14	12	serial clock line
SDA	15	13	serial data line
V_{DD}	16	14	supply voltage

^[1] HVQFN16 package die supply ground is connected to both the V_{SS} pin and the exposed center pad. The V_{SS} pin must be connected to supply ground for proper device operation. For enhanced thermal, electrical, and board-level performance, the exposed pad needs to be soldered to the board using a corresponding thermal pad on the board, and for proper heat conduction through the board thermal vias need to be incorporated in the PCB in the thermal pad region.

7. Functional description


Refer to Figure 1 "Block diagram of PCA9672".

7.1 Device address

Following a START condition, the bus master must send the address of the slave it is accessing and the operation it wants to perform (read or write). The address format of the PCA9672 is shown in Figure 6. Slave address pins AD1 and AD0 are used to choose one of 16 slave addresses. These devices can monitor the change in SDA or SCL in addition to the static levels of V_{DD} or V_{SS} to decode four states allowing a larger address range. To conserve power, no internal pull-up resistors are incorporated on AD1 or AD0, so they must be externally connected to V_{DD} , V_{SS} directly or through resistors, or to SCL or SDA directly. Address values depending on AD1 and AD0 can be found in Table 4 "PCA9672 address map".

Remark: When using the PCA9672 reserved I²C-bus addresses must be used with caution since they can interfere with:

- "reserved for future use" l²C-bus addresses (0000 011, 1111 101, 1111 110, 1111 111)
- slave devices that use the 10-bit addressing scheme (1111 0xx)
- High speed mode (Hs-mode) master code (0000 1xx)



The last bit of the first byte defines the operation to be performed. When set to logic 1 a read is selected, while a logic 0 selects a write operation.

When AD1 and AD0 are held to V_{DD} or V_{SS} , the same address as the PCF8574 or the newer PCA8574 with A2 held to V_{SS} is applied.

Remote 8-bit I/O expander for Fm+ I2C-bus with interrupt and reset

7.1.1 Address map


Table 4. PCA9672 address map

Pin conr	Pin connectivity		1	Addr	ess c	of PC	A967	' 2		Address byte value		7-bit
AD1	AD0	A6	A5	A4	A3	A2	A 1	A0	R/W	Write	Read	hexadecimal address_ without R/W
SCL	V_{SS}	0	0	1	0	0	0	0	-	20h	21h	10h
SCL	V_{DD}	0	0	1	0	0	0	1	-	22h	23h	11h
SDA	V_{SS}	0	0	1	0	0	1	0	-	24h	25h	12h
SDA	V_{DD}	0	0	1	0	0	1	1	-	26h	27h	13h
SCL	SCL	0	0	1	1	0	0	0	-	30h	31h	18h
SCL	SDA	0	0	1	1	0	0	1	-	32h	33h	19h
SDA	SCL	0	0	1	1	0	1	0	-	34h	35h	1Ah
SDA	SDA	0	0	1	1	0	1	1	-	36h	37h	1Bh
V_{SS}	V_{SS}	0	1	0	0	0	0	0	-	40h	41h	20h
V_{SS}	V_{DD}	0	1	0	0	0	0	1	-	42h	43h	21h
V_{DD}	V_{SS}	0	1	0	0	0	1	0	-	44h	45h	22h
V_{DD}	V_{DD}	0	1	0	0	0	1	1	-	46h	47h	23h
V_{SS}	SCL	0	1	0	1	0	0	0	-	50h	51h	28h
V _{SS}	SDA	0	1	0	1	0	0	1	-	52h	53h	29h
V_{DD}	SCL	0	1	0	1	0	1	0	-	54h	55h	2Ah
V_{DD}	SDA	0	1	0	1	0	1	1	-	56h	57h	2Bh

7.2 Software Reset Call, and device ID addresses

Two other different addresses can be sent to the PCA9672.

- General Call address: allows to reset the PCA9672 through the I²C-bus upon reception of the right I²C-bus sequence. See <u>Section 7.2.1 "Software Reset"</u> for more information.
- Device ID address: allows to read ID information from the device (manufacturer, part identification, revision). See <u>Section 7.2.2 "Device ID (PCA9672 ID field)"</u> for more information.



1 1 1 1 0 0 R/W
002aac116

Fig 8. Device ID address

Remote 8-bit I/O expander for Fm+ I²C-bus with interrupt and reset

7.2.1 Software Reset

The Software Reset Call allows all the devices in the I²C-bus to be reset to the power-up state value through a specific formatted I²C-bus command. To be performed correctly, it implies that the I²C-bus is functional and that there is no device hanging the bus.

The Software Reset sequence is defined as following:


- 1. A START command is sent by the I²C-bus master.
- 2. The reserved General Call I²C-bus address '0000 000' with the R/\overline{W} bit set to 0 (write) is sent by the I²C-bus master.
- 3. The PCA9672 device(s) acknowledge(s) after seeing the General Call address '0000 0000' (00h) only. If the R/W bit is set to 1 (read), no acknowledge is returned to the I²C-bus master.
- 4. Once the General Call address has been sent and acknowledged, the master sends 1 byte. The value of the byte must be equal to 06h.
 - a. The PCA9672 acknowledges this value only. If the byte is not equal to 06h, the PCA9672 does not acknowledge it.

If more than 1 byte of data is sent, the PCA9672 does not acknowledge any more.

5. Once the right byte has been sent and correctly acknowledged, the master sends a STOP command to end the Software Reset sequence: the PCA9672 then resets to the default value (power-up value) and is ready to be addressed again within the specified bus free time. If the master sends a Repeated START instead, no reset is performed.

The I²C-bus master must interpret a non-acknowledge from the PCA9672 (at any time) as a 'Software Reset Abort'. The PCA9672 does not initiate a reset of its registers.

The unique sequence that initiates a Software Reset is described in Figure 9.



Simple code for Software Reset:

<S> <00h> **<ACK>** <06h> **<ACK>** <P>

Remote 8-bit I/O expander for Fm+ I²C-bus with interrupt and reset

7.2.2 Device ID (PCA9672 ID field)

The Device ID field is a 3-byte read-only (24 bits) word giving the following information:

- 12 bits with the manufacturer name, unique per manufacturer (for example, NXP).
- 9 bits with the part identification, assigned by manufacturer.
- 3 bits with the die revision, assigned by manufacturer (for example, Rev X).

The Device ID is read-only, hardwired in the device and can be accessed as follows:

- 1. START command
- 2. The master sends the Reserved Device ID I²C-bus address '1111 100' with the R/W bit set to 0 (write).
- The master sends the I²C-bus slave address of the slave device it needs to identify.
 The LSB is a 'Don't care' value. Only one device must acknowledge this byte (the one that has the I²C-bus slave address).
- 4. The master sends a Re-START command.

Remark: A STOP command followed by a START command will reset the slave state machine and the Device ID read cannot be performed.


Remark: A STOP command or a Re-START command followed by an access to another slave device will reset the slave state machine and the Device ID read cannot be performed.

- 5. The master sends the Reserved Device ID I²C-bus address '1111 100' with the R/W bit set to 1 (read).
- 6. The device ID read can be done, starting with the 12 manufacturer bits (first byte + 4 MSB of the second byte), followed by the 9 part identification bits and then the 3 die revision bits (3 LSB of the third byte).
- 7. The master ends the reading sequence by NACKing the last byte, thus resetting the slave device state machine and allowing the master to send the STOP command.


Remark: The reading of the Device ID can be stopped anytime by sending a NACK command.

Remark: If the master continues to ACK the bytes after the third byte, the PCA9672 rolls back to the first byte and keeps sending the Device ID sequence until a NACK has been detected.

For the PCA9672, the Device ID is as shown in Figure 10.



Remote 8-bit I/O expander for Fm+ I2C-bus with interrupt and reset



Simple code for reading Device ID:

<S> <F8h> <ACK> <slave address> <ACK> <Sr> <F9h > <ACK> <DATA1> <ACK> <DATA2> <ACK> <DATA3> <NACK> <P>

8. I/O programming

8.1 Quasi-bidirectional I/Os

A quasi-bidirectional I/O is an input or output port without using a direction control register. Whenever the master reads the register, the value returned to master depends on the actual voltage or status of the pin. At power-on, all the ports are HIGH with a weak 100 μA internal pull-up to V_{DD} , but can be driven LOW by an internal transistor, or an external signal. The I/O ports are entirely independent of each other, but each I/O octal is controlled by the same read or write data byte.

Advantages of the quasi-bidirectional I/O over totem pole I/O include:

- Better for driving LEDs since the p-channel (transistor to V_{DD}) is small, which saves
 die size and therefore cost. LED drive only requires an internal transistor to ground,
 while the LED is connected to V_{DD} through a current-limiting resistor. Totem pole I/O
 have both n-channel and p-channel transistors, which allow solid HIGH and LOW
 output levels without a pull-up resistor good for logic levels.
- Simpler architecture only a single register and the I/O can be both input and output
 at the same time. Totem pole I/O have a direction register that specifies the port pin
 direction and it is always in that configuration unless the direction is explicitly
 changed.
- Does not require a command byte. The simplicity of one register (no need for the
 pointer register or, technically, the command byte) is an advantage in some
 embedded systems where every byte counts because of memory or bandwidth
 limitations.

PCA9672

Remote 8-bit I/O expander for Fm+ I²C-bus with interrupt and reset


There is only one register to control four possibilities of the port pin: Input HIGH, input LOW, output HIGH, or output LOW.

Input HIGH: The master needs to write 1 to the register to set the port as an input mode if the device is not in the default power-on condition. The master reads the register to check the input status. If the external source pulls the port pin up to V_{DD} or drives logic 1, then the master will read the value of 1.

Input LOW: The master needs to write 1 to the register to set the port to input mode if the device is not in the default power-on condition. The master reads the register to check the input status. If the external source pulls the port pin down to V_{SS} or drives logic 0, which sinks the weak 100 μ A current source, then the master will read the value of 0.

Output HIGH: The master writes 1 to the register. There is an additional 'accelerator' or strong pull-up current when the master sets the port HIGH. The additional strong pull-up is only active during the HIGH time of the acknowledge clock cycle. This accelerator current helps the port's 100 μ A current source make a faster rising edge into a heavily loaded output, but only at the start of the acknowledge clock cycle to avoid bus contention if an external signal is pulling the port LOW to V_{SS} /driving the port with logic 0 at the same time. After the half clock cycle there is only the 100 μ A current source to hold the port HIGH.

Output LOW: The master writes 0 to the register. There is a strong current sink transistor that holds the port pin LOW. A large current may flow into the port, which could potentially damage the part if the master writes a 0 to the register and an external source is pulling the port HIGH at the same time.




Remote 8-bit I/O expander for Fm+ I2C-bus with interrupt and reset

8.2 Writing to the port (Output mode)

The master (microcontroller) sends the START condition and slave address setting the last bit of the address byte to logic 0 for the write mode. The PCA9672 acknowledges and the master then sends the data byte for P7 to P0 to the port register. As the clock line goes HIGH, the 8-bit data is presented on the port lines after it has been acknowledged by the PCA9672. If a LOW is written, the strong pull-down turns on and stays on. If a HIGH is written, the strong pull-up turns on for $\frac{1}{2}$ of the clock cycle, then the line is held HIGH by the weak current source. The master can then send a STOP or ReSTART condition or continue sending data. The number of data bytes that can be sent successively is not limited and the previous data is overwritten every time a data byte has been sent and acknowledged.

Ensure a logic 1 is written for any port that is being used as an input to ensure the strong external pull-down is turned off.



Simple code for Write cycle:

<S> <slave address + W> <ACK> <DATA1> <ACK> <DATA2> <ACK> <DATA1> ... <DATAn> <ACK> <P>


Remote 8-bit I/O expander for Fm+ I²C-bus with interrupt and reset

8.3 Reading from a port (Input mode)

The port must have been previously written to logic 1, which is the condition after power-on reset or hardware reset or software reset. To enter the Read mode, the master (microcontroller) addresses the slave device and sets the last bit of the address byte to logic 1 (address byte read). The slave will acknowledge and then send the data byte to the master. The master will NACK and then send the STOP condition or ACK and read the input register again.

The read of any pin being used as an output will indicate HIGH or LOW depending on the actual state of the input pin.

If the data on the input port changes faster than the master can read, this data may be lost. The DATA 2 and DATA 3 are lost because these data did not meet the set-up time and hold time (see Figure 14).



Simple code for Read cycle:

<S> <slave address + R> <ACK> <DATA in> <ACK> <DATA in> ... <NACK> <P>

8.4 Power-on reset

Fig 14. Read input port register

When power is applied to V_{DD} , an internal Power-On Reset (POR) holds the PCA9672 in a reset condition until V_{DD} has reached V_{POR} . At that point, the reset condition is released and the PCA9672 registers and I^2C -bus/SMBus state machine will initialize to their default states of all I/Os to inputs with weak current source to V_{DD} . Thereafter V_{DD} must be lowered below V_{POR} and back up to the operation voltage for power-on reset cycle.

Remote 8-bit I/O expander for Fm+ I²C-bus with interrupt and reset

8.5 Interrupt output (INT)

The PCA9672 provides an open-drain output ($\overline{\text{INT}}$) which can be fed to a corresponding input of the microcontroller (see <u>Figure 15</u>). As soon as a port input is changed, the $\overline{\text{INT}}$ will be active (LOW) and notify the microcontroller.

An interrupt is generated at any rising or falling edge of the port inputs. After time $t_{V(Q)}$, the signal \overline{INT} is valid.


The interrupt will reset to HIGH when data on the port is changed to the original setting or data is read or written by the master.

In the Write mode, the interrupt may be reset (HIGH) on the rising edge of the acknowledge bit of the data byte and also on the rising edge of the write to port pulse. The interrupt will always be reset (HIGH) on the falling edge of the write to port pulse (see Figure 13).

The interrupt is reset (HIGH) in the rising edge of the read from port pulse (see Figure 14).

During the interrupt reset, any I/O change close to the read or write pulse may not generate an interrupt, or the interrupt will have a very short pulse. After the interrupt is reset, any change in I/Os will be detected and transmitted as an INT.

At power-on reset all ports are in Input mode and the initial state of the ports is HIGH, therefore, for any port pin that is pulled LOW or driven LOW by external source, the interrupt output will be active (output LOW).



8.6 RESET input

A reset can be accomplished by holding the \overline{RESET} pin LOW for a minimum of $t_{w(rst)}$. The PCA9672 registers and I²C-bus state machine will be held in their default state until the RESET input is once again HIGH. The RESET input pin requires a pull-up resistor to V_{DD} if no active connection is used.


Remote 8-bit I/O expander for Fm+ I²C-bus with interrupt and reset

9. Characteristics of the I²C-bus

The I^2C -bus is for 2-way, 2-line communication between different ICs or modules. The two lines are a serial data line (SDA) and a serial clock line (SCL). Both lines must be connected to a positive supply via a pull-up resistor when connected to the output stages of a device. Data transfer may be initiated only when the bus is not busy.


9.1 Bit transfer

One data bit is transferred during each clock pulse. The data on the SDA line must remain stable during the HIGH period of the clock pulse as changes in the data line at this time will be interpreted as control signals (see Figure 16).



9.1.1 START and STOP conditions


Both data and clock lines remain HIGH when the bus is not busy. A HIGH-to-LOW transition of the data line while the clock is HIGH is defined as the START condition (S). A LOW-to-HIGH transition of the data line while the clock is HIGH is defined as the STOP condition (P) (see Figure 17.)



9.2 System configuration

A device generating a message is a 'transmitter'; a device receiving is the 'receiver'. The device that controls the message is the 'master' and the devices which are controlled by the master are the 'slaves' (see Figure 18).

Remote 8-bit I/O expander for Fm+ I²C-bus with interrupt and reset




9.3 Acknowledge

The number of data bytes transferred between the START and the STOP conditions from transmitter to receiver is not limited. Each byte of eight bits is followed by one acknowledge bit. The acknowledge bit is an active LOW level (generated by the receiving device) that indicates to the transmitter that the data transfer was successful.

A slave receiver which is addressed must generate an acknowledge after the reception of each byte. Also a master must generate an acknowledge after the reception of each byte that has been clocked out of the slave transmitter. The device that wants to issue an acknowledge bit has to pull down the SDA line during the acknowledge clock pulse, so that the SDA line is stable LOW during the HIGH period of the acknowledge bit related clock pulse; set-up and hold times must be taken into account.

A master receiver must signal an end of data to the transmitter by **not** generating an acknowledge on the last byte that has been clocked out of the slave. In this event, the transmitter must leave the data line HIGH to enable the master to generate a STOP condition.



Remote 8-bit I/O expander for Fm+ I2C-bus with interrupt and reset


10. Application design-in information

10.1 Bidirectional I/O expander applications

In the 8-bit I/O expander application shown in Figure 20, P0 and P1 are inputs, and P2 to P7 are outputs. When used in this configuration, during a write, the input (P0 and P1) must be written as HIGH so the external devices fully control the input ports. The desired HIGH or LOW logic levels may be written to the I/Os used as outputs (P2 to P7). If 10 μ A internal output HIGH is not enough current source, the port needs external pull-up resistor. During a read, the logic levels of the external devices driving the input ports (P0 and P1) and the previous written logic level to the output ports (P2 to P7) will be read.

The GPIO also has an interrupt line $(\overline{\text{INT}})$ that can be connected to the interrupt logic of the microprocessor. By sending an interrupt signal on this line, the remote I/O informs the microprocessor that there has been a change of data on its ports without having to communicate via the I²C-bus.

The GPIO also has a reset line (\overline{RESET}) that can be connected to an output pin of the microcontroller.



10.2 How to read and write to I/O expander (example)

In the application example of PCA9672 shown in <u>Figure 20</u>, the microcontroller wants to control the P3 switch ON and the P7 LED ON when the temperature sensor P0 changes.

1. When the system power on:

Core Processor needs to issue an initial command to set P0 and P1 as inputs and P[7:2] as outputs with value 1010 00 (LED off, MP3 off, camera on, audio off, switch off and latch off).

2. Operation:

When the temperature changes above the threshold, the temperature sensor signal will toggle from HIGH to LOW. The $\overline{\text{INT}}$ will be activated and notifies the 'core processor', that there have been changes on the input pins. Read the input register. If P0 = 0 (temperature sensor has changed), then turn on LED and turn on switch.


Remote 8-bit I/O expander for Fm+ I²C-bus with interrupt and reset

3. Software code:

```
//System Power on
// write to PCA9672 with data 1010 0011b to set P[7:2] outputs and P[1:0] inputs
<S> <0100 0000> <ACK> <1010 0011> <ACK> <P>//Initial setting for PCA9672
while (INT == 1); //Monitor the interrupt pin. If INT = 1 do nothing
//When INT = 0 then read input ports
<S> <slave address read> <ACK> <1010 0010> <NACK> <P> //Read PCA9672 data
If (P0 == 0) //Temperature sensor activated
{
// write to PCA9672 with data 0010 1011b to turn on LED (P7), on Switch (P3)
and keep P[1:0] as input ports.
<S> <0100 0000> <ACK> <0010 1011> <ACK> <P> // Write to PCA9672
}
```

10.3 High current-drive load applications

The GPIO has a minimum guaranteed sinking current of 25 mA per bit at 5 V. In applications requiring additional drive, two port pins may be connected together to sink up to 50 mA current. Both bits must then always be turned on or off together. Up to 8 pins can be connected together to drive 200 mA, which is the device recommended total limit. Each pin needs its own limiting resistor as shown in Figure 21 to prevent damage to the device should all ports not be turned on at the same time.



10.4 Migration path

NXP offers newer, more capable drop-in replacements for the PCF8574/74A in newer space-saving packages.

Table 5. Migration path

Type number	I ² C-bus frequency	Voltage range	Number of addresses per device	Interrupt	Reset	Total package sink current
PCF8574/74A	100 kHz	2.5 V to 6 V	8	yes	no	80 mA
PCA8574/74A	400 kHz	2.3 V to 5.5 V	8	yes	no	200 mA
PCA9674/74A	1 MHz Fm+	2.3 V to 5.5 V	64	yes	no	200 mA
PCA9670	1 MHz Fm+	2.3 V to 5.5 V	64	no	yes	200 mA
PCA9672	1 MHz Fm+	2.3 V to 5.5 V	16	yes	yes	200 mA

PCA9672 All information provided in this document is subject to legal disclaimers. © NXP B.V. 2013. All rights reserved.

Remote 8-bit I/O expander for Fm+ I²C-bus with interrupt and reset

PCA9670 replaces the interrupt output of the PCA9674 with hardware reset input to retain the maximum number of addresses. The PCA9672 replaces address A2 of the PCA9674 with hardware reset input to retain the interrupt, but limit the number of addresses.

11. Limiting values

Table 6. Limiting values

In accordance with the Absolute Maximum Rating System (IEC 60134).

Symbol	Parameter	Conditions	Min	Max	Unit
V_{DD}	supply voltage		-0.5	+6	V
I_{DD}	supply current		-	±100	mA
I_{SS}	ground supply current		-	±400	mA
VI	input voltage		$V_{\text{SS}}-0.5$	5.5	V
I _I	input current		-	±20	mA
Io	output current		<u>[1]</u> _	±50	mA
P _{tot}	total power dissipation		-	400	mW
P/out	power dissipation per output		-	100	mW
T _{j(max)}	maximum junction temperature		-	125	°C
T _{stg}	storage temperature		–65	+150	°C
T _{amb}	ambient temperature	operating	-40	+85	°C

^[1] Total package (maximum) output current is 400 mA.

12. Thermal characteristics

Table 7. Thermal characteristics

Symbol	Parameter	Conditions	Тур	Unit
$R_{th(j-a)}$	thermal resistance from junction	SO16 package	115	°C/W
	to ambient	TSSOP16 package	160	°C/W
		HVQFN16 package	40	°C/W

Remote 8-bit I/O expander for Fm+ I²C-bus with interrupt and reset

13. Static characteristics

Table 8. Static characteristics

 V_{DD} = 2.3 V to 5.5 V; V_{SS} = 0 V; T_{amb} = -40 °C to +85 °C; unless otherwise specified.

Symbol	Parameter	Conditions		Min	Тур	Max	Unit
Supplies							
V_{DD}	supply voltage			2.3	-	5.5	V
I _{DD}	supply current	Operating mode; no load; $V_I = V_{DD}$ or V_{SS} ; $f_{SCL} = 1$ MHz; AD0, AD1 = static H or L		-	260	500	μА
I _{stb}	standby current	Standby mode; no load; $V_I = V_{DD}$ or V_{SS} ; $f_{SCL} = 0$ kHz		-	2.5	10	μΑ
V_{POR}	power-on reset voltage		<u>[1]</u>	-	1.8	2.0	V
Input SCI	_; input/output SDA						
V_{IL}	LOW-level input voltage			-0.5	-	$+0.3V_{DD}$	V
V_{IH}	HIGH-level input voltage			$0.7V_{DD}$	-	5.5	V
I_{OL}	LOW-level output current	$V_{OL} = 0.4 \text{ V}; V_{DD} = 2.3 \text{ V}$		20	-	-	mA
		$V_{OL} = 0.4 \text{ V}; V_{DD} = 3.0 \text{ V}$		25	-	-	mA
		$V_{OL} = 0.4 \text{ V}; V_{DD} = 4.5 \text{ V}$		30	-	-	mA
IL	leakage current	$V_I = V_{DD}$ or V_{SS}		-1	-	+1	μΑ
Ci	input capacitance	$V_I = V_{SS}$		-	4	10	pF
I/Os; P0 t	o P7						
V_{IL}	LOW-level input voltage			-0.5	-	$+0.3V_{DD}$	V
V_{IH}	HIGH-level input voltage			$0.7V_{DD}$	-	5.5	V
I _{OL}	LOW-level output current	$V_{OL} = 0.5 \text{ V}; V_{DD} = 2.3 \text{ V}$	[2]	12	28	-	mA
		$V_{OL} = 0.5 \text{ V}; V_{DD} = 3.0 \text{ V}$	[2]	17	35	-	mA
		V _{OL} = 0.5 V; V _{DD} = 4.5 V	[2]	25	43	-	mΑ
I _{OL(tot)}	total LOW-level output current	$V_{OL} = 0.5 \text{ V}; V_{DD} = 4.5 \text{ V}$	[2]	-	-	200	mA
I _{OH}	HIGH-level output current	V _{OH} = V _{SS}		-30	-250	-300	μΑ
I _{trt(pu)}	transient boosted pull-up current	V _{OH} = V _{SS} ; see <u>Figure 13</u>		-0.5	-1.0	-	mA
Ci	input capacitance		[3]	-	3	10	pF
Co	output capacitance		[3]	-	3	10	pF
Input RES	SET						
V_{IL}	LOW-level input voltage			-0.5	-	+0.8	V
V_{IH}	HIGH-level input voltage			2	-	5.5	V
ILI	input leakage current			-1	-	+1	μΑ
C _i	input capacitance			-	3	5	pF
Interrupt	INT (see <u>Figure 13</u> and <u>Figure 14</u>)					
I _{OL}	LOW-level output current	V _{OL} = 0.4 V		3.0	-	-	mA
C _o	output capacitance			-	2	5	pF

Remote 8-bit I/O expander for Fm+ I²C-bus with interrupt and reset

Table 8. Static characteristics ... continued

 V_{DD} = 2.3 V to 5.5 V; V_{SS} = 0 V; T_{amb} = -40 °C to +85 °C; unless otherwise specified.

Symbol	Parameter	Conditions	Min	Тур	Max	Unit
Inputs Al	00, AD1					
V_{IL}	LOW-level input voltage		-0.5	-	+0.3V _{DD}	V
V_{IH}	HIGH-level input voltage		$0.7V_{DD}$	-	5.5	V
ILI	input leakage current		-1	-	+1	μΑ
Ci	input capacitance		-	3	5	pF

^[1] The power-on reset circuit resets the I^2C -bus logic with $V_{DD} < V_{POR}$ and set all I/Os to logic 1 (with current source to V_{DD}).

14. Dynamic characteristics

Table 9. Dynamic characteristics

 V_{DD} = 2.3 V to 5.5 V; V_{SS} = 0 V; T_{amb} = -40 °C to +85 °C; unless otherwise specified.

Symbol	Parameter	Conditions		rd mode ·bus	Fast mode I ²	Fast mo	Unit		
			Min	Max	Min	Max	Min	Max	
f_{SCL}	SCL clock frequency		0	100	0	400	0	1000	kHz
t _{BUF}	bus free time between a STOP and START condition		4.7	-	1.3	-	0.5	-	μS
t _{HD;STA}	hold time (repeated) START condition		4.0	-	0.6	-	0.26	-	μS
t _{SU;STA}	set-up time for a repeated START condition		4.7	-	0.6	-	0.26	-	μS
t _{SU;STO}	set-up time for STOP condition		4.0	-	0.6	-	0.26	-	μS
t _{HD;DAT}	data hold time		0	-	0	-	0	-	ns
t _{VD;ACK}	data valid acknowledge time	[1]	0.3	3.45	0.1	0.9	0.05	0.45	μS
t _{VD;DAT}	data valid time	[2]	300	-	50	-	50	450	ns
t _{SU;DAT}	data set-up time		250	-	100	-	50	-	ns
t_{LOW}	LOW period of the SCL clock		4.7	-	1.3	-	0.5	-	μS
t _{HIGH}	HIGH period of the SCL clock		4.0	-	0.6	-	0.26	-	μS
t _f	fall time of both SDA and SCL signals	<u>[4][5]</u>	-	300	20 + 0.1C _b [3]	300	-	120	ns
t _r	rise time of both SDA and SCL signals		-	1000	20 + 0.1C _b [3]	300	-	120	ns
t _{SP}	pulse width of spikes that must be suppressed by the input filter	<u>[6]</u>	-	50	-	50	-	50	ns

^[2] Each bit must be limited to a maximum of 25 mA and the total package limited to 200 mA due to internal busing limits.

^[3] The value is not tested, but verified on sampling basis.


Remote 8-bit I/O expander for Fm+ I²C-bus with interrupt and reset

 Table 9.
 Dynamic characteristics ...continued


 V_{DD} = 2.3 V to 5.5 V; V_{SS} = 0 V; T_{amb} = -40 °C to +85 °C; unless otherwise specified.

Symbol	Parameter	Conditions	Standard mode I ² C-bus		Fast mode I ² C-bus		Fast mode Plus I ² C-bus		Unit
			Min	Max	Min	Max	Min	Max	
Port timi	ng; C _L ≤ 100 pF (see <u>Figu</u>	<u>re 13</u> and <u>Figure 14</u>)		'		'		•	
$t_{v(Q)}$	data output valid time		-	4	-	4	-	4	μS
t _{su(D)}	data input set-up time		0	-	0	-	0	-	μS
t _{h(D)}	data input hold time		4	-	4	-	4	-	μS
Interrupt	timing; $C_L \le 100 \text{ pF}$ (see	Figure 13 and Figure	e 14)						
$t_{v(INT)}$	valid time on pin INT	fro <u>m p</u> ort to INT	-	4	-	4	-	4	μS
t _{rst(INT)}	reset time on pin INT	from SCL to INT	-	4	-	4	-	4	μS
Reset tin	ning (see <u>Figure 23</u>)								
t _{w(rst)}	reset pulse width		4	-	4	-	4	-	μS
t _{rec(rst)}	reset recovery time		0	-	0	-	0	-	μS
t _{rst}	reset time		100	-	100	-	100	-	μS

- [1] $t_{VD;ACK}$ = time for Acknowledgement signal from SCL LOW to SDA (out) LOW.
- [2] $t_{VD:DAT}$ = minimum time for SDA data out to be valid following SCL LOW.
- [3] $C_b = \text{total capacitance of one bus line in pF.}$
- [4] A master device must internally provide a hold time of at least 300 ns for the SDA signal (refer to the V_{IL} of the SCL signal) in order to bridge the undefined region SCL's falling edge.
- [5] The maximum t_f for the SDA and SCL bus lines is specified at 300 ns. The maximum fall time for the SDA output stage t_f is specified at 250 ns. This allows series protection resistors to be connected between the SDA and the SCL pins and the SDA/SCL bus lines without exceeding the maximum specified t_f.
- [6] Input filters on the SDA and SCL inputs suppress noise spikes less than 50 ns.



Remote 8-bit I/O expander for Fm+ I²C-bus with interrupt and reset



Remote 8-bit I/O expander for Fm+ I²C-bus with interrupt and reset

15. Package outline

HVQFN16: plastic thermal enhanced very thin quad flat package; no leads; 16 terminals; body $3 \times 3 \times 0.85$ mm

SOT758-1




Fig 24. Package outline SOT758-1 (HVQFN16)


A9672 All information provided in this document is subject to legal disclaimers.

© NXP B.V. 2013. All rights reserved.

Remote 8-bit I/O expander for Fm+ I²C-bus with interrupt and reset

SO16: plastic small outline package; 16 leads; body width 7.5 mm

SOT162-1



Note

1. Plastic or metal protrusions of 0.15 mm (0.006 inch) maximum per side are not included.

OUTLINE		REFER	ENCES	EUROPEAN	ISSUE DATE	
VERSION	IEC	JEDEC	JEITA	PROJECTION	ISSUE DATE	
SOT162-1	075E03	MS-013			-99-12-27 03-02-19	

Fig 25. Package outline SOT162-1 (SO16)

PCA9672

All information provided in this document is subject to legal disclaimers.


© NXP B.V. 2013. All rights reserved.

PCA9672 NXP Semiconductors

Remote 8-bit I/O expander for Fm+ I²C-bus with interrupt and reset

TSSOP16: plastic thin shrink small outline package; 16 leads; body width 4.4 mm

SOT403-1



UNIT	A max.	A ₁	A ₂	A ₃	bp	С	D ⁽¹⁾	E (2)	е	HE	L	Lp	Q	v	w	у	Z ⁽¹⁾	θ
mm	1.1	0.15 0.05	0.95 0.80	0.25	0.30 0.19	0.2 0.1	5.1 4.9	4.5 4.3	0.65	6.6 6.2	1	0.75 0.50	0.4 0.3	0.2	0.13	0.1	0.40 0.06	8° 0°

- 1. Plastic or metal protrusions of 0.15 mm maximum per side are not included.
- 2. Plastic interlead protrusions of 0.25 mm maximum per side are not included.

OUTLINE		REFER	EUROPEAN	ISSUE DATE			
VERSION	IEC	JEDEC	JEITA		PROJECTION	ISSUE DATE	
SOT403-1		MO-153				99-12-27 03-02-18	
501403-1		IVIO-153				<u> </u>	

Fig 26. Package outline SOT403-1 (TSSOP16)

Remote 8-bit I/O expander for Fm+ I²C-bus with interrupt and reset

16. Handling information

All input and output pins are protected against ElectroStatic Discharge (ESD) under normal handling. When handling ensure that the appropriate precautions are taken as described in *JESD625-A* or equivalent standards.

17. Soldering of SMD packages

This text provides a very brief insight into a complex technology. A more in-depth account of soldering ICs can be found in Application Note *AN10365* "Surface mount reflow soldering description".

17.1 Introduction to soldering

Soldering is one of the most common methods through which packages are attached to Printed Circuit Boards (PCBs), to form electrical circuits. The soldered joint provides both the mechanical and the electrical connection. There is no single soldering method that is ideal for all IC packages. Wave soldering is often preferred when through-hole and Surface Mount Devices (SMDs) are mixed on one printed wiring board; however, it is not suitable for fine pitch SMDs. Reflow soldering is ideal for the small pitches and high densities that come with increased miniaturization.

17.2 Wave and reflow soldering

Wave soldering is a joining technology in which the joints are made by solder coming from a standing wave of liquid solder. The wave soldering process is suitable for the following:

- Through-hole components
- Leaded or leadless SMDs, which are glued to the surface of the printed circuit board

Not all SMDs can be wave soldered. Packages with solder balls, and some leadless packages which have solder lands underneath the body, cannot be wave soldered. Also, leaded SMDs with leads having a pitch smaller than ~0.6 mm cannot be wave soldered, due to an increased probability of bridging.

The reflow soldering process involves applying solder paste to a board, followed by component placement and exposure to a temperature profile. Leaded packages, packages with solder balls, and leadless packages are all reflow solderable.

Key characteristics in both wave and reflow soldering are:

- Board specifications, including the board finish, solder masks and vias
- Package footprints, including solder thieves and orientation
- The moisture sensitivity level of the packages
- Package placement
- Inspection and repair
- Lead-free soldering versus SnPb soldering

17.3 Wave soldering

Key characteristics in wave soldering are:

PCA9672

Remote 8-bit I/O expander for Fm+ I²C-bus with interrupt and reset

- Process issues, such as application of adhesive and flux, clinching of leads, board transport, the solder wave parameters, and the time during which components are exposed to the wave
- Solder bath specifications, including temperature and impurities

17.4 Reflow soldering

Key characteristics in reflow soldering are:

- Lead-free versus SnPb soldering; note that a lead-free reflow process usually leads to higher minimum peak temperatures (see <u>Figure 27</u>) than a SnPb process, thus reducing the process window
- Solder paste printing issues including smearing, release, and adjusting the process window for a mix of large and small components on one board
- Reflow temperature profile; this profile includes preheat, reflow (in which the board is heated to the peak temperature) and cooling down. It is imperative that the peak temperature is high enough for the solder to make reliable solder joints (a solder paste characteristic). In addition, the peak temperature must be low enough that the packages and/or boards are not damaged. The peak temperature of the package depends on package thickness and volume and is classified in accordance with Table 10 and 11

Table 10. SnPb eutectic process (from J-STD-020D)

Package thickness (mm)	Package reflow temperature (°C)		
	Volume (mm³)			
	< 350	≥ 350		
< 2.5	235	220		
≥ 2.5	220	220		


Table 11. Lead-free process (from J-STD-020D)

Package thickness (mm)	Package reflow temperature (°C) Volume (mm³)					
	< 350	350 to 2000	> 2000			
< 1.6	260	260	260			
1.6 to 2.5	260	250	245			
> 2.5	250	245	245			

Moisture sensitivity precautions, as indicated on the packing, must be respected at all times.

Studies have shown that small packages reach higher temperatures during reflow soldering, see Figure 27.

Remote 8-bit I/O expander for Fm+ I²C-bus with interrupt and reset



For further information on temperature profiles, refer to Application Note *AN10365* "Surface mount reflow soldering description".

Remote 8-bit I/O expander for Fm+ I2C-bus with interrupt and reset

18. Soldering: PCB footprints




Fig 28. PCB footprint for SOT758-1 (HVQFN16); reflow soldering

PCA9672 All information provided in this document is subject to legal disclaimers.

© NXP B.V. 2013. All rights reserved.

Remote 8-bit I/O expander for Fm+ I²C-bus with interrupt and reset




Fig 29. PCB footprint for SOT162-1 (SO16); reflow soldering

Remote 8-bit I/O expander for Fm+ I²C-bus with interrupt and reset




Fig 30. PCB footprint for SOT403-1 (TSSOP16); reflow soldering

Remote 8-bit I/O expander for Fm+ I²C-bus with interrupt and reset

19. Abbreviations

Table 12. Abbreviations

Tubic 12. Abb	Teviations
Acronym	Description
CDM	Charged Device Model
CMOS	Complementary Metal Oxide Semiconductor
ESD	ElectroStatic Discharge
GPIO	General Purpose Input/Output
НВМ	Human Body Model
LED	Light Emitting Diode
IC	Integrated Circuit
I ² C-bus	Inter IC bus
ID	Identification
LSB	Least Significant Bit
MM	Machine Model
MSB	Most Significant Bit
PLC	Programmable Logic Controller
PWM	Pulse Width Modulation
RAID	Redundant Array of Independent Disks
·	

20. Revision history

Table 13. Revision history

Document ID	Release date	Data sheet status	Change notice	Supersedes
PCA9672 v.3	20130527	Product data sheet	-	PCA9672 v.2

Modifications:

- Section 1 "General description" re-written
- Section 2 "Features and benefits" re-written
- Section 3 "Applications":
 - added (new) third bullet item "Keypads"
 - added (new) eighth bullet item "Mobile devices"
- Added Section 4.1 "Ordering options"
- Figure 1 "Block diagram of PCA9672" modified: switched positions of blocks "INTERRUPT LOGIC" and "LP FILTER"
- <u>Figure 2 "Simplified schematic diagram of P0 to P7"</u> modified: removed diode between "V_{DD}" and "P0 to P7" signals
- Section 7.1 "Device address":
 - first paragraph re-written
 - fourth paragraph: inserted phrase "or the newer PCA8574"
- Section 7.2.1 "Software Reset": added paragraph following Figure 9

Remote 8-bit I/O expander for Fm+ I²C-bus with interrupt and reset

Table 13. Revision history ... continued **Document ID** Release date Data sheet status Change notice Supersedes Modifications: Section 7.2.2 "Device ID (PCA9672 ID field)": (continued) first bullet item following first paragraph changed from "8 bits with the manufacturer name" to "12 bits with the manufacturer name" second bullet item following first paragraph re-written List item 6, on page 8 changed from "starting with the 8 manufacturer bits ..., followed by the 13 part identification bits" to "starting with the 12 manufacturer bits ..., followed by the 9 part identification bits" Figure 10 "PCA9672 Device ID field" updated Figure 11 modified: added "Sr" bit (ReSTART condition) added paragraph following Figure 11 Section 8.1 "Quasi-bidirectional I/Os" re-written Section 8.2 "Writing to the port (Output mode)" re-written Section 8.3 "Reading from a port (Input mode)" re-written Section 8.4 "Power-on reset": second and third sentences re-written Section 8.5 "Interrupt output (INT)": fourth, fifth and sixth paragraphs re-written; added (new) seventh Section 8.6 "RESET input": added (new) third sentence Section 9.3 "Acknowledge": - first paragraph, third sentence re-written - second paragraph, third sentence re-written Section 10.1 "Bidirectional I/O expander applications": - second paragraph: second sentence changed from "there is incoming data or a change of data" to "there has been a change of data" added (new) third paragraph Added Section 10.2 "How to read and write to I/O expander (example)" Section 10.3 "High current-drive load applications": - first sentence changed from "maximum sinking current of 25 mA per bit" to "minimum guaranteed sinking current of 25 mA per bit at 5 V" deleted phrase "in the same octal" from second sentence appended phrase "which is the device recommended total limit" to fourth sentence - added (new) fifth sentence - Figure 21 "High current-drive load application" modified: added resistors on P6 and P7 signals Added Section 10.4 "Migration path" <u>Table 6 "Limiting values"</u>: added T_{i(max)} limits Added Section 12 "Thermal characteristics" Table 8 "Static characteristics": - sub-section "I/Os; P0 to P7": added V_{IL} characteristic - sub-section "I/Os; P0 to P7": added VIH characteristic sub-section "Input RESET" is corrected by removing I_{OH} row Table 9 "Dynamic characteristics", sub-section "Interrupt timing": symbol/parameter changed from "t_{v(D)}, data input valid time" to "t_{v(INT)}, valid time on pin INT" symbol/parameter changed from t_{d(rst)}, reset delay time" to "t_{rst(INT)}, reset time on pin INT" Added Section 18 "Soldering: PCB footprints"

 PCA9672 v.2
 20070706
 Product data sheet
 PCA9672 v.1

 PCA9672 v.1
 20060620
 Objective data sheet

Remote 8-bit I/O expander for Fm+ I²C-bus with interrupt and reset

21. Legal information

21.1 Data sheet status

Document status[1][2]	Product status[3]	Definition
Objective [short] data sheet	Development	This document contains data from the objective specification for product development.
Preliminary [short] data sheet	Qualification	This document contains data from the preliminary specification.
Product [short] data sheet	Production	This document contains the product specification.

- [1] Please consult the most recently issued document before initiating or completing a design.
- [2] The term 'short data sheet' is explained in section "Definitions"
- [3] The product status of device(s) described in this document may have changed since this document was published and may differ in case of multiple devices. The latest product status information is available on the Internet at URL http://www.nxp.com.

21.2 Definitions

Draft — The document is a draft version only. The content is still under internal review and subject to formal approval, which may result in modifications or additions. NXP Semiconductors does not give any representations or warranties as to the accuracy or completeness of information included herein and shall have no liability for the consequences of use of such information.

Short data sheet — A short data sheet is an extract from a full data sheet with the same product type number(s) and title. A short data sheet is intended for quick reference only and should not be relied upon to contain detailed and full information. For detailed and full information see the relevant full data sheet, which is available on request via the local NXP Semiconductors sales office. In case of any inconsistency or conflict with the short data sheet, the full data sheet shall prevail.

Product specification — The information and data provided in a Product data sheet shall define the specification of the product as agreed between NXP Semiconductors and its customer, unless NXP Semiconductors and customer have explicitly agreed otherwise in writing. In no event however, shall an agreement be valid in which the NXP Semiconductors product is deemed to offer functions and qualities beyond those described in the Product data sheet.

21.3 Disclaimers

Limited warranty and liability — Information in this document is believed to be accurate and reliable. However, NXP Semiconductors does not give any representations or warranties, expressed or implied, as to the accuracy or completeness of such information and shall have no liability for the consequences of use of such information. NXP Semiconductors takes no responsibility for the content in this document if provided by an information source outside of NXP Semiconductors.

In no event shall NXP Semiconductors be liable for any indirect, incidental, punitive, special or consequential damages (including - without limitation - lost profits, lost savings, business interruption, costs related to the removal or replacement of any products or rework charges) whether or not such damages are based on tort (including negligence), warranty, breach of contract or any other legal theory.

Notwithstanding any damages that customer might incur for any reason whatsoever, NXP Semiconductors' aggregate and cumulative liability towards customer for the products described herein shall be limited in accordance with the *Terms and conditions of commercial sale* of NXP Semiconductors.

Right to make changes — NXP Semiconductors reserves the right to make changes to information published in this document, including without limitation specifications and product descriptions, at any time and without notice. This document supersedes and replaces all information supplied prior to the publication hereof.

Suitability for use — NXP Semiconductors products are not designed, authorized or warranted to be suitable for use in life support, life-critical or safety-critical systems or equipment, nor in applications where failure or malfunction of an NXP Semiconductors product can reasonably be expected to result in personal injury, death or severe property or environmental damage. NXP Semiconductors and its suppliers accept no liability for inclusion and/or use of NXP Semiconductors products in such equipment or applications and therefore such inclusion and/or use is at the customer's own risk.

Applications — Applications that are described herein for any of these products are for illustrative purposes only. NXP Semiconductors makes no representation or warranty that such applications will be suitable for the specified use without further testing or modification.

Customers are responsible for the design and operation of their applications and products using NXP Semiconductors products, and NXP Semiconductors accepts no liability for any assistance with applications or customer product design. It is customer's sole responsibility to determine whether the NXP Semiconductors product is suitable and fit for the customer's applications and products planned, as well as for the planned application and use of customer's third party customer(s). Customers should provide appropriate design and operating safeguards to minimize the risks associated with their applications and products.

NXP Semiconductors does not accept any liability related to any default, damage, costs or problem which is based on any weakness or default in the customer's applications or products, or the application or use by customer's third party customer(s). Customer is responsible for doing all necessary testing for the customer's applications and products using NXP Semiconductors products in order to avoid a default of the applications and the products or of the application or use by customer's third party customer(s). NXP does not accept any liability in this respect.

Limiting values — Stress above one or more limiting values (as defined in the Absolute Maximum Ratings System of IEC 60134) will cause permanent damage to the device. Limiting values are stress ratings only and (proper) operation of the device at these or any other conditions above those given in the Recommended operating conditions section (if present) or the Characteristics sections of this document is not warranted. Constant or repeated exposure to limiting values will permanently and irreversibly affect the quality and reliability of the device.

Terms and conditions of commercial sale — NXP Semiconductors products are sold subject to the general terms and conditions of commercial sale, as published at http://www.nxp.com/profile/terms, unless otherwise agreed in a valid written individual agreement. In case an individual agreement is concluded only the terms and conditions of the respective agreement shall apply. NXP Semiconductors hereby expressly objects to applying the customer's general terms and conditions with regard to the purchase of NXP Semiconductors products by customer.

No offer to sell or license — Nothing in this document may be interpreted or construed as an offer to sell products that is open for acceptance or the grant, conveyance or implication of any license under any copyrights, patents or other industrial or intellectual property rights.

PCA9672

Remote 8-bit I/O expander for Fm+ I2C-bus with interrupt and reset

Export control — This document as well as the item(s) described herein may be subject to export control regulations. Export might require a prior authorization from competent authorities.

Non-automotive qualified products — Unless this data sheet expressly states that this specific NXP Semiconductors product is automotive qualified, the product is not suitable for automotive use. It is neither qualified nor tested in accordance with automotive testing or application requirements. NXP Semiconductors accepts no liability for inclusion and/or use of non-automotive qualified products in automotive equipment or applications.

In the event that customer uses the product for design-in and use in automotive applications to automotive specifications and standards, customer (a) shall use the product without NXP Semiconductors' warranty of the product for such automotive applications, use and specifications, and (b) whenever customer uses the product for automotive applications beyond NXP Semiconductors' specifications such use shall be solely at customer's

own risk, and (c) customer fully indemnifies NXP Semiconductors for any liability, damages or failed product claims resulting from customer design and use of the product for automotive applications beyond NXP Semiconductors' standard warranty and NXP Semiconductors' product specifications.

Translations — A non-English (translated) version of a document is for reference only. The English version shall prevail in case of any discrepancy between the translated and English versions.

21.4 Trademarks

Notice: All referenced brands, product names, service names and trademarks are the property of their respective owners.

I²C-bus — logo is a trademark of NXP B.V.

22. Contact information

For more information, please visit: http://www.nxp.com

For sales office addresses, please send an email to: salesaddresses@nxp.com

18

19 20 21 21.1 21.2 21.3 21.4 22 23

Remote 8-bit I/O expander for Fm+ I2C-bus with interrupt and reset

23. Contents

1	General description	
2	Features and benefits	
3	Applications	
4	Ordering information	2
4.1	Ordering options	2
5	Block diagram	3
6	Pinning information	4
6.1	Pinning	4
6.2	Pin description	4
7	Functional description	5
7.1	Device address	5
7.1.1	Address map	6
7.2	Software Reset Call, and device ID addresses	6
7.2.1	Software Reset	7
7.2.2	Device ID (PCA9672 ID field)	8
8	I/O programming	9
8.1	Quasi-bidirectional I/Os	
8.2	. 3	11
8.3	3	12
8.4 8.5		12 13
8.6		13
9		14
9.1		14
9.1.1		14
9.2	-,	14
9.3	Acknowledge	15
10	Application design-in information	16
10.1		16
10.2	How to read and write to I/O expander	
	(16
10.3 10.4	g carrotte arrive reals approximation	17
	g.a	17
11	gg	18
12		18
13		19
14	•	20
15	Package outline	23
16	Handling information	26
17	Soldering of SMD packages	26
17.1		26
17.2	•	26
17.3		26
17.4	Reflow soldering	27

Soldering: PCB footprints	29
Abbreviations	32
Revision history	32
Legal information	34
Data sheet status	34
Definitions	34
Disclaimers	34
Trademarks	35
Contact information	35

Please be aware that important notices concerning this document and the product(s) described herein, have been included in section 'Legal information'.

© NXP B.V. 2013.

All rights reserved.

For more information, please visit: http://www.nxp.com For sales office addresses, please send an email to: salesaddresses@nxp.com

Date of release: 27 May 2013 Document identifier: PCA9672

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

NXP:

PCA9672BS,118 PCA9672D,512 PCA9672D,518 PCA9672PW,112 PCA9672PW,118