



PALM TECHNOLOGY CO., LTD.

The LCD(M) Specialist

*CONTACT ADDRESS : 14F~15F, No.383, Yangming Rd.,Samin District,
Kaohsiung City 807,Taiwan(R.O.C)
Tel: 886-7-3983966
Fax: 886-7-3982966
E-mail: sales@palmtech.com.tw*

PART NO. : PMG1203D-SYL

FOR MESSRS. : _____

CONTENTS

<i>NO.</i>	<i>ITEM</i>	<i>PAGE</i>
1.	COVER	1
2.	RECORD OF REVISION	2
3.	GENERAL SPECIFICATION	3
4.	MECHANICAL DATA	3
5.	ABSOLUTE MAXIMUM RATINGS	4
6.	ELECTRICAL CHARACTERISTICS	5
7.	OPTICAL CHARACTERISTICS	5
8.	DIMENSION OUTLINE	6
9.	BLOCK DIAGRAM	7
10.	DISPLAY DATA RAM	8
11.	INITIALIZATION BY INSTRUCTIONS	9
12.	POWER SUPPLY	10



ACCEPTED BY : _____

PROPOSED BY : _____

RECORD OF REVISION

DATE	PAGE	SUMMARY

3. General specifications

3.1 General specifications

PLEASE REFER TO:

“CUSTOMER ACCEPTANCE STANDARD SPECIFICATIONS (MS-10-1520S)”.

3.2 This individual specification is prior to general specifications

4. Mechanical data

- (1) NUMBER OF DOTS -----122 W * 32 H DOTS
- (2) MODULE SIZE -----68.0 W * 31.75 H * 10.0 T (max) mm
- (3) EFFECTIVE AREA -----57.2 W * 17.7 H mm
- (4) ACTIVE AREA -----52.42 W * 13.72 H mm
- (5) DOT SIZE-----0.39 W * 0.39 Hmm
- (6) DOT PITCH -----0.43 W * 0.43 H mm
- (7) VIEWING DIRECTION -----6 O’CLOCK
- (8) LCD TYPE-----STN,YELLOW-GREEN,TRANSFLECTIVE
- (9) LED COLOR -----YELLOW-GREEN

5. Absolute maximum ratings

5.1 Electrical absolute maximum ratings

<i>I T E M</i>	<i>SYMBOL</i>	<i>MIN.</i>	<i>MAX.</i>	<i>UNIT</i>	<i>COMMENT</i>
POWER SUPPLY FOR LOGIC	V _{DD} -V _{SS}	0	6.0	V	-----
INPUT VOLTAGE	V _I	V _{SS}	V _{DD}	V	-----
STATIC ELECTRICITY	-----	-----	100	V	NOTE (1)

NOTE (1): ELECTRO-STATIC DISCHARGE RESISTANCE IS TESTED BY CHARGING A 200PF CAPACITOR AND DISCHARGING IT BY CONTACT WITH A INTERFACE CONNECTOR PIN.

5.2 Environmental absolute maximum ratings

<i>I T E M</i>	<i>OPERATING</i>		<i>STORAGE</i>		<i>COMMENT</i>
	<i>MIN.</i>	<i>MAX.</i>	<i>MIN.</i>	<i>MAX.</i>	
AMBIENT TEMPERATURE	0°C	50°C	-20°C	70°C	-----
HUMIDITY	NOTE (2)		NOTE (2)		NO CONDENSATION
VIBRATION NOTE (3)	-----	0.5G	-----	2G	10~300Hz XYZ DIRECTIONS 1 Hr EACH
SHOCK NOTE (3)	-----	3G	-----	50G	10 msec XYZ DIRECTIONS 1 TIME EACH
CORROSIVE GAS	NOT ACCEPTABLE		NOT ACCEPTABLE		-----

NOTE (3): Ta ≤ 50°C: 90% RH MAX.

Ta > 50°C: ABSOLUTE HUMIDITY MUST BE LOWER THAN THE HUMIDITY OF 90% RH AT 50°C. (80% RH AT 60°C)

NOTE (4): 1G = 9.8 m/s²

6. Electrical characteristics

Ta = 25°C VDD = 5.060.25 V

<i>I T E M</i>	<i>SYMBOL</i>	<i>CONDITION</i>	<i>MIN.</i>	<i>TYP.</i>	<i>MAX.</i>	<i>UNIT</i>
POWER SUPPLY VOLTAGE FOR CIRCUIT	VDD-VSS	-----	4.75	5.0	5.25	V
INPUT VOLTAGE NOTE (2)	V _{IH}	H LEVEL	2.0	-----	V _{DD}	V
	V _{IL}	L LEVEL	0	-----	0.8	
OUTPUT VOLTAGE NOTE (1)	V _{OH}	I _{OH} = -0.3 mA	2.4	-----	-----	V
	V _{OL}	I _{OL} = 3.0 mA	-----	-----	0.4	V
POWER SUPPLY CURRENT, NOTE (3)	I _{DD}	V _{DD} -V _{SS} = 5.0V	-----	1.5	2.0	mA
LCD DISPLAY DUTY RATIO	DUTY	-----	-----	1/32	-----	-----
CLOCK OSCILLATION FREQUENCY	f _{osc}	FOR LCD MODULE	15	18	21	KHz
RECOMMENDED LCD DRIVING VOLTAGE, NOTE (4)	V _{DD} -V _O Φ=10° θ = 0°	Ta = 50°C	-----	4.2	-----	V
		Ta = 25°C	-----	4.6	-----	V
		Ta = 0°C	-----	4.8	-----	V
POWER SUPPLY CURRENT FOR LED	I _{LED}	V _{DD} = 5.0V	-----	40	50	mA

NOTE (1): APPLIED TO TERMINALS DB0~DB7

NOTE (2): APPLIED TO TERMINALS E, A0, DB0~DB7

NOTE (3): THE DISPLAY PATTERN IS ALL "ON", OR ALL "OFF"

NOTE (4): RECOMMENDED LCD DRIVING VOLTAGE MAY FLUCTUATE ABOUT=0.5V EACH MODULE.

NOTE (5): OPTICAL CHARACTERISTIC

7. Optical characteristics


Ta = 25°C VDD = 5.0V

<i>I T E M</i>	<i>SYMBOL</i>	<i>CONDITION</i>	<i>MIN.</i>	<i>TYP.</i>	<i>MAX.</i>	<i>UNIT</i>	<i>NOTE</i>
VIEWING ANGLE	Φ2-Φ1	K = 2.0	30	40	-----	deg.	1
CONTRAST RATIO	K	Φ = 10° θ = 0°	3	4	-----	-----	1
RESPONSE TIME	tr (rise)	Φ = 10° θ = 0°	-----	200	350	ms	1
	tf (fall)	Φ = 10° θ = 0°	-----	300	400	ms	1
BRIGHTNESS FOR LED BACKLIGHT	B	(*) Φ = 0° θ = 0°	3.0	-----	-----	cd/m ²	-----

(*UNDER NORMAL TEMPERATURE AND HUMIDITY IN A DARK ROOM)

NOTE (1): SEE CUSTOMER ACCEPTANCE STANDARD SPECIFICATION FOR DEFINITION OF OPTICAL CHARACTERISTICS.


8. Dimension outline



Interface pin connection

PIN NO.	1	2	3	4	5	6	7	8	9	10
SYMBOL	V _{SS}	V _{DD}	V _O	NC	A0	E1	E2	DB0	DB1	NC
PIN NO.	11	12	13	14	15	16	17	18	19	20
SYMBOL	NC	DB2	DB3	DB4	DB5	DB6	DB7	NC	NC	NC

9. Block diagram




10. Display data RAM

Page Address D1,D2=	DATA	Display Pattern										Line Address	
0, 0	D0	[Pattern]										00H	
	D1	[Pattern]										01	
	D2	[Pattern]										02	
	D3	[Pattern]										03	
	D4	[Pattern]										04	
	D5	[Pattern]										05	
	D6	[Pattern]										06	
	D7	[Pattern]										07	
0, 1	D0	[Pattern]										08	
	D1	[Pattern]										09	
	D2	[Pattern]										0A	
	D3	[Pattern]										0B	
	D4	[Pattern]										0C	
	D5	[Pattern]										0D	
	D6	[Pattern]										0E	
	D7	[Pattern]										0F	
1, 0	D0	[Pattern]										10	
	D1	[Pattern]										11	
	D2	[Pattern]										12	
	D3	[Pattern]										13	
	D4	[Pattern]										14	
	D5	[Pattern]										15	
	D6	[Pattern]										16	
	D7	[Pattern]										17	
1, 1	D0	[Pattern]										18	
	D1	[Pattern]										19	
	D2	[Pattern]										1A	
	D3	[Pattern]										1B	
	D4	[Pattern]										1C	
	D5	[Pattern]										1D	
	D6	[Pattern]										1E	
	D7	[Pattern]										1F	
Column Address	A	DO=0	3C	3B	3A	39	38	37	36	35	←-----	00	normal
	C	DO=1	13	14	15	16	17	18	19	1A	-----→	4F	
Segment Term.			60	59	58	57	56	55	54	53	-----	0	

Fig.1. Correspondence with Display Data RAM and address

11. Initialization by instructions



12. Power supply for LCM

