



FEATURES:

- Accepts miniature banana plugs.
- Mounts in panels up to .250" thick.

MATERIAL:

Banana Jack Insulation – Polycarbonate. Color: Black

Panel Insulator – Polycarbonate. Color: Black

Lockwasher, #8 Internal Tooth – Steel

Hex Nut, #8-32 – Brass

Banana Jack Body - Brass

Finish:

Lockwasher #8 – Nickel plated

Hex Nut - Nickel plated.

Banana Jack Body - Gold plated.

RATINGS:

Operating Temperature: +115°C. (+239°F.) Max.

Current: 5 Amperes.

ORDERING INFORMATION: Model 2142-*

*=Color Code – See Tabulation Block

Sold in packages of 10.

All dimensions are in inches. Tolerances (except noted): .xx = ±.02" (.51 mm), .xxx = ± .005" (.127 mm).

All specifications are to the latest revisions. Specifications are subject to change without notice.

Registered trademarks are the property of their respective companies. Made in USA