


U.I. Lapp GmbH	<b>PRODUCT INFORMATION</b>	
	<b>SKINTOP® MS-M ATEX</b>	07.11.2014

Cold impact resistance  
 High strain relief  
 Wide, variable clamping ranges  
 Anti-static  
 Maximum reliability




Good chemical resistance



Mechanical resistance



Oil & Gas



Optimum strain relief



Reliability



Variety of approval certifications

### Application range

Devices, machines and apparatus of enhanced safety protection type "e"  
 Equipment group II / Category 2G+1D  
 For mobile applications in offshore and marine industries  
 Chemical and petrochemical industry

### Product Make-up

Metric connection thread acc. to EN 50262

### Norm references / Approvals

UL File Nr. E79903

### Note

Refer to SKINTOP® SDV-M ATEX for suitable accessories


### Product features

SKINTOP® MS-M-XL ATEX is similar to the SKINTOP® MS-M ATEX, but has an extended connection thread for thick walls

### Remark

Photographs are not to scale and do not represent detailed images of the respective products.

Product Management	Document: LAPP_PRO993EN.pdf	1 / 4
--------------------	-----------------------------	-------

U.I. Lapp GmbH	<b>PRODUCT INFORMATION</b>	
	<b>SKINTOP® MS-M ATEX</b>	<b>07.11.2014</b>

**Technical Data**


Caution:	Refer to the instruction leaflet for the installation dimensions and torques
Approvals:	CE 0637 Ex II 2G Ex eb IIC Ex II 1D Ex ta IIIC IECEX IBE 13.0026X
Classification:	ETIM 5.0 Class-ID: EC000441 ETIM 5.0 Class-Description: cable screw gland
Material:	Body: nickel-plated brass Insert: polyamide Sealing ring: CR O-ring: NBR
Tests:	DIN EN 60079-0 DIN EN 60079-7
Protection rating:	IP 68 - 10 bar
Temperature range:	-30°C to +90°C


Product Management	Document: LAPP_PRO993EN.pdf	2 / 4
--------------------	-----------------------------	-------

**SKINTOP® MS-M ATEX**

07.11.2014

Part number	Article designation / size	Clamping range ØF (mm)	SW (mm)	Overall length/ C (mm)	Thread length/ D (mm)	Pieces / PU
<b>SKINTOP® MS-M ATEX</b>						
53112700	12 x 1,5	3 - 7	16	26,5	6.5	100
53112710	16 x 1,5	4,5 - 10	20	33.0	7.0	100
53112720	20 x 1,5	7 - 13	24	37.0	8.0	50
53112730	25 x 1,5	9 - 17	29	38,5	8.0	25
53112740	32 x 1,5	11 - 21	36	45,5	9.0	25
53112750	40 x 1,5	19 - 28	45	48.0	9.0	10
53112760	50 x 1,5	26 - 35	54	55,5	10.0	5
53112770	63 x 1,5	34 - 45	67	67.0	15.0	5
53112779	63 x 1,5 plus	44 - 55	75	65,5	15.0	1
<b>SKINTOP® MS-M-XL ATEX</b>						
53112800	12 x 1,5	3 - 7	16	32,8	12.0	100
53112810	16 x 1,5	4,5 - 10	20	37.0	12.0	100
53112820	20 x 1,5	7 - 13	24	39,5	12.0	50
53112830	25 x 1,5	9 - 17	29	41,5	12.0	25
53112840	32 x 1,5	11 - 21	36	48,2	15.0	25
53112850	40 x 1,5	19 - 28	45	53,5	15.0	10
53112860	50 x 1,5	26 - 35	54	57,5	15.0	5

U.I. Lapp GmbH	<b>PRODUCT INFORMATION</b>	
	<b>SKINTOP® MS-M ATEX</b>	07.11.2014



Product Management	Document: LAPP_PRO993EN.pdf	4 / 4
--------------------	-----------------------------	-------