

RF TERMINATION

Type 65_MMCX-50-0-2/111_N

Description

Standard Termination, Low Power



Product Configuration

Connector	MMCX plug (male)
Interface standards	HUBER+SUHNER - MMCX

Technical Data

Electrical Data

Nominal Impedance	50 Ω
Frequency range	0 to 6 GHz
VSWR max.	1.22
Power rating	1 Watt average power up to 85 °C ambient temperature, linearly derated to 0 Watt at 115 °C ambient temperature.

Mechanical Data

Weight	0.001 kg
--------	----------

Environmental Data

Operating temperature	-40 °C to 115 °C
2011/65/EU (RoHS - including 2015/863 and 2017/2102)	compliant

Material Data

Piece Part	Material	Surface Plating
Centre contact	Copper Beryllium Alloy	SUCOPRO / Gold Plating
Outer contact	Brass	Gold Plating
Body	Brass	Gold Plating
Insulator	PFA / PTFE	

Related Documents

Outline drawing	DOU-00278433
-----------------	--------------

Ordering Information

Single Packaging	65_MMCX-50-0-2/111_NE
Packaging	

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[HUBER+SUHNER:](#)

[65_MMCX-50-0-2/111_NE](#)