


Coaxial PCB Connector 85_N-50-0-5/13-_N

Description

Right angle PCB jack

Interface Standards

IEC 61169-16_MIL-STD-348A/304_CECC 22210



Technical Data

Electrical Data

Impedance 50 Ω
Interface frequency max. 11 GHz

Mechanical Data

Board mounting type through holes

Environmental Data

Operating temperature -65 °C to 165 °C
2011/65/EU (RoHS - including compliant
2015/863 and 2017/2102)

Material Data

Piece Parts	Material	Surface Plating
Centre contact	Copper Beryllium / Brass	Gold Plating (Nickel underplated)
Outer contact	Brass	SUCOPLATE (R) Plating
Body	Brass	SUCOPLATE (R) Plating
Insulator	PFA / PTFE	
Gasket	VMQ (Silicone rubber)	
Fastening nut	Brass	SUCOPLATE (R) Plating
Washer	Bronze	SUCOPLATE (R) Plating

Related Documents

Outline drawing DOU-00013288

Ordering Information

Tray package 85_N-50-0-5/13-_NY

Remarks

PCB connector with stand-offs

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[HUBER+SUHNER:](#)

[85_N-50-0-5/13-_NY](#)