

Downloaded from Arrow.com.

UF4001, UF4002, UF4003, UF4004, UF4005, UF4006, UF4007

www.vishay.com

Vishay General Semiconductor

COMPLIANT

HALOGEN FREE

Ultrafast Plastic Rectifier



PRIMARY CHARACTERISTICS								
I _{F(AV)} 1.0 A								
V_{RRM}	50 V, 100 V, 200 V, 400 V, 600 V, 800 V, 1000 V							
I _{FSM}	30 A							
t _{rr}	50 ns, 75 ns							
V_{F}	1.0 V, 1.7 V							
T_J max.	150 °C							
Package	DO-41 (DO-204AL)							
Circuit configuration	Single							

FEATURES

- · Glass passivated chip junction
- · Ultrafast reverse recovery time
- Low forward voltage drop
- · Low switching losses, high efficiency
- High forward surge capability
- Solder dip 275 °C max. 10 s, per JESD 22-B106
- Material categorization: for definitions of compliance please see <u>www.vishay.com/doc?99912</u>

TYPICAL APPLICATIONS

For use in high frequency rectification and freewheeling application in switching mode converters and inverters for consumer, computer, and telecommunication.

MECHANICAL DATA

Case: DO-41 (DO-204AL)

Molding compound meets UL 94 V-0 flammability rating Base P/N-E3 - RoHS-compliant, commercial grade Base P/N-M3 - halogen-free, RoHS-compliant, commercial grade

graue

Terminals: matte tin plated leads, solderable per

J-STD-002 and JESD 22-B102

E3 and M3 suffix meets JESD 201 class 1A whisker test

Polarity: color band denotes cathode end

MAXIMUM RATINGS (T _A = 25 °C unless otherwise noted)									
PARAMETER	SYMBOL	UF4001	UF4002	UF4003	UF4004	UF4005	UF4006	UF4007	UNIT
Maximum repetitive peak reverse voltage	V _{RRM}	50	100	200	400	600	800	1000	V
Maximum RMS voltage	V _{RMS}	35	70	140	280	420	560	700	V
Maximum DC blocking voltage	V_{DC}	50	100	200	400	600	800	1000	V
Maximum average forward rectified current 0.375" (9.5 mm) lead length at T _A = 55 °C	I _{F(AV)}	1.0					Α		
Peak forward surge current 8.3 ms single half sine-wave superimposed on rated load	I _{FSM}	30				Α			
Operating junction and storage temperature range	T _J , T _{STG}	-55 to +150					°C		

Revision: 06-Apr-2020 **1** Document Number: 88755 For technical questions within your region: <u>DiodesAmericas@vishay.com</u>, <u>DiodesAsia@vishay.com</u>, <u>DiodesEurope@vishay.com</u>

THIS DOCUMENT IS SUBJECT TO CHANGE WITHOUT NOTICE. THE PRODUCTS DESCRIBED HEREIN AND THIS DOCUMENT ARE SUBJECT TO SPECIFIC DISCLAIMERS, SET FORTH AT www.vishay.com/doc?91000



UF4001, UF4002, UF4003, UF4004, UF4005, UF4006, UF4007

www.vishay.com

Vishay General Semiconductor

ELECTRICAL CHARACTERISTICS (T _A = 25 °C unless otherwise noted)											
PARAMETER	TEST CONDITIONS		SYMBOL	UF4001	UF4002	UF4003	UF4004	UF4005	UF4006	UF4007	UNIT
Maximum instantaneous forward voltage	1.0 A		V _F ⁽¹⁾	1.0 1.7				1.7		V	
Maximum DC reverse current at rated DC		T _A = 25 °C	1_	10							
blocking voltage		T _A = 100 °C	I _R	50						– μA	
Maximum reverse recovery time	I _F = 0. I _{rr} = 0.	5 A, I _R = 1.0 A, 25 A	t _{rr}	50 75					ns		
Typical junction capacitance	4.0 V,	1 MHz	CJ	17					pF		

Note

⁽¹⁾ Pulse test: 300 µs pulse width, 1 % duty cycle

THERMAL CHARACTERISTICS (T _A = 25 °C unless otherwise noted)									
PARAMETER SYMBOL UF4001 UF4002 UF4003 UF4004 UF4005 UF4006 UF4007 UNIT								UNIT	
Typical thermal resistance	R _{0JA} (1)	60							°C/W
Typical thermal resistance	R _{BJL} ⁽¹⁾ 15						C/VV		

Note

⁽¹⁾ Thermal resistance from junction to ambient at 0.375" (9.5 mm) lead length

ORDERING INFORMATION (Example)									
PREFERRED P/N	UNIT WEIGHT (g)	PREFERRED PACKAGE CODE	BASE QUANTITY	DELIVERY MODE					
UF4007-E3/54	0.33	54	5500	13" diameter paper tape and reel					
UF4007-E3/73	0.34	73	3000	Ammo pack packaging					
UF4007-M3/54	0.33	54	5500	13" diameter paper tape and reel					
UF4007-M3/73	0.34	73	3000	Ammo pack packaging					

RATINGS AND CHARACTERISTICS CURVES (T_A = 25 °C unless otherwise noted)




Fig. 1 - Maximum Forward Current Derating Curve




Fig. 2 - Maximum Non-Repetitive Peak Forward Surge Current

Revision: 06-Apr-2020 2 Document Number: 88755



UF4001, UF4002, UF4003, UF4004, UF4005, UF4006, UF4007

www.vishay.com

Vishay General Semiconductor




Fig. 3 - Typical Instantaneous Forward Characteristics




Fig. 6 - Typical Reverse Leakage Characteristics




Fig. 4 - Typical Instantaneous Forward Characteristics




Fig. 7 - Typical Junction Capacitance




Fig. 5 - Typical Reverse Leakage Characteristics




UF4001, UF4002, UF4003, UF4004, UF4005, UF4006, UF4007

www.vishay.com

Vishay General Semiconductor

PACKAGE OUTLINE DIMENSIONS in inches (millimeters)



Legal Disclaimer Notice



Vishay

Disclaimer

ALL PRODUCT, PRODUCT SPECIFICATIONS AND DATA ARE SUBJECT TO CHANGE WITHOUT NOTICE TO IMPROVE RELIABILITY, FUNCTION OR DESIGN OR OTHERWISE.

Vishay Intertechnology, Inc., its affiliates, agents, and employees, and all persons acting on its or their behalf (collectively, "Vishay"), disclaim any and all liability for any errors, inaccuracies or incompleteness contained in any datasheet or in any other disclosure relating to any product.

Vishay makes no warranty, representation or guarantee regarding the suitability of the products for any particular purpose or the continuing production of any product. To the maximum extent permitted by applicable law, Vishay disclaims (i) any and all liability arising out of the application or use of any product, (ii) any and all liability, including without limitation special, consequential or incidental damages, and (iii) any and all implied warranties, including warranties of fitness for particular purpose, non-infringement and merchantability.

Statements regarding the suitability of products for certain types of applications are based on Vishay's knowledge of typical requirements that are often placed on Vishay products in generic applications. Such statements are not binding statements about the suitability of products for a particular application. It is the customer's responsibility to validate that a particular product with the properties described in the product specification is suitable for use in a particular application. Parameters provided in datasheets and / or specifications may vary in different applications and performance may vary over time. All operating parameters, including typical parameters, must be validated for each customer application by the customer's technical experts. Product specifications do not expand or otherwise modify Vishay's terms and conditions of purchase, including but not limited to the warranty expressed therein.

Except as expressly indicated in writing, Vishay products are not designed for use in medical, life-saving, or life-sustaining applications or for any other application in which the failure of the Vishay product could result in personal injury or death. Customers using or selling Vishay products not expressly indicated for use in such applications do so at their own risk. Please contact authorized Vishay personnel to obtain written terms and conditions regarding products designed for such applications.

No license, express or implied, by estoppel or otherwise, to any intellectual property rights is granted by this document or by any conduct of Vishay. Product names and markings noted herein may be trademarks of their respective owners.

© 2021 VISHAY INTERTECHNOLOGY, INC. ALL RIGHTS RESERVED