


Optocoupler, Phototransistor Output, AC Input, Low Input Current, SSOP-4, Half Pitch, Mini-Flat Package



DESCRIPTION

The VOS628A series has a GaAs infrared emitting diode emitter, which is optically coupled to a silicon planar phototransistor detector, and is incorporated in a 4-pin 50 mil lead pitch mini-flat package.

It features a high current transfer ratio at low input current, low coupling capacitance, and high isolation voltage.

The coupling devices are designed for signal transmission between two electrically separated circuits.

FEATURES

- · High CTR with low input current
- Low profile package (half pitch)
- High collector emitter voltage V_{CEO} = 80 V
- Isolation test voltage = 3750 V_{RMS}
- · Low coupling capacitance
- High common mode transient immunity
- Material categorization:
 For definitions of compliance please see www.vishay.com/doc?99912





COMPLIANT HALOGEN FREE GREEN

APPLICATIONS

- Telecom
- · Industrial controls
- Battery powered equipment
- · Office machines
- · Programmable controllers

AGENCY APPROVALS

Safety application model number covering all products in this datasheet is VOS628A. This model number should be used when consulting safety agency documents.

- UL1577, file no. E52744
- cUL
- DIN EN 60747-5-5 (VDE 0884-5), available with option 1
- FIMKO EN 60065, EN 60950-1
- CQC GB4943.1-2011 and GB8898-2011 (suitable for installation altitude below 2000 m)

ORDERING INFORMATION					
V O S 6 2 8 PART NUMBER	A - # X CTR PACE	0 0 1 T KAGE OPTION TAPE AND REEL	SSOP-4 ≥ 5 mm		
AGENCY CERTIFIED/PACKAGE	CTR (%)				
AGENOT GENTINED/T AGNAGE	± 1 mA				
UL, cUL, FIMKO, CQC	50 to 600	63 to 125	100 to 200		
SSOP-4, 50 mil pitch	VOS628AT	VOS628A-2T	VOS628A-3T		
UL, cUL, FIMKO, CQC, VDE (option 1)	50 to 600	63 to 125	100 to 200		
SSOP-4, 50 mil pitch	VOS628A-X001T	VOS628A-2X001T	VOS628A-3X001T		

Note

Additional options may be possible, please contact sales office.



www.vishay.com

Vishay Semiconductors

ABSOLUTE MAXIMUM RATINGS (T _{amb} = 25 °C, unless otherwise specified)					
PARAMETER	TEST CONDITION	SYMBOL	VALUE	UNIT	
INPUT	•				
Reverse voltage		V _R	6	V	
Power dissipation		P _{diss}	70	mW	
Surge forward current	t _p ≤ 10 μs	I _{FSM}	1.5	Α	
Forward current		I _F	50	mA	
OUTPUT					
Collector emitter voltage		V _{CEO}	80	V	
Emitter collector voltage		V _{ECO}	7	V	
Collector current		I _C	50	mA	
	$t_p/T = 0.5, t_p < 10 \text{ ms}$	I _C	100	mA	
Power dissipation		P _{diss}	150	mW	
COUPLER	•				
Isolation test voltage between emitter and detector	t = 1 min	V _{ISO}	3750	V _{RMS}	
Total power dissipation		P _{tot}	170	mW	
Storage temperature range		T _{stg}	-55 to +150	°C	
Ambient temperature range		T _{amb}	-55 to +110	°C	
Junction temperature		T _j	125	°C	
Soldering temperature (1)		T _{sld}	260	°C	

Notes

- Stresses in excess of the absolute maximum ratings can cause permanent damage to the device. Functional operation of the device is not
 implied at these or any other conditions in excess of those given in the operational sections of this document. Exposure to absolute
 maximum ratings for extended periods of the time can adversely affect reliability.
- (1) Refer to reflow profile for soldering conditions for surface mounted devices.




Fig. 1 - Power Dissipation vs. Ambient Temperature




Fig. 2 - Forward Current vs. Ambient Temperature



www.vishay.com Vishay Semiconductors

ELECTRICAL CHARACTERISTICS (T _{amb} = 25 °C, unless otherwise specified)						
PARAMETER	TEST CONDITION	SYMBOL	MIN.	TYP.	MAX.	UNIT
INPUT						
Forward voltage	I _F = 50 mA	V_{F}		1.1	1.5	V
Reverse current	V _R = 6 V	I _R		0.01	10	μA
Capacitance	$V_R = 0 V, f = 1 MHz$	Co		8		pF
OUTPUT						
Collector emitter leakage current	V _{CE} = 10 V	I _{CEO}		0.7	100	nA
Collector emitter breakdown voltage	I _C = 100 μA	BV _{CEO}	80			V
Emitter collector breakdown voltage	I _E = 10 μA	BV _{ECO}	7			V
Collector emitter capacitance	V _{CE} = 5 V, f = 1 MHz	C _{CE}		6		pF
COUPLER						
Collector emitter saturation voltage	$I_F = 1 \text{ mA}, I_C = 0.25 \text{ mA}$	V _{CEsat}		0.12	0.4	V
Cut-off frequency	$I_F = 10$ mA, $V_{CC} = 5$ V, $R_L = 100 \Omega$	f _{ctr}		119		kHz

Note

Minimum and maximum values are testing requirements. Typical values are characteristics of the device and are the result of engineering
evaluation. Typical values are for information only and are not part of the testing requirements.

CURRENT TRANSFER RATIO (T _{amb} = 25 °C, unless otherwise specified)							
PARAMETER	TEST CONDITION	PART	SYMBOL	MIN.	TYP.	MAX.	UNIT
I _C /I _F	$I_F = \pm 1 \text{ mA}, V_{CE} = 5 \text{ V}$	VOS628A	CTR	50		600	%
		VOS628A-2	CTR	63		125	%
		VOS628A-3	CTR	100		200	%

SWITCHING CHARACTERISTICS (T _{amb} = 25 °C, unless otherwise specified)								
PARAMETER	TEST CONDITION	SYMBOL	MIN.	TYP.	MAX.	UNIT		
NON-SATURATED	NON-SATURATED							
Turn on time		t _{on}		5		μs		
Rise time	$V_{CC} = 5 \text{ V}, I_{C} = 2 \text{ mA}, R_{I} = 100 \Omega$	t _r		5		μs		
Turn off time	$V_{CC} = 5 \text{ V}, I_{C} = 2 \text{ IIIA}, R_{L} = 100 \Omega$	t _{off}		8		μs		
Fall time		t _f		7		μs		
SATURATED								
Rise and fall time	$I_F = 1.6 \text{ mA}, V_{CC} = 5 \text{ V}, R_L = 1.9 \text{ k}\Omega$	t _r		10		μs		
Fall time		t _f		11		μs		
Turn on time		t _{on}		14		μs		
Turn off time		t _{off}		12		μs		




Fig. 3 - Test Circuit




Fig. 4 - Test Circuit and Waveforms



SAFETY AND INSULATION RATINGS						
PARAMETER	SYMBOL	VALUE	UNIT			
MAXIMUM SAFETY RATINGS						
Output safety power		P _{SO}	300	mW		
Input safety current		I _{si}	200	mA		
Safety temperature		T _S	150	°C		
Comparative tracking index	CTI	175				
INSULATION RATED PARAMETERS						
Maximum withstanding isolation voltage	40 % to 60 % RH, AC test of 1 min	V _{ISO}	3750	V _{RMS}		
Maximum transient isolation voltage		V _{IOTM}	6000	V _{peak}		
Maximum repetitive peak isolation voltage		V _{IORM}	565	V _{peak}		
Insulation resistance	$T_{amb} = 25 ^{\circ}\text{C}, V_{DC} = 500 \text{V}$	R _{IO}	≥ 10 ¹²	Ω		
Isolation resistance	$T_{amb} = 100 ^{\circ}\text{C}, V_{DC} = 500 \text{V}$	R _{IO}	≥ 10 ¹¹	Ω		
Climatic classification (according to IEC 68 part 1)			55/110/21			
Environment (pollution degree in accordance to DIN VDE 0109)			2			
Creepage distance			≥ 5	mm		
Clearance distance			≥ 5	mm		
Insulation thickness		DTI	≥ 0.4	mm		

Note

TYPICAL CHARACTERISTICS (T_{amb} = 25 °C, unless otherwise specified)




Fig. 5 - Forward Voltage vs. Forward Current




Fig. 6 - Collector Current vs. Collector Emitter Voltage

As per IEC 60747-5-5, §7.4.3.8.2, this optocoupler is suitable for "safe electrical insulation" only within the safety ratings. Compliance with
the safety ratings shall be ensured by means of protective circuits.




Fig. 7 - Collector Emitter Current vs. Ambient Temperature




Fig. 8 - Collector Current vs. Collector Emitter Voltage




Fig. 9 - Collector Emitter Voltage vs. Ambient Temperature




Fig. 10 - Normalized Current Transfer Ratio vs.
Ambient Temperature




Fig. 11 - Normalized Current Transfer Ratio vs.

Ambient Temperature




Fig. 12 - Current Transfer Ratio vs. Forward Current






Fig. 13 - Current Transfer Ratio vs. Forward Current




Fig. 14 - Frequency (- 3 dB) vs. Collector Current




Fig. 15 - Frequency vs. Phase Angle




Fig. 16 - Switching Time vs. Load Resistance






Fig. 17 - Voltage Gain vs. Frequency







PACKAGE DIMENSIONS in millimeters










PACKAGE MARKING (example of VOS628A-3X001T)



Notes

- Option 1 is reflected with letter "X".
- Tape and reel suffix (T) is not part of the package marking.
- VOS628AT can be marked as 628A1, 628A2, 628A3, or 628A4.
- VOS628A-X001T is marked as 628A1X, 628A2X, 628A3X, or 628A4X.

TAPE AND REEL DIMENSIONS in millimeters




Fig. 18 - Reel Dimensions (3000 units per reel)




Fig. 19 - Tape Dimensions

Legal Disclaimer Notice



Vishay

Disclaimer

ALL PRODUCT, PRODUCT SPECIFICATIONS AND DATA ARE SUBJECT TO CHANGE WITHOUT NOTICE TO IMPROVE RELIABILITY, FUNCTION OR DESIGN OR OTHERWISE.

Vishay Intertechnology, Inc., its affiliates, agents, and employees, and all persons acting on its or their behalf (collectively, "Vishay"), disclaim any and all liability for any errors, inaccuracies or incompleteness contained in any datasheet or in any other disclosure relating to any product.

Vishay makes no warranty, representation or guarantee regarding the suitability of the products for any particular purpose or the continuing production of any product. To the maximum extent permitted by applicable law, Vishay disclaims (i) any and all liability arising out of the application or use of any product, (ii) any and all liability, including without limitation special, consequential or incidental damages, and (iii) any and all implied warranties, including warranties of fitness for particular purpose, non-infringement and merchantability.

Statements regarding the suitability of products for certain types of applications are based on Vishay's knowledge of typical requirements that are often placed on Vishay products in generic applications. Such statements are not binding statements about the suitability of products for a particular application. It is the customer's responsibility to validate that a particular product with the properties described in the product specification is suitable for use in a particular application. Parameters provided in datasheets and / or specifications may vary in different applications and performance may vary over time. All operating parameters, including typical parameters, must be validated for each customer application by the customer's technical experts. Product specifications do not expand or otherwise modify Vishay's terms and conditions of purchase, including but not limited to the warranty expressed therein.

Hyperlinks included in this datasheet may direct users to third-party websites. These links are provided as a convenience and for informational purposes only. Inclusion of these hyperlinks does not constitute an endorsement or an approval by Vishay of any of the products, services or opinions of the corporation, organization or individual associated with the third-party website. Vishay disclaims any and all liability and bears no responsibility for the accuracy, legality or content of the third-party website or for that of subsequent links.

Except as expressly indicated in writing, Vishay products are not designed for use in medical, life-saving, or life-sustaining applications or for any other application in which the failure of the Vishay product could result in personal injury or death. Customers using or selling Vishay products not expressly indicated for use in such applications do so at their own risk. Please contact authorized Vishay personnel to obtain written terms and conditions regarding products designed for such applications.

No license, express or implied, by estoppel or otherwise, to any intellectual property rights is granted by this document or by any conduct of Vishay. Product names and markings noted herein may be trademarks of their respective owners.