

**Customer Part:**

**Description**

- Ceramic package with a hermetically seam sealed metal lid suitable for automotive applications. Qualified to AEC-Q200 and available with IATF-16949:2016 release. Not suitable for safety critical applications.
- 4 pad
- Model IQXC-180 AUTO-B
- Model Issue number 3

**Frequency Parameters**

- Frequency 25.0MHz
- Frequency Tolerance ±50.00ppm
- Tolerance Condition @25°C ±2°C
- Frequency Stability ±100.00ppm
- Operating Temperature Range -40.00 to 125.00°C
- Overtone Order Fundamental
- Ageing ±5ppm max per year @ 25°C

**Electrical Parameters**

- Load Capacitance (CL) 8.00pF
- Shunt Capacitance (C0) 7pF max
- Drive Level 50µW standard, 200µW max
- ESR 50.00Ω max

**Environmental Parameters**

- Storage Temperature Range: -55°C to +150°C
- Qualified to AEC-Q200

**Manufacturing Details**


- RoHS Terminations NiAu
- RoHS Reflow Temp 260°C max for 10secs max

**Compliance**


- RoHS Status (2015/863/EU) Compliant
- REACH Status Compliant
- MSL Rating (JDEC-STD-033): Not Applicable

**Packaging Details**

- Pack Style: **Cutt** Cut tape
- Pack Size: 100
- *Alternative packing option available*




**Outline (mm)**




**Pad Connections**

1. Crystal
2. GND
3. Crystal
4. GND



**Solder Pad Layout**



**Sales Office Contact Details:**

UK: +44 (0)1460 270200  
 Germany: 0800 1808 443

France: 0800 901 383  
 USA: +1.760.318.2824

Email: [info@iqdfrequencyproducts.com](mailto:info@iqdfrequencyproducts.com)  
 Web: [www.iqdfrequencyproducts.com](http://www.iqdfrequencyproducts.com)

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[IQD Frequency Products:](#)

[LFX TAL071785Cutt](#)