


Stamped crimp contacts




| Identification | Wire gauge (mm <sup>2</sup> ) | Part No. |  |  |
|----------------|-------------------------------|----------|--|--|
|----------------|-------------------------------|----------|--|--|

D-Sub

| Performance levels<br>Explanations see page 05.04<br>Other performance levels on request    | Wire gauge (mm <sup>2</sup> )      | stamped male contacts                              |  |  |
|---|------------------------------------|--|--|--|
|   |                                    | Performance level 3                                | Performance level 2                                | Performance level 1                                |
| Individual contacts   | AWG 28-24<br>0.09-0.25<br>stranded | 09 67 000 7177 <sup>1)</sup>                       | 09 67 000 7178 <sup>1)</sup>                       | 09 67 000 7176 <sup>1)</sup>                       |
| 500 pieces/reel<br>Unrolling left   |                                    | 09 67 000 7167                                     | 09 67 000 7168                                     | 09 67 000 7166                                     |
| 10 000 pieces/reel<br>Unrolling left<br>Unrolling left reversed<br>Unrolling right reversed |                                    | 09 67 000 7157<br>09 67 000 7147<br>09 67 000 7137 | 09 67 000 7158<br>09 67 000 7148<br>09 67 000 7138 | 09 67 000 7156<br>09 67 000 7146<br>09 67 000 7136 |
| Individual contacts   | AWG 24-20<br>0.25-0.56<br>stranded | 09 67 000 8177 <sup>1)</sup>                       | 09 67 000 8178 <sup>1)</sup>                       | 09 67 000 8176 <sup>1)</sup>                       |
| 500 pieces/reel<br>Unrolling left   |                                    | 09 67 000 8167                                     | 09 67 000 8168                                     | 09 67 000 8166                                     |
| 10 000 pieces/reel<br>Unrolling left<br>Unrolling left reversed<br>Unrolling right reversed |                                    | 09 67 000 8157<br>09 67 000 8147<br>09 67 000 8137 | 09 67 000 8158<br>09 67 000 8148<br>09 67 000 8138 | 09 67 000 8156<br>09 67 000 8146<br>09 67 000 8136 |

Unrolling direction



<sup>1)</sup> Minimum order 500 pieces or multiples of 500  
Insertion and removal tool see chapter 20  
Contact dimensions see page 05.29