



All dimensions are in mm; tolerances according to ISO 2768 m-H

**Interface**

According to DIN EN 61169-8

**Documents**

Assembly instruction 51 P10

**Material and plating**

**Connector parts**

- Center contact
- Outer contact
- Body
- Dielectric
- Gasket
- Crimping ferrule

**Material**

- Brass
- Brass
- Brass
- PTFE
- NeopreneCR 50C6
- Copper

**Plating**

- AuroDur®, gold plated
- Flash white bronze over silver(e.g. Optargen®)
- Flash white bronze over silver(e.g. Optargen®)
- Flash white bronze over silver(e.g. Optargen®)

Dieses Dokument ist urheberrechtlich geschützt • This document is protected by copyright • Rosenberger Hochfrequenztechnik GmbH & Co. KG

RFB00035/12.20/6.4

**Electrical data**

|  |  |
|--|--|
| Impedance                                      | 50 Ω   |
| Frequency                                      | DC to 10 GHz   |
| Return loss                                    | ≥ 30 dB, DC to 2.5 GHz<br>≥ 20 dB, 2.5 to 4 GHz<br>≥ 18 dB, 4 to 6 GHz |
| Insertion loss                                 | ≤ 0.05 x √ f [GHz] dB, DC to 6 GHz                                     |
| Insulation resistance                          | ≥ 5 x 10 <sup>3</sup> MΩ   |
| Center contact resistance                      | ≤ 1.5 mΩ   |
| Outer contact resistance                       | ≤ 1 mΩ   |
| Test voltage                                   | 1500 V rms   |
| Working voltage                                | 400 V rms  |
| Power handling (at 20 °C, sea level, VSWR 1.0) | ≤ 80 W @ 2 GHz   |

- Limitations are possible due to the used cable type -

**Mechanical data**

|                                   |        |
|-----------------------------------|--------|
| Mating cycles                     | ≥ 500  |
| Center contact captivation: axial | ≥ 15 N |

**Environmental data**

|                     |                                 |
|---------------------|---------------------------------|
| Temperature range   | -55°C to +155°C                 |
| Thermal shock       | MIL-STD-202, Meth. 107, Cond. B |
| Corrosion           | MIL-STD-202, Meth. 101, Cond. B |
| Vibration           | MIL-STD-202, Meth. 204, Cond. B |
| Shock               | MIL-STD-202, Meth. 213, Cond. G |
| Moisture resistance | MIL-STD-202, Meth. 106          |
| RoHS                | compliant                       |

**Tooling**

|               |            |
|---------------|------------|
| Crimping tool | 11W150-000 |
| Crimp insert  | 11W150-208 |

**Suitable cables**

RG 141 /U, RG 58 C/U

**Weight**

|        |            |
|--------|------------|
| Weight | 10.8 g/pce |
|--------|------------|

While the information has been carefully compiled to the best of our knowledge, nothing is intended as representation or warranty on our part and no statement herein shall be construed as recommendation to infringe existing patents. In the effort to improve our products, we reserve the right to make changes judged to be necessary.

For the installation of the electrotechnical equipment, particular electrotechnical expertise is required.



|               |          |             |          |      |                           |                |          |
|---------------|----------|-------------|----------|------|---------------------------|----------------|----------|
| Draft         | Date     | Approved    | Date     | Rev. | Engineering change number | Name           | Date     |
| Inge Mühlauer | 20.07.04 | Chr. Janßen | 17.12.20 | d00  | 20-1927                   | S. Huber-Siegl | 17.12.20 |

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Rosenberger:](#)

[51S107-106N5](#)