



All dimensions are in mm; tolerances according to ISO 2768 m-H

**Interface**

According to SMA side: IEC 60169-15; EN 122110; MIL-STD-348A, Fig. 310  
 BNC side: IEC 60169-8, MIL-PRF-39012, CECC 22120

**Documents**

N/A

**Material and plating**

**Connector parts**

Center contact  
 Outer contact SMA side  
 Outer contact BNC side  
 Dielectric

**Material**

CuBe  
 CuBe or equiv.  
 Brass  
 PTFE

**Plating**

AuroDur®, gold plated  
 AuroDur®, gold plated  
 Nickel, 2.5-5 µm

ADAPTOR  
SMA JACK – BNC 50 Ω JACK

32K151-K00L5

**Electrical data**

Impedance	50 Ω	
Frequency	DC to 10 GHz	
VSWR	$\leq 1.05 + 0.005 \times f$ [GHz]	
Insertion loss	$\leq 0.04 \times \sqrt{f(\text{GHz})}$ dB	
Insulation resistance	$\geq 5 \times 10^3$ MΩ	
Center contact resistance	$\leq 3$ mΩ, SMA side	$\leq 1.5$ mΩ, BNC side
Outer contact resistance	$\leq 2$ mΩ, SMA side	$\leq 1.0$ mΩ, BNC side
Test voltage	1000 V rms	
Working voltage	400 V rms	
Power handling (at 20 °C, sea level, VSWR 1.0)	$\leq 80$ W @ 2 GHz	

**Mechanical data**

	SMA side	BNC side
Mating cycles	min. 500	min. 500
Center contact captivation: axial	$\geq 27$ N	$\geq 27$ N
Coupling test torque	max. 1.7 Nm	N/A
Recommended torque	0.8 Nm to 1.1 Nm	N/A

**Environmental data**

Temperature range	-55°C to +155°C
Thermal shock	MIL-STD-202, Meth. 107, Cond. B
Corrosion	MIL-STD-202, Meth. 101, Cond. B
Vibration	MIL-STD-202, Meth. 204, Cond. D
Shock	MIL-STD-202, Meth. 213, Cond. I
Moisture resistance 2002/95/EC (RoHS)	MIL-STD-202, Meth. 106 compliant

**Tooling**

N/A

**Suitable cables**

N/A

**Packing**

Standard	1 pcs in bag
Weight	8.7 g/pce

While the information has been carefully compiled to the best of our knowledge, nothing is intended as representation or warranty on our part and no statement herein shall be construed as recommendation to infringe existing patents. In the effort to improve our products, we reserve the right to make changes judged to be necessary.

Draft	Date	Approved	Date	Rev.	Engineering change number	Name	Date
Rong Fang	13/09/04	M. Schmid	05/09/07	d00	07-0625	B. Dandl	05.09.07
Rosenberger Hochfrequenztechnik GmbH & Co. KG P.O.Box 1260 D-84526 Tittmoning Germany <a href="http://www.rosenberger.de">www.rosenberger.de</a>					Tel.: +49 8684 18-0 Fax: +49 8684 18-499 email: <a href="mailto:info@rosenberger.de">info@rosenberger.de</a>		Page 2 / 2