



All dimensions are in mm; tolerances acc. ISO 2768 m-H

**Interface**

According to

MIL-STD-348A, Fig. 326

**Documents**

PCB layout

B 125

Tape & reel packaging

VG03.01M00

**Material and plating**

**Connector parts**

Center contact

Outer contact

Dielectric

**Material**

Brass

Brass

PTFE

**Plating**

AuroDur®, gold plated

AuroDur®, gold plated

**Electrical data**

Impedance	50 $\Omega$
Frequency	DC to 26.5 GHz
Return loss	$\geq 26$ dB, DC to 6 GHz $\geq 20$ dB, 6 to 18 GHz $\geq 17$ dB, 18 to 26.5 GHz
Insertion loss	$\leq 0.05 \times \sqrt{f(\text{GHz})}$ dB, DC to 18 GHz
Insulation resistance	$\geq 5$ G $\Omega$
Center contact resistance	$\leq 6.0$ m $\Omega$
Outer contact resistance	$\leq 2.0$ m $\Omega$
Test voltage	500 V rms
Working voltage	335 V rms
Contact Current	1.2A DC max.

- VSWR in application depends decisive on PCB layout -

**Mechanical data**

Mating cycles	$\geq 1000$
Center contact captivation:	$\geq 7$ N
Engagement force	
- smooth bore	9 N max.
Disengagement force	
- smooth bore	2.2 N min.

**Environmental data**

Temperature range	-65°C to +155°C
Thermal shock	MIL-STD-202, Method 107, Condition B
Vibration	MIL-STD-202, Method 204, Condition B
Shock	MIL-STD-202, Method 213, Condition A
Moisture resistance	MIL-STD-202, Method 106
Max. soldering temperature	IEC 61760-1, +260°C for 10 sec.
RoHS	compliant

**Tooling**

N/A

**Suitable cables**

N/A

**Weight**

Weight 0.4 g/pce

While the information has been carefully compiled to the best of our knowledge, nothing is intended as representation or warranty on our part and no statement herein shall be construed as recommendation to infringe existing patents. In the effort to improve our products, we reserve the right to make changes judged to be necessary.

Draft	Date	Approved	Date	Rev.	Engineering change number	Name	Date
F. Schmidhammer	04/04/06	Sa. Krautenbacher	12.03.14	e00	14-0352	T. Krojer	12.03.14
Rosenberger Hochfrequenztechnik GmbH & Co. KG P.O.Box 1260 D-84526 Tittmoning Germany <a href="http://www.rosenberger.de">www.rosenberger.de</a>					Tel.: +49 8684 18-0 Fax: +49 8684 18-499 email: <a href="mailto:info@rosenberger.de">info@rosenberger.de</a>		Page 2 / 2

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Rosenberger:](#)

[19S242-40ML5](#)