



preci-dip

PCB CONNECTORS


**SERIES
800**

800-PP-NNN-65-001101

Single row

2.54 mm, Solderless compliant press-fit, Pin Ø 0.76 mm

Pin connectors, press-fit With compliant pin for solderless mount in PCB plated through holes.



TECHNICAL SPECS.:

| | |
|----------------------------|---|
| Insulator | Black glass filled polyester PCT-GF30-FR |
| Flammability | UL 94V-O |
| Contact | Bronze CuSn4Pb4Zn4 (C54400) |
| Connecting pin Ø | 0.76 mm |
| Mechanical life | Min. 500 cycles |
| Rated current | 3 A |
| Dielectric strength | Min. 1000 V RMS |
| PCB hole Ø | 1 mm +0.09/-0.06 mm finished (1.15 ±0.025 mm drill) |

ORDERING INFORMATION:

| PP Plating code | Termination | Connecting pin |
|-----------------|--------------|----------------|
| 10* | Gold 0.25 µm | Gold 0.25 µm |
| 80* | Tin | Tin |
| V3 | Tin | Gold 0.75 µm |

* not for 800...-6B-002101NNN number of poles. Replace NNN with the requested number of poles, e.g. 800-10-NNN-65-001101 for a single row version with 8 pins becomes 800-10-008-65-001101.

TECHNICAL ASSISTANCE

GENERAL SPECIFICATIONS:

The values listed below are general specs applying for PRECI-DIP socket and pin connectors. Please see individual catalog page for additional and product specific technical data.

| | |
|-----------------------------|---------------------------------|
| Operating temperature range | -55 ... +125 °C |
| Climatic category (IEC) | 55/125/21 |
| Operating humidity range | annual mean 75 % |
| Max working voltage | 100 VRMS/150 VDC (2.54 mm grid) |

PRECI-DIP sockets are recognized by Underwriters Laboratories Inc. and listed under "Connectors for Use in Data, Signal, Control and Power Applications", File Nr. E174442

MECHANICAL CHARACTERISTICS:

| | |
|-----------------------------------|---|
| Clip retention | Min. 40 N (no displacement under axial force applied) |
| Contact (sleeve / clip) retention | Min. 3.3 N acc. to MIL-DTL-83734, pt 4.6.4.2 |

ELECTRICAL CHARACTERISTICS:

| | |
|---|---------------------------|
| Insulation resistance between any two adjacent contacts | Min. 10'000 M at 500 V AC |
| Capacitance between any two adjacent contacts | Max. 1 pF |

Air and creepage distances between any two adjacent contacts :

| SERIES | 3xx/4xx/7xx | 80x | 83x | 85x | 86x |
|--------|-------------|------------|-----|-----------|-----|
| mm | 0.7 | 0.85 / 0.7 | 0.5 | 0.4 / 0.5 | 0.5 |

ENVIRONMENTAL CHARACTERISTICS:

The sockets withstand the following environmental tests without mechanical and electrical defects:

- Dry heat steady state IEC 60512-11-9.11i / 60068-2-2.Bb: 125 °C, 16h
- Damp heat cyclic IEC 60512-11-12.11m / 60068-2-30.Db: 25/55 °C, 90 – 100 %rH, 1 cycle of 24 h
- Cold steady state IEC 60512-11-10.11j / 60068-2-1.A: -55 °C, 2 h
- Thermal shock IEC 60512-11-4.11d / 60068-2-14.Na: -55/125 °C, 5 cycles 30 min
- Sinusoidal vibrations IEC 60512-6-4.6d / 60068-2-6.Fc: 10 to 500 Hz, 10 g, 1 octave/min, 10 cycles for each axis
- Shock IEC 60512-6-3.6c / 60068-2-27.Ea: 50 g, 11 ms, 3 shocks in three axis

During the above two tests no contact interruption >50 ns does appear.

- Solderability J-STD-002A, Test A, 245°C, 5 s solder alloy SnAg3.8Cu0.7
- Resistance to soldering heat J-STD-0020C, 260°C, 20 s
- Moisture sensitivity J-STD-020C level 1
- Resistance to corrosion :
 - 1) Salt spray test IEC 60068-2-11.Ka: 48 h
 - 2) Sulfur dioxide (SO₂) test IEC 60068-2-42 Kc: 96 h at 25 ppm SO₂, 25 °C, 75 %rH
 - 3) Hydrogen sulfide (H₂S) test IEC 60068-2-43 Kd: 96 h at 12 ppm H₂S, 25 °C, 75 %rH

SOLDERLESS COMPLIANT PRESS-FIT CHARACTERISTICS:

PRESS-FIT CHARACTERISTICS MEASURED ACC. TO IEC 60352-5

- Press-in force: 90 N max. (at min. hole dia.) / 65 N typ.
- Push-out force: 30 N min. (at max. hole dia.) / 50 N typ.
- Push-out 3rd cycle: 20 N min. (at max. hole dia.)

PCB HOLE DIMENSIONS

- 2 mm grid: Finished hole \varnothing : $0.7 + 0.09/-0.06$ mm | Drilled hole \varnothing : 0.8 ± 0.02 mm
- 2.54 mm grid: Finished hole \varnothing : $1 + 0.09/-0.06$ mm | Drilled hole \varnothing : 1.15 ± 0.02 mm

PCB HOLE PLATING

- PCB surface finish: Hole plating
- Tin: 5-15 μm tin over min. 25 μm copper
- Copper: min. 25 μm copper
- Gold over nickel: 0.05-0.2 μm gold over 2.5-5 μm nickel over min. 25 μm copper

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Preci-dip:

[800-80-054-65-001101](#) [800-80-064-65-001101](#) [800-80-063-65-001101](#) [800-80-062-65-001101](#) [800-80-061-65-001101](#) [800-80-060-65-001101](#) [800-10-006-65-001101](#) [800-10-018-65-001101](#) [800-10-004-65-001101](#) [800-10-003-65-001101](#) [800-10-002-65-001101](#) [800-10-007-65-001101](#) [800-10-013-65-001101](#) [800-10-012-65-001101](#) [800-10-011-65-001101](#) [800-10-010-65-001101](#) [800-10-009-65-001101](#) [800-10-008-65-001101](#) [800-10-056-65-001101](#) [800-10-019-65-001101](#) [800-10-005-65-001101](#) [800-10-016-65-001101](#) [800-10-015-65-001101](#) [800-10-014-65-001101](#) [800-10-049-65-001101](#) [800-10-048-65-001101](#) [800-10-047-65-001101](#) [800-10-046-65-001101](#) [800-10-045-65-001101](#) [800-10-017-65-001101](#) [800-10-055-65-001101](#) [800-10-043-65-001101](#) [800-10-053-65-001101](#) [800-10-052-65-001101](#) [800-10-051-65-001101](#) [800-10-050-65-001101](#) [800-10-061-65-001101](#) [800-10-060-65-001101](#) [800-10-059-65-001101](#) [800-10-058-65-001101](#) [800-10-057-65-001101](#) [800-10-042-65-001101](#) [800-10-054-65-001101](#) [800-80-003-65-001101](#) [800-80-002-65-001101](#) [800-10-064-65-001101](#) [800-10-063-65-001101](#) [800-10-062-65-001101](#) [800-10-024-65-001101](#) [800-10-023-65-001101](#) [800-10-022-65-001101](#) [800-10-021-65-001101](#) [800-10-020-65-001101](#) [800-10-032-65-001101](#) [800-10-044-65-001101](#) [800-10-029-65-001101](#) [800-10-028-65-001101](#) [800-10-027-65-001101](#) [800-10-026-65-001101](#) [800-10-025-65-001101](#) [800-10-037-65-001101](#) [800-10-036-65-001101](#) [800-10-035-65-001101](#) [800-10-034-65-001101](#) [800-10-033-65-001101](#) [800-10-031-65-001101](#) [800-80-006-65-001101](#) [800-10-030-65-001101](#) [800-10-041-65-001101](#) [800-10-040-65-001101](#) [800-10-039-65-001101](#) [800-10-038-65-001101](#) [800-80-034-65-001101](#) [800-80-033-65-001101](#) [800-80-032-65-001101](#) [800-80-031-65-001101](#) [800-80-042-65-001101](#) [800-80-004-65-001101](#) [800-80-029-65-001101](#) [800-80-039-65-001101](#) [800-80-038-65-001101](#) [800-80-037-65-001101](#) [800-80-036-65-001101](#) [800-80-035-65-001101](#) [800-80-046-65-001101](#) [800-80-045-65-001101](#) [800-80-044-65-001101](#) [800-80-043-65-001101](#) [800-80-028-65-001101](#) [800-80-041-65-001101](#) [800-80-052-65-001101](#) [800-80-051-65-001101](#) [800-80-050-65-001101](#) [800-80-049-65-001101](#) [800-80-048-65-001101](#) [800-80-047-65-001101](#) [800-80-010-65-001101](#) [800-80-009-65-001101](#) [800-80-008-65-001101](#) [800-80-007-65-001101](#)