



REVISION RECORD			
REV	ECO	DESCRIPTION	DRFT DATE
Δ		Drawing Revise	Haoyh 03/18/06
Δ		增加引脚字	CSSX 12/14/06



Pitch range in mm	Normal dimension range in mm							
	over 6 to 10	over 10 to 24	over 6 to 30	over 30 to 90	over 90 to 200	over 200 to 480	over 480 to 1000	—
±0.10	±0.15	±0.25	±0.1	±0.2	±0.3	±0.5	±0.7	±0.05/10

- Notes:
1. Pitch:5.0mm
  2. Rated current:10A
  3. Rated voltage:300V
  4. Operation temperatures:-40°C~+105°C
  5. Withstanding Voltage:AC1500V/1min
  6. Insulation Resistance:5000MΩ/DC1000V
  7. Wire Range:26~14AWG, 1.5mm<sup>2</sup>
  8. Max. Torque Value:4.08kgf·cm
  9. Undimensioned Tolerances:

ITEM	NAME OF PART	QTY	MATERIAL	NOTES
4	DG126 <sup>+</sup> Screws-M2.5	XX	steel	G <sup>+</sup> Zn
3	DC306 Spring	XX	stainless steel	
2	DC306 Pin	XX	Brass	SnCe
1	DG126-5.0-Housing	1	PA66	UJ.94V-0

DEGSON		宁波高正电子有限公司	
DEGSON®		DEGSON ELECTRONICS CO., LTD.	
NAME			
DG126-5.0-XXP-1Y-00A(H)			
DRAWING NO. DG126-5.0-E02		SIZE REV	
/PART NO.		A3 T2	
DO NOT SCALE DRAWING		SHEET 1 OF 1	

DETACHED LISTS			
MM	(INCH)	MM	(INCH)
0 ±	±	±	±
.00 ±	±	±	±
.000 ±	±	±	±
ANGLES ± 1°			
THIRD ANGLE PROJECTION			
SCALE : 1:1			