



REVISION RECORD



REV	EGN	DESCRIPTION	DRFT	DATE
△		图面更新	HW	04/14/08*
△		增加COC刻字	WJM	02/02/08*
△		修改视图	LJH	05/30/08*
△		图面更新	LJH	06/11/08*
△	01-059	增加010刻字及修改参数	ZXX	10/21/08*



W/O COVER VIEW



14.1
13.2
10.3
0.50±0.05
7.62
1.5
2.54




3.5±0.3
2.54

5.08X(N-1)

- Notes:
- 1. Pitch: 5.08mm , Poles: XXP
 - 2. Rated voltage/current: UL 300V/10A VDE 250V/15A
 - 3. Operation temperatures: -40°C ~ +105°C
 - 4. Withstanding Voltage: AC2000V/1Min
 - 5. Insulation Resistance: 5000M Ω /DC1000V
 - 6. Wire Range: 22~16AWG, 0.2~1.5mm²
 - 7. Undimensioned Tolerances: ∇

Pitch range in mm	Nominal dimension in mm	over	over	over	over	over
6 to 10	30 to 60	to 10	to 60	to 100	to 150	()
10 to 24	60 to 100	to 24	to 100	to 150		▽
±0.10	±0.15	±0.25	±0.2±0.3	±0.5±0.7	±1.0	0.05/0.10

TOP VIEW-LAYOUT



ITEM	NAME OF PART	NO. OF PART	Q'TY	MATERIAL	NOTES
1	DG142V-5.08 Housing	3003A0Y01A(H)	XX	PA66	UL94V-0

DETACHED LISTS	
MM	0.0 ±
ANGLES	± 1°
THIRD ANGLE PROJECTION	
SCALE	1:1

NAME	DEGSON 宁波德正电子有限公司 DEGSON ELECTRONICS CO., LTD	
DRAWING NO.	DG142V-5.08-E13	
FINISH	/PART NO.	
DO NOT SCALE DRAWING	SHEET	1 OF 1

5	DG142 Spring	XX00000130(H)	XX	Stainless Steel	
4	DG142V Pin header	3003B00010(H)	XX	Brass	Sn6 Plate
3	DG142V-5.08 Button	3003D0501A(H)	XX	PA66	UL94V-0
2	DG142V-5.08 Cover	3003C0Y01A(H)	1	PA66	UL94V-0

8

7

6

5

4

3

2

1