



Fusible, Non-Flammable Metal Film Led Resistors



FEATURES

- Technology: metal film
- Overload protection without risk of fire
- Wide range of overload currents (refer Fusing Characteristics graphs)
- Lead (Pb)-free solder contacts
- Pure tin plating provides compatibility with lead (Pb)-free and lead containing soldering processes
- Material categorization: for definitions of compliance please see www.vishay.com/doc?99912



RoHS COMPLIANT

DESCRIPTION

A homogeneous film of metal alloy is deposited on a high grade ceramic body. After a helical groove has been cut in the resistive layer, tinned connecting wires of electrolytic copper are welded to the end-caps. The resistors are coated with a gray, flame retardant lacquer which provides electrical, mechanical, and climatic protection. The encapsulant is resistant to all cleaning solvents in accordance with IEC 60068-2-45.

APPLICATIONS

- Audio
- Video

| TECHNICAL SPECIFICATIONS | | |
|---|---|---|
| DESCRIPTION | NFR25 | NFR25H |
| Resistance range ⁽¹⁾ | 0.22 Ω to 15 kΩ | 0.22 Ω to 15 kΩ |
| Resistance tolerance | ± 5 % | ± 5 % |
| Resistance series | E24 | E24 |
| Rated dissipation P_{70} | 0.33 W | 0.5 W |
| Thermal resistance (R_{th}) | 240 K/W | 150 K/W |
| Temperature coefficient 0.22 Ω ≤ R ≤ 4.7 Ω 4.7 Ω ≤ R ≤ 15 Ω 15 Ω ≤ R ≤ 15 kΩ | ≤ ± 200 ppm/K ≤ ± 200 ppm/K ≤ ± 100 ppm/K | ≤ ± 200 ppm/K ≤ ± 100 ppm/K ≤ ± 100 ppm/K |
| Operating voltage, U_{max} . DC or RMS | 250 V | 350 V |
| Basic specifications | IEC 60 115-1 | IEC 60 115-1 |
| Climatic category (IEC 60068-1) | 55/155/56 | 55/155/56 |
| Maximum resistance change for resistance range, ΔR max., after: | | |
| Load (1000 h, P_{70}): | ± (1 % R + 0.05 Ω) | ± (1 % R + 0.05 Ω) |
| Long term damp heat test (56 days): | ± (1 % R + 0.05 Ω) | ± (1 % R + 0.05 Ω) |
| Soldering (260 °C, 10 s): | ± (0.25 % R + 0.05 Ω) | ± (0.25 % R + 0.05 Ω) |

Notes

- R value is measured with probe distance of 24 mm ± 1 mm using 4-terminal method
- ⁽¹⁾ Ohmic values (other than resistance range) are available on request

| PACKAGING | | | | | |
|---------------|--------------|----------|------|--------|------|
| MODEL | TAPING | AMMOPACK | | REEL | |
| | | PIECES | CODE | PIECES | CODE |
| NFR25, NFR25H | Axial, 52 mm | 5000 | A5 | 5000 | R5 |
| | | 1000 | A1 | | |
| NFR25, NFR25H | Radial | 2000 | N2 | - | - |

DIMENSIONS


| DIMENSIONS (Resistor types, mass, and relevant physical dimensions) | | | | | |
|---|------------------------|--------------------------|--------------------------|-------------|-----------|
| TYPE | D _{max.} (mm) | L ₁ max. (mm) | L ₂ max. (mm) | Ø d (mm) | MASS (mg) |
| NFR25 | 2.5 | 6.5 | 7.5 | 0.58 ± 0.05 | 201 |
| NFR25H | | | | | |

| PART NUMBER AND PRODUCT DESCRIPTION | | | | | | |
|---------------------------------------|---|--------------------------|--|-----------|--------------------------|---|
| Part Number: NFR250002207JA100 | | | | | | |
| N | F | R | 2 | 5 | 0 | 0 |
| 0 | 0 | 0 | 0 | 2 | 2 | 0 |
| 7 | J | A | 1 | 0 | 0 | |
| MODEL/SIZE | VARIANT | TCR/MATERIAL | VALUE | TOLERANCE | PACKAGING ⁽¹⁾ | SPECIAL |
| NFR2500 NFR25H0 | 0 = neutral Z = value overload (special) | 0 = standard | 3 digit value 1 digit multiplier MULTIPLIER 7 = *10 ⁻³ 8 = *10 ⁻² 9 = *10 ⁻¹ 0 = *10 ⁰ 1 = *10 ¹ 2 = *10 ² | J = ± 5 % | N2 A5 A1 R5 | Up to 2 digits are used for all special parts. 00 = standard |
| Product Description: NFR25 5 % A1 R22 | | | | | | |
| NFR25 | 5 % | A1 | R22 | | | |
| MODEL / SIZE | TOLERANCE | PACKAGING ⁽¹⁾ | RESISTANCE VALUE | | | |
| NFR25 NFR25H | ± 5 % | N2 A5 A1 R5 | 1K0 = 1 kΩ 4R7 = 4.7 Ω | | | |

Notes

- The PART NUMBER is shown to facilitate the introduction of the unified part numbering system
- ⁽¹⁾ Please refer to table PACKAGING, see next page

PRODUCTS WITH RADIAL LEADS (NFR25, NFR25H)


| DIMENSIONS (Radial taping) | | | | |
|----------------------------|---|-------|-------------|------|
| SYMBOL | PARAMETER | VALUE | TOLERANCE | UNIT |
| P | Pitch of components | 12.7 | ± 1.0 | mm |
| P ₀ | Feed-hole pitch | 12.7 | ± 0.2 | mm |
| P ₁ | Feed-hole center to lead at topside at the tape | 3.85 | ± 0.5 | mm |
| P ₂ | Feed-hole center to body center | 6.35 | ± 1.0 | mm |
| F | Lead-to-lead distance | 4.8 | + 0.7 / - 0 | mm |
| W | Tape width | 18.0 | ± 0.5 | mm |
| W ₀ | Minimum hold down tape width | 5.5 | - | mm |
| H ₁ | Component height | 29.0 | Max. | mm |
| H ₀ | Lead wire clinch height | 16.5 | ± 0.5 | mm |
| H | Height of component from tape center | 19.5 | ± 1 | mm |
| D ₀ | Feed-hole diameter | 4.0 | ± 0.2 | mm |
| L | Maximum length of snapped lead | 11.0 | - | mm |
| L ₁ | Minimum lead wire (tape portion) shortest lead | 2.5 | - | mm |

Note

- Please refer document number 28721 "Packaging" for more detail

MARKING

The nominal resistance and tolerance are marked on the resistor using four colored bands in accordance with IEC 60062, marking codes for resistors and capacitors. For ease of recognition a fifth ring is added, which is violet for type NFR25 and white for type NFR25H.

OUTLINES

The length of the body (L₁) is measured by inserting the leads into holes of two identical gauge plates and moving these plates parallel to each other until the resistor body is clamped without deformation (IEC 60294).

FUNCTIONAL PERFORMANCE, PRODUCT CHARACTERIZATION

Standard values of nominal resistance are taken from the E24 series for resistors with a tolerance of ± 5 %.

The values of the E24 series are in accordance with IEC 60063.

| LIMITING VALUES | | |
|-----------------|-----------------------------------|--------------------------------|
| TYPE | LIMITING VOLTAGE $U^{(1)}$ (V) | LIMITING POWER P_{70} (W) |
| NFR25 | 250 | 0.33 |
| NFR25H | 350 | 0.5 |


Note

- (1) The maximum voltage that may be continuously applied to the resistor element, see IEC 60115-1. The maximum permissible hot-spot temperature is 155 °C.



DERATING

The power that the resistor can dissipate depends on the operating temperature.




Maximum dissipation (P_{max}) in percentage of rated power as a function of the ambient temperature (T_{amb})


FUSING CHARACTERISTICS

The resistors will fuse without the risk of fire and within an indicated range of overload. Fusing means that the resistive value of the resistor increases at least 100 times.

The fusing characteristic is measured under constant voltage.



NFR25 This graph is based on measured data which may deviate according to the application.
Fusing Characteristics: $\leq 1 \Omega$



NFR25 This graph is based on measured data which may deviate according to the application.
Fusing Characteristics: $1 \Omega \leq R \leq 15 \Omega$




NFR25 This graph is based on measured data which may deviate according to the application.
Fusing Characteristics: $15 \Omega \leq R \leq 15 k\Omega$



FUSING CHARACTERISTICS



NFR25H This graph is based on measured data which may deviate according to the application.
Fusing Characteristics: $\leq 1 \Omega$




NFR25H This graph is based on measured data which may deviate according to the application.
Fusing Characteristics: $1 \Omega \leq R \leq 15 \text{ k}\Omega$

PULSE LOADING CAPABILITIES




NFR25 Pulse on a regular basis; maximum permissible peak pulse power (\hat{P}_{max}) as a function of pulse duration (t_i), $0.22 \Omega \leq R \leq 1 \text{ k}\Omega$




NFR25 Pulse on a regular basis; maximum permissible peak pulse power (\hat{P}_{max}) as a function of pulse duration (t_i), $15 \Omega \leq R \leq 15 \text{ k}\Omega$




PULSE LOADING CAPABILITIES



NFR25 Pulse on a regular basis; maximum permissible peak pulse power (\hat{U}_{max}) as a function of pulse duration (t_i)



NFR25H Pulse on a regular basis; maximum permissible peak pulse power (\hat{P}_{max}) as a function of pulse duration (t_i)



NFR25H Pulse on a regular basis; maximum permissible peak pulse power (\hat{P}_{max}) as a function of pulse duration (t_i)



APPLICATION INFORMATION



NFR25 Hot-spot temperature rise (ΔT) as a function of dissipated power



NFR25H Hot-spot temperature rise (ΔT) as a function of dissipated power



Minimum distance from resistor body to PCB. = 1 mm

NFR25 Temperature rise (ΔT) at the lead end (soldering point) as a function of dissipated power at various lead lengths after mounting



Minimum distance from resistor body to PCB. = 1 mm

NFR25H Temperature rise (ΔT) at the lead end (soldering point) as a function of dissipated power at various lead lengths after mounting

TESTS AND REQUIREMENTES

Essentially all tests are carried out in accordance with IEC 60115-1 specification, category LCT/UCT/56 (rated temperature range: Lower category temperature, upper category temperature; damp heat, long term, 56 days). The tests are carried out in accordance with IEC 60068-2-xx test method, "Recommended basic climatic and mechanical robustness testing procedure for electronic components" and under standard atmospheric conditions according to IEC 60068-1, 5.3.

In the Test Procedures and Requirements table the tests and requirements are listed with reference to the relevant clauses of IEC 60115-1 and IEC 60068-2-xx test methods. A short description of the test procedure is also given. In some instances deviations from the IEC recommendations were necessary for our method of specifying. For inflammability requirements reference is made to IEC 60115-1. All soldering tests are performed with mildly activated flux.



| TEST PROCEDURES AND REQUIREMENTS | | | | | |
|----------------------------------|-------------------------|--|---|--|--|
| IEC 60115-1 CLAUSE | IEC 60068-2 TEST METHOD | TEST | PROCEDURE | REQUIREMENTS | |
| | | | | NFR25 | NFR25H |
| 4.4.1 | | Visual examination | | No holes; clean surface; no damage | |
| 4.4.2 | | Dimensions (outline) | Gauge (mm) | See Dimensions Table | |
| 4.5 | | Resistance (refer note on first page for measuring distance) | Applied voltage (+ 0 % / - 10 %): $R < 10 \Omega$: 0.1 V $10 \Omega \leq R < 100 \Omega$: 0.3 V $100 \Omega \leq R < 1 \text{ k}\Omega$: 1 V $1 \text{ k}\Omega \leq R < 10 \text{ k}\Omega$: 3 V $10 \text{ k}\Omega \leq R \leq 15 \text{ k}\Omega$: 10 V | $R - R_{\text{nom}}$: max. $\pm 5 \%$ | |
| 4.18 | 20 (Tb) | Resistance to soldering heat | Thermal shock: 10 s; 260 °C; 3 mm from body | ΔR max.: $\pm (0.25 \% R + 0.05 \Omega)$ | |
| 4.29 | 45 (Xa) | Component solvent resistance | Isopropyl alcohol or H ₂ O followed by brushing | No visual damage | |
| 4.17 | 20 (Ta) | Solderability | 2 s; 235 °C: Solder bath method; SnPb40 3 s; 245 °C: Solder bath method; SnAg3Cu0.5 | Good tinning ($\geq 95 \%$ covered); no damage | |
| | | Solderability (after aging) | 8 h steam or 16 h, 155 °C; leads immersed 6 mm; for 2 s at 235 °C: Solder bath (SnPb40) for 3 s at 245 °C: Solder bath (SnAg3Cu0.5) method | Good tinning ($\geq 95 \%$ covered); no damage | |
| 4.7 | | Voltage proof on insulation | $U_{\text{RMS}} = 500 \text{ V}$ during 1 min; metal block method | No breakdown or flashover | |
| 4.16 | | Robustness of terminations: | | | |
| 4.16.2 | 21 (Ua1) | Tensile all samples | Load 10 N; 10 s | Number of failures $< 10 \times 10^{-6}$ | |
| 4.16.3 | 21 (Ub) | Bending half number of samples | Load 5 N; 4 x 90° | Number of failures $< 10 \times 10^{-6}$ | |
| 4.16.4 | 21 (Uc) | Torsion other half of samples | 3 x 360° in opposite directions | No damage ΔR max.: $\pm (0.25 \% R + 0.05 \Omega)$ | |
| 4.20 | 29 (Eb) | Bump | 3 x 1500 bumps in 3 directions; 40 g | No damage ΔR max.: $\pm (0.25 \% R + 0.05 \Omega)$ | |
| 4.22 | 6 (Fc) | Vibration | Frequency 10 Hz to 500 Hz; displacement 1.5 mm or acceleration 10 g; 3 directions; total 6 h (3 x 2 h) | No damage ΔR max.: $\pm (0.25 \% R + 0.05 \Omega)$ | |
| 4.19 | 14 (Na) | Rapid change of temperature | 30 min at LCT and 30 min at UCT; 5 cycles | No visual damage ΔR max.: $\pm (0.25 \% R + 0.05 \Omega)$ | |
| 4.23 | | Climatic sequence: | | | |
| 4.23.2 | 2 (Ba) | Dry heat | 16 h; 155 °C | | |
| 4.23.3 | 30 (Db) | Damp heat (accelerated) 1 st cycle | 24 h; 55 °C; 90 % to 100 % RH | | |
| 4.23.4 | 1 (Aa) | Cold | 2 h; -55 °C | | |
| 4.23.5 | 13 (M) | Low air pressure | 2 h; 8.5 kPa; 15 °C to 35 °C | | |
| 4.23.6 | 30 (Db) | Damp heat (accelerated) remaining cycles | 5 days; 55 °C; 95 % to 100 % RH | R_{ins} min. $10^3 \text{ M}\Omega$ ΔR max.: $\pm (1.5 \% R + 0.1 \Omega)$ | |
| 4.24 | 78 (Cab) | Damp heat (steady state) | 56 days; 40 °C; 90 % to 95 % RH; loaded with 0.01 P_{70} (IEC steps: 0 V to 100 V) | R_{ins} min. $10^3 \text{ M}\Omega$ ΔR max.: $\pm (1 \% R + 0.05 \Omega)$ | |
| 4.25.1 | | Endurance (at 70 °C) | 1000 h; loaded with P_{70} or U_{max} ; 1.5 h ON and 0.5 h OFF | ΔR max.: $\pm (1 \% R + 0.05 \Omega)$ | |
| 4.25.3 | | Endurance at upper category temperature | 1000 h; no load | ΔR max.: $\pm (1 \% R + 0.05 \Omega)$ | |
| 4.8 | | Temperature coefficient | Between -55 °C and +155 °C $0.22 \Omega \leq R \leq 4.7 \Omega$ $4.7 \Omega < R \leq 15 \Omega$ $15 \Omega < R \leq 15 \text{ k}\Omega$ | $\leq \pm 200 \text{ ppm/K}$ $\leq \pm 200 \text{ ppm/K}$ $\leq \pm 100 \text{ ppm/K}$ | $\leq \pm 200 \text{ ppm/K}$ $\leq \pm 100 \text{ ppm/K}$ $\leq \pm 100 \text{ ppm/K}$ |
| 4.12 | | Noise | IEC 60195 | $< 0.1 \mu\text{V/V}$ | |
| 4.26 | | Accidental overload | Cheese-cloth | Non flammable | |
| 4.6.1.1 | | Insulation resistance | Maximum voltage U_{max} , DC = 500 V after 1 min; metal block method | R_{ins} min. $10^4 \text{ M}\Omega$ | |



12NC INFORMATION FOR HISTORICAL CODING REFERENCE

- The resistors have a 12 digit numeric code starting with 23
- The subsequent 7 digits indicate the resistor type and packaging
- The remaining 3 digits indicate the resistance value:
 - The first 2 digits indicate the resistance value
 - The last digit indicates the resistance decade

Last Digit of 12NC Indicating Resistance Decade

| RESISTANCE DECADE | LAST DIGIT |
|-------------------|------------|
| 0.22 Ω to 0.91 Ω | 7 |
| 1 Ω to 9.1 Ω | 8 |
| 10 Ω to 91 Ω | 9 |
| 100 Ω to 910 Ω | 1 |
| 1 kΩ to 9.1 kΩ | 2 |
| 10 kΩ to 15 kΩ | 3 |

12NC Example

The 12NC of a NFR25 resistor with value 750 Ω, supplied on a bandolier of 1000 units in ammopack is: 2322 205 13751.

| 12NC (Resistors Type and Packaging) | | | | |
|-------------------------------------|-----------------------|----------------|--------------|-------------------|
| TYPE | 23.. | | | |
| | BANDOLIER IN AMMOPACK | | | BANDOLIER ON REEL |
| | RADIAL TAPED | STRAIGHT LEADS | | STRAIGHT LEADS |
| | 2000 UNITS | 1000 UNITS | 5000 UNITS | 5000 UNITS |
| NFR25 | 22 204 03... | 22 205 13... | 22 205 33... | 22 205 23... |
| NFR25H | 22 207 03... | 22 207 13... | 22 207 33... | 22 207 23... |



Disclaimer

ALL PRODUCT, PRODUCT SPECIFICATIONS AND DATA ARE SUBJECT TO CHANGE WITHOUT NOTICE TO IMPROVE RELIABILITY, FUNCTION OR DESIGN OR OTHERWISE.

Vishay Intertechnology, Inc., its affiliates, agents, and employees, and all persons acting on its or their behalf (collectively, "Vishay"), disclaim any and all liability for any errors, inaccuracies or incompleteness contained in any datasheet or in any other disclosure relating to any product.

Vishay makes no warranty, representation or guarantee regarding the suitability of the products for any particular purpose or the continuing production of any product. To the maximum extent permitted by applicable law, Vishay disclaims (i) any and all liability arising out of the application or use of any product, (ii) any and all liability, including without limitation special, consequential or incidental damages, and (iii) any and all implied warranties, including warranties of fitness for particular purpose, non-infringement and merchantability.

Statements regarding the suitability of products for certain types of applications are based on Vishay's knowledge of typical requirements that are often placed on Vishay products in generic applications. Such statements are not binding statements about the suitability of products for a particular application. It is the customer's responsibility to validate that a particular product with the properties described in the product specification is suitable for use in a particular application. Parameters provided in datasheets and / or specifications may vary in different applications and performance may vary over time. All operating parameters, including typical parameters, must be validated for each customer application by the customer's technical experts. Product specifications do not expand or otherwise modify Vishay's terms and conditions of purchase, including but not limited to the warranty expressed therein.

Hyperlinks included in this datasheet may direct users to third-party websites. These links are provided as a convenience and for informational purposes only. Inclusion of these hyperlinks does not constitute an endorsement or an approval by Vishay of any of the products, services or opinions of the corporation, organization or individual associated with the third-party website. Vishay disclaims any and all liability and bears no responsibility for the accuracy, legality or content of the third-party website or for that of subsequent links.

Except as expressly indicated in writing, Vishay products are not designed for use in medical, life-saving, or life-sustaining applications or for any other application in which the failure of the Vishay product could result in personal injury or death. Customers using or selling Vishay products not expressly indicated for use in such applications do so at their own risk. Please contact authorized Vishay personnel to obtain written terms and conditions regarding products designed for such applications.

No license, express or implied, by estoppel or otherwise, to any intellectual property rights is granted by this document or by any conduct of Vishay. Product names and markings noted herein may be trademarks of their respective owners.