



## Precision Metal Film Leaded Resistors



### FEATURES

- IECQ-CECC approved according to EN 140101-806
- Superior overall stability: class 0.05
- Wide precision ohmic range: 10 Ω to 1.5 MΩ
- Radial version available for MBB/SMA 0207
- Material categorization: for definitions of compliance please see [www.vishay.com/doc?99912](http://www.vishay.com/doc?99912)



**RoHS**  
COMPLIANT  
HALOGEN  
**FREE**

### APPLICATIONS

- Test and measuring equipment
- Industrial electronics
- Medical electronics

### DESIGN SUPPORT TOOLS

[click logo to get started](#)

**3D**  
Models  
Available

### DESCRIPTION

MBA/SMA 0204, MBB/SMA 0207, and MBE/SMA 0414 precision led thin film resistors combine the proven reliability of the professional products with an advanced level of precision and stability. Therefore they are perfectly suited for applications in the fields of test and measuring equipment along with industrial and medical electronics.

TECHNICAL SPECIFICATIONS			
DESCRIPTION	MBA/SMA 0204	MBB/SMA 0207	MBE/SMA 0414
DIN size	0204	0207	0414
CECC size	A	B	D
Resistance range	22 Ω to 332 kΩ	10 Ω to 1 MΩ	22 Ω to 1.5 MΩ
Resistance tolerance	± 0.25 %; ± 0.1 %		
Temperature coefficient	± 25 ppm/K; ± 15 ppm/K		
Rated dissipation, $P_{70}$	0.25 W	0.40 W	0.65 W
Operating voltage, $U_{max}$ . AC/DC	200 V	350 V	500 V
Operating temperature range <sup>(1)</sup>	-55 °C to +125 °C		
Peak permissible film temperature <sup>(1)</sup>	125 °C	125 °C	125 °C
Insulation voltage:	1 min; $U_{ins}$	300 V	500 V
	Continuous	75 V	75 V
Failure rate: FIT <sub>observed</sub>	≤ 0.1 x 10 <sup>-9</sup> /h		

### Notes

- MB\_ series has been merged with the related SMA series to form one series "MB\_/SMA\_"
- <sup>(1)</sup> Please refer to APPLICATION INFORMATION below

**APPLICATION INFORMATION**

The power dissipation on the resistor generates a temperature rise against the local ambient, depending on the heat flow support of the printed-circuit board (thermal resistance). The rated dissipation applies only if the permitted film temperature is not exceeded. Furthermore, a high level of ambient temperature or of power dissipation may raise the temperature of the solder joint, hence special solder alloys or board materials may be required to maintain the reliability of the assembly.

These resistors do not feature a limited lifetime when operated within the permissible limits. However, resistance value drift increasing over operating time may result in exceeding a limit acceptable to the specific application, thereby establishing a functional lifetime. The designer may estimate the performance of the particular resistor application or set certain load and temperature limits in order to maintain a desired stability.

<b>MAXIMUM RESISTANCE CHANGE AT RATED DISSIPATION</b>				
Operation mode		Precision	Standard	
Climatic category		-10 °C / +85 °C / 56 days	-55 °C / +125 °C / 56 days	
Rated dissipation, $P_{70}$	MBA/SMA 0204	0.07 W	0.25 W	
	MBB/SMA 0207	0.11 W	0.40 W	
	MBE/SMA 0414	0.17 W	0.65 W	
Applied maximum film temperature, $\vartheta_{F \text{ max.}}$		85 °C	125 °C	
Max. resistance change at rated dissipation $ \Delta R/R \text{ max.} $ , after:	MBA/SMA 0204	100 $\Omega$ to 100 k $\Omega$	100 $\Omega$ to 100 k $\Omega$	
		1000 h	$\leq 0.05 \%$	$\leq 0.25 \%$
		8000 h	$\leq 0.1 \%$	$\leq 0.5 \%$
	MBB/SMA 0207	100 $\Omega$ to 270 k $\Omega$	100 $\Omega$ to 270 k $\Omega$	100 $\Omega$ to 270 k $\Omega$
		1000 h	$\leq 0.03 \%$	$\leq 0.15 \%$
		8000 h	$\leq 0.1 \%$	$\leq 0.5 \%$
	MBE/SMA 0414	100 $\Omega$ to 470 k $\Omega$	100 $\Omega$ to 470 k $\Omega$	100 $\Omega$ to 470 k $\Omega$
		1000 h	$\leq 0.05 \%$	$\leq 0.25 \%$
		8000 h	$\leq 0.1 \%$	$\leq 0.5 \%$
		225 000 h	$\leq 0.3 \%$	$\leq 1.5 \%$

<b>TEMPERATURE COEFFICIENT AND RESISTANCE RANGE</b>				
TYPE	TCR	TOLERANCE	RESISTANCE <sup>(1)</sup>	E-SERIES
MBA/SMA 0204	$\pm 25 \text{ ppm/K}$	$\pm 0.25 \%$	22 $\Omega$ to 332 k $\Omega$	E96; E192
		$\pm 0.1 \%$	43 $\Omega$ to 332 k $\Omega$	E96; E192
	$\pm 15 \text{ ppm/K}$	$\pm 0.25 \%$	22 $\Omega$ to 221 k $\Omega$	E96; E192
		$\pm 0.1 \%$	43 $\Omega$ to 221 k $\Omega$	E96; E192
MBB/SMA 0207	$\pm 25 \text{ ppm/K}$	$\pm 0.25 \%$	10 $\Omega$ to 1 M $\Omega$	E96; E192
		$\pm 0.1 \%$	10 $\Omega$ to 1 M $\Omega$	E96; E192
	$\pm 15 \text{ ppm/K}$	$\pm 0.25 \%$	10 $\Omega$ to 1 M $\Omega$	E96; E192
		$\pm 0.1 \%$	10 $\Omega$ to 1 M $\Omega$	E96; E192
MBE/SMA 0414	$\pm 25 \text{ ppm/K}$	$\pm 0.25 \%$	22 $\Omega$ to 1.5 M $\Omega$	E96; E192
		$\pm 0.1 \%$	43 $\Omega$ to 1 M $\Omega$	E96; E192
	$\pm 15 \text{ ppm/K}$	$\pm 0.25 \%$	22 $\Omega$ to 1 M $\Omega$	E96; E192
		$\pm 0.1 \%$	43 $\Omega$ to 1 M $\Omega$	E96; E192

**Notes**

- Radial version (RB, UB) cannot be qualified according to CECC so these can only be ordered with variant N or S

<sup>(1)</sup> Approval is according to EN 140101-806, version A



**PART NUMBER AND PRODUCT DESCRIPTION - CECC APPROVED PRODUCTS**

PART NUMBER: MBB0207VD1001BCT00

M	B	B	0	2	0	7	V	D	1	0	0	1	B	C	T	0	0
---	---	---	---	---	---	---	---	---	---	---	---	---	---	---	---	---	---

<b>TYPE / SIZE</b> <b>MBA0204</b> = MBA/SMA 0204 <b>MBB0207</b> = MBB/SMA 0207 <b>MBE0414</b> = MBE/SMA 0414	<b>VARIANT</b> <b>V</b> = CECC 06 <b>N</b> = RB radial 5 mm for MBB/SMA 0207 <b>S</b> = UB radial 2.5 mm for MBB/SMA 0207	<b>TCR</b> <b>E</b> = ± 15 ppm/K <b>D</b> = ± 25 ppm/K	<b>RESISTANCE</b> <b>3 digit value</b> <b>1 digit multiplier</b> <b>MULTIPLIER</b> 8 = *10 <sup>-2</sup> 2 = *10 <sup>2</sup> 9 = *10 <sup>-1</sup> 3 = *10 <sup>3</sup> 0 = *10 <sup>0</sup> 4 = *10 <sup>4</sup> 1 = *10 <sup>1</sup> 5 = *10 <sup>5</sup>	<b>TOLERANCE</b> <b>B</b> = ± 0.1 % <b>C</b> = ± 0.25 %	<b>PACKAGING</b> <b>CT</b> <b>C1</b> <b>N4</b>	<b>Special</b> <b>00</b> = standard  <b>L0</b> = welding joint not lacquered for MBB/SMA 0207 <b>KL</b> = lacquered welding joint for MBA/SMA 0204
--	--	--	---	---	---	--

PRODUCT DESCRIPTION: MBB/SMA 0207-25 0.1 % CECC 06 CT 1K0

<b>MBB/SMA 0207</b>	-	<b>25</b>	<b>0.1 %</b>	<b>CECC 06</b>	<b>CT</b>	<b>1K0</b>
<b>TYPE / SIZE</b> <b>MBA/SMA 0204</b> <b>MBB/SMA 0207</b> <b>MBE/SMA 0414</b>		<b>TCR</b> ± 15 ppm/K ± 25 ppm/K	<b>TOLERANCE</b> ± 0.1 % ± 0.25 %	<b>VARIANT</b> <b>CECC 06</b> <b>CECC 06 L0</b> <b>CECC 06 KL</b>	<b>PACKAGING</b> <b>CT</b> <b>C1</b> <b>N4</b>	<b>RESISTANCE</b> <b>1K0</b> = 1 kΩ <b>51R1</b> = 51.1 Ω

**Note**

- The products can be ordered using either the PRODUCT DESCRIPTION or the PART NUMBER

**PACKAGING**

TYPE	CODE	QUANTITY	PACKAGING STYLE	WIDTH	PITCH	DIMENSIONS
MBA/SMA 0204	C1	1000	Taped acc. to IEC 60286-1 fan-folded in a box	53 mm	5 mm	184 mm x 75 mm x 42 mm
	CT	5000				330 mm x 75 mm x 55 mm
MBB/SMA 0207	C1	1000	Taped acc. to IEC 60286-1 fan-folded in a box	53 mm	5 mm	184 mm x 74 mm x 42 mm
	CT	5000				324 mm x 77 mm x 82 mm
MBB/SMA 0207 UB = 2.5 mm pitch	N4	4000	Taped acc. to IEC 60286-2 fan-folded in a box	-	12.7 mm	330 mm x 262 mm x 45 mm
	R4	4000	Taped acc. to IEC 60286-2 on a reel	-		330 mm x 253 mm x 48 mm
MBB/SMA 0207 UB = 5.0 mm pitch	N4	4000	Taped acc. to IEC 60286-2 fan-folded in a box	-		330 mm x 262 mm x 45 mm
	R4	4000	Taped acc. to IEC 60286-2 on a reel	-		330 mm x 253 mm x 48 mm
MBE/SMA 0414	C1	1000	Taped acc. to IEC 60286-1 fan-folded in a box	63 mm	5 mm	374 mm x 84 mm x 47 mm

**Note**

- For details related to packaging specs, refer datasheet link [www.vishay.com/doc?28721](http://www.vishay.com/doc?28721)



## DESCRIPTION

Production is strictly controlled and follows an extensive set of instructions established for reproducibility. A homogeneous film of metal alloy is deposited on a high grade ceramic body and conditioned to achieve the desired temperature coefficient. Plated steel termination caps are firmly pressed on the metallized rods. A special laser is used to achieve the target value by smoothly cutting a helical groove in the resistive layer without damaging the ceramics. Connecting wires of electrolytic copper plated with 100 % pure tin are welded to the termination caps. The resistor elements are covered by a light blue protective coating designed for electrical, mechanical and climatic protection. Four or five color code rings designate the resistance value and tolerance in accordance with **IEC 60062**.

The result of the determined production is verified by an extensive testing procedure performed on 100 % of the individual resistors. Only accepted products are stuck directly on the adhesive tapes in accordance with **IEC 60286-1** or for the radial versions in accordance to **IEC 60286-2**.

## MATERIALS

Vishay acknowledges the following systems for the regulation of hazardous substances:

- IEC 62474, Material Declaration for Products of and for the Electrotechnical Industry, with the list of declarable substances given therein <sup>(1)</sup>
- The Global Automotive Declarable Substance List (GADSL) <sup>(2)</sup>
- The REACH regulation (1907/2006/EC) and the related list of substances with very high concern (SVHC) <sup>(3)</sup> for its supply chain

The products do not contain any of the banned substances as per IEC 62474, GADSL, or the SVHC list, see [www.vishay.com/how/leadfree](http://www.vishay.com/how/leadfree).

Hence the products fully comply with the following directives:

- 2000/53/EC End-of-Life Vehicle Directive (ELV) and Annex II (ELV II)
- 2011/65/EU Restriction of the Use of Hazardous Substances Directive (RoHS) with amendment 2015/863/EU
- 2012/19/EU Waste Electrical and Electronic Equipment Directive (WEEE)

Vishay pursues the elimination of conflict minerals from its supply chain, see the Conflict Minerals Policy at [www.vishay.com/doc?49037](http://www.vishay.com/doc?49037).

## Notes

- <sup>(1)</sup> Global Automotive Declarable Substance List, see [www.gadsl.org](http://www.gadsl.org)
- <sup>(2)</sup> CEFIC (European Chemical Industry Council), EECA (European Electronic Component Manufacturers Association), EICTA (European trade organisation representing the information and communications technology and consumer electronics), see [www.digitaleurope.org/SearchResults.aspx?Search=eicta](http://www.digitaleurope.org/SearchResults.aspx?Search=eicta). All products comply with the IEC 62474, Material Declaration for Products of and for the Electrotechnical Industry
- <sup>(3)</sup> Other cleaning solvents with aggressive chemicals should be evaluated in actual cleaning process for their suitability

## ASSEMBLY

The resistors are suitable for processing on automatic insertion equipment and cutting and bending machines. Excellent solderability is proven, even after extended storage. They are suitable for automatic soldering using wave or dipping.

The resistors are completely lead (Pb)-free, the pure tin plating provides compatibility with lead (Pb)-free and lead-containing soldering processes. The immunity of the plating against tin whisker growth, in compliance with IEC 60068-2-82, has been proven under extensive testing.

The encapsulant is resistant to cleaning solvent specified in IEC 60115-1 <sup>(3)</sup>. The suitability of conformal coatings, if applied, shall be qualified by appropriate means to ensure the long-term stability of the whole system.

All products comply with **GADSL** <sup>(1)</sup> and the **IEC 62474** <sup>(2)</sup> list of legal restrictions on hazardous substances. This includes full compliance with the following directives:

- 2000/53/EC End of Vehicle Life Directive (ELV) and Annex II (ELVII)
- 2011/65/EU Restriction of the use of Hazardous Substances Directive (RoHS)
- 2002/96/EC Waste Electrical and Electrical Equipment Directive (WEEE)

## APPROVALS

The resistors (CECC version) are approved within the IECQ-CECC Quality Assessment System for Electronic Components to the detail specification EN 140101-806 which refers to **EN 60115-1** and **EN 140100 and the variety of environmental test procedures of the IEC 60068 series**. Conformity is attested by the use of the CECC logo (E) as the Mark of Conformity on the package label for the CECC version.

Vishay Beyschlag has achieved “**Approval of Manufacturer**” in accordance with **IEC QC 001002-3, clause 2**. The release certificate for “**Technology Approval Schedule**” in accordance with **CECC 240001** based on **IEC QC 001002-3, clause 6** is granted for the Vishay Beyschlag manufacturing process.

## RELATED PRODUCTS

For a correlated range of professional TCR and tolerance specifications see the datasheet:

- “Professional Thin Film Leaded Resistors”, [www.vishay.com/doc?28766](http://www.vishay.com/doc?28766)

For products approved to EN 140101-806, version E, with established reliability and failure rate level E7 (Quality factor  $\pi Q = 0.1$ ), see the datasheet:

- “Established Reliability Thin Film Leaded Resistors”, [www.vishay.com/doc?28768](http://www.vishay.com/doc?28768)



FUNCTIONAL PERFORMANCE



Derating



Rise of the surface temperature.

Temperature Rise



Current Noise A1 in accordance with IEC 60195



**TEST PROCEDURES AND REQUIREMENTS**

Essentially all tests are carried out in accordance with the following specifications:

- EN 60115-1, Generic specification (includes tests)
- EN 140100, Sectional specification (includes schedule for qualification approval)
- EN 140101-806 (successor of CECC 40101-806), Detail specification (includes schedule for conformance inspection)

Most of the components are approved in accordance with the European CECC-system, where applicable. The Test Procedures and Requirements table contains only the most important tests. For the full test schedule refer to the documents listed above. The testing also covers most of the requirements specified by EIA/IS-703 and JIS-C-5202.

The tests are carried out in accordance with IEC 60068-2-xx test method and under standard atmospheric conditions in

accordance with IEC 60068-1, 5.3. Climatic category LCT/UCT/56 (rated temperature range: Lower category temperature, upper category temperature; damp heat, steady state, test duration: 56 days) is valid.

Unless otherwise specified the following values apply:

- Temperature: 15 °C to 35 °C
- Relative humidity: 45 % to 75 %
- Air pressure: 86 kPa to 106 kPa (860 mbar to 1060 mbar).

For testing the components are mounted on a test board in accordance with IEC 60115-1, 4.31 unless otherwise specified.

In the Test Procedures and Requirements table, only the tests and requirements are listed with reference to the relevant clauses of IEC 60115-1 and IEC 60068-2-xx test methods. A short description of the test procedure is also given.

TEST PROCEDURES AND REQUIREMENTS						
IEC 60115-1 CLAUSE	IEC 60068-2 TEST METHOD	TEST	PROCEDURE	REQUIREMENTS PERMISSIBLE CHANGE ( $\Delta R$ max.)		
			Stability for product types:	STABILITY CLASS 0.05	STABILITY CLASS 0.1	STABILITY CLASS 0.25
			<b>MBA/SMA 0204</b>	100 $\Omega$ to 100 k $\Omega$	43 $\Omega$ to 221 k $\Omega$	22 $\Omega$ to 332 k $\Omega$
			<b>MBB/SMA 0207</b>	100 $\Omega$ to 270 k $\Omega$	43 $\Omega$ to 510 k $\Omega$	22 $\Omega$ to 1 M $\Omega$
			<b>MBE/SMA 0414</b>	100 $\Omega$ to 470 k $\Omega$	43 $\Omega$ to 1 M $\Omega$	22 $\Omega$ to 1.5 M $\Omega$
4.5	-	Resistance	-	$\pm 0.25\%$ ; $\pm 0.1\%$		
4.7	-	Voltage proof	$U_{RMS} = U_{ins}$ ; 60 s	No flashover or breakdown		
4.8	-	Temperature coefficient	At 20/LCT/20 °C and 20/UCT/20 °C	$\pm 25$ ppm/K; $\pm 15$ ppm/K		
4.13	-	Short time overload	Room temperature; $U = 2.5 \times \sqrt{P_{70} \times R}$ or $U = 2 \times U_{max}$ ; 5 s	$\pm (0.01\% R + 0.01 \Omega)$ no visible damage	$\pm (0.02\% R + 0.01 \Omega)$ no visible damage	$\pm (0.05\% R + 0.01 \Omega)$ no visible damage
4.16	21 (Ua <sub>1</sub> ) 21 (Ub) 21 (Uc)	Robustness of terminations	Tensile, bending and torsion	$\pm (0.01\% R + 0.01 \Omega)$	$\pm (0.02\% R + 0.01 \Omega)$	$\pm (0.05\% R + 0.01 \Omega)$
4.17	20 (Ta)	Solderability	+235 °C; 2 s solder bath method; SnPb40  +245 °C; 3 s solder bath method; SnAg3Cu0.5	Good tinning ( $\geq 95\%$ covered, no visible damage)		
4.18.2	20 (Tb)	Resistance to soldering heat	Unmounted components; (270 $\pm$ 3) °C; (10 $\pm$ 1) s	$\pm (0.01\% R + 0.01 \Omega)$ no visible damage	$\pm (0.02\% R + 0.01 \Omega)$ no visible damage	$\pm (0.05\% R + 0.01 \Omega)$ no visible damage
4.19	14 (Na)	Rapid change of temperature	30 min at LCT = -55 °C 30 min at UCT = 125 °C  5 cycles  MBA/SMA 0204: 500 cycles MBB/SMA 0207: 200 cycles MBE/SMA 0414: 100 cycles	$\pm (0.01\% R + 0.01 \Omega)$ no visible damage  $\pm (0.25\% R + 0.05 \Omega)$ no visible damage	$\pm (0.02\% R + 0.01 \Omega)$ no visible damage  $\pm (0.25\% R + 0.05 \Omega)$ no visible damage	$\pm (0.05\% R + 0.01 \Omega)$ no visible damage  $\pm (0.25\% R + 0.05 \Omega)$ no visible damage
4.22	6	Vibration	10 sweep cycles per direction; 10 Hz to 2000 Hz 1.5 mm or 200 m/s <sup>2</sup>	$\pm (0.01\% R + 0.01 \Omega)$	$\pm (0.02\% R + 0.01 \Omega)$	$\pm (0.05\% R + 0.01 \Omega)$



TEST PROCEDURES AND REQUIREMENTS						
IEC 60115-1 CLAUSE	IEC 60068-2 TEST METHOD	TEST	PROCEDURE	REQUIREMENTS PERMISSIBLE CHANGE ( $\Delta R$ max.)		
			Stability for product types:	STABILITY CLASS 0.05	STABILITY CLASS 0.1	STABILITY CLASS 0.25
			<b>MBA/SMA 0204</b>	100 $\Omega$ to 100 k $\Omega$	43 $\Omega$ to 221 k $\Omega$	22 $\Omega$ to 332 k $\Omega$
			<b>MBB/SMA 0207</b>	100 $\Omega$ to 270 k $\Omega$	43 $\Omega$ to 510 k $\Omega$	22 $\Omega$ to 1 M $\Omega$
			<b>MBE/SMA 0414</b>	100 $\Omega$ to 470 k $\Omega$	43 $\Omega$ to 1 M $\Omega$	22 $\Omega$ to 1.5 M $\Omega$
4.23		Climatic sequence:				
4.23.2	2 (Ba)	Dry heat	125 °C; 16 h			
4.23.3	30 (Db)	Damp heat, cyclic	55 °C; 24 h; 90 % to 100 % RH; 1 cycle	$\pm (0.05 \% R + 0.01 \Omega)$ no visible damage	$\pm (0.1 \% R + 0.01 \Omega)$ no visible damage	$\pm (0.25 \% R + 0.05 \Omega)$ no visible damage
4.23.4	1 (Aa)	Cold	-55 °C; 2 h			
4.23.5	13 (M)	Low air pressure	8.5 kPa; 2 h; 15 °C to 35 °C			
4.23.6	30 (Db)	Damp heat, cyclic	55 °C; 5 days; 95 % to 100 % RH; 5 cycles			
4.23.7		DC load	Apply rated power for 1 min			
4.24	78 (Cab)	Damp heat, steady state	(40 $\pm$ 2) °C; 56 days; (93 $\pm$ 3) % RH	$\pm (0.05 \% R + 0.01 \Omega)$	$\pm (0.1 \% R + 0.01 \Omega)$	$\pm (0.25 \% R + 0.05 \Omega)$
4.25.1	-	Endurance at 70 °C: Precision operation mode	$U = \sqrt{P_{70}} \times R$ or $U = U_{max.}$ ; 1.5 h on; 0.5 h off 70 °C; 1000 h 70 °C; 8000 h	$\pm (0.05 \% R + 0.01 \Omega)$ <sup>(1)</sup> $\pm (0.1 \% R + 0.01 \Omega)$	$\pm (0.1 \% R + 0.01 \Omega)$ $\pm (0.2 \% R + 0.01 \Omega)$	$\pm (0.25 \% R + 0.05 \Omega)$ <sup>(2)</sup> $\pm (0.5 \% R + 0.05 \Omega)$
	-	Endurance at 70 °C: Standard operation mode	$U = \sqrt{P_{70}} \times R$ or $U = U_{max.}$ ; 1.5 h on; 0.5 h off 70 °C; 1000 h 70 °C; 8000 h	$\pm (0.25 \% R + 0.05 \Omega)$ <sup>(2)</sup> $\pm (0.5 \% R + 0.05 \Omega)$	- -	- -
4.25.3	-	Endurance at upper category temperature	85 °C; 1000 h 125 °C; 1000 h	- $\pm (0.05 \% R + 0.01 \Omega)$	- $\pm (0.1 \% R + 0.01 \Omega)$	- $\pm (0.25 \% R + 0.05 \Omega)$
4.29	45 (XA)	Component solvent resistance	Isopropyl alcohol +23 °C; toothbrush method	Marking legible; No visible damage		
4.40	-	Electrostatic discharge (human body model)	IEC 61340-3-1; 3 pos. + 3 neg. MBA/SMA 0204: 2 kV MBB/SMA 0207: 4 kV MBE/SMA 0414: 6 kV	$\pm (0.5 \% R + 0.05 \Omega)$		

Notes

(1)  $\pm (0.03 \% R + 0.01 \Omega)$  for MBB/SMA 0207

(2)  $\pm (0.15 \% R + 0.05 \Omega)$  for MBB/SMA 0207



**DIMENSIONS**




<b>DIMENSIONS</b> - Leaded resistor types, mass and relevant physical dimensions						
TYPE	D <sub>max.</sub> (mm)	L <sub>max.</sub> (mm)	d <sub>nom.</sub> (mm)	I <sub>min.</sub> (mm)	M <sub>min.</sub> (mm)	MASS (mg)
MBA/SMA 0204	1.6	3.6	0.5	29.0	5.0	125
MBB/SMA 0207 <sup>(1)</sup>	2.5	6.3	0.6	28.0	10.0 <sup>(1)</sup>	220
MBE/SMA 0414	4.0	11.9	0.8	31.0	15.0	700

**Note**

<sup>(1)</sup> For  $7.5 \leq M < 10.0$  mm, use version MBB/SMA 0207... L0 (welding joint not lacquered)


**MBB/SMA 0207 WITH RADIAL TAPING**

LEAD SPACING (UB = 2.5 mm), SIZE 0207



<b>DIMENSIONS</b> in millimeters		
Pitch of components	P	12.7 ± 1.0
Lead spacing	F	2.5 + 0.6 / - 0.1
Width of carrier tape	W	18.0 + 1.0 / - 0.5
Body to hole center	H	18.0 ± 2.0
Height for cutting (max.)	L	11
Height for bending	C	2.5 + 0 / - 0.5
Height for insertion (max.)	H1	32

LEAD SPACING (RB = 5.0 mm), SIZE 0207



<b>DIMENSIONS</b> in millimeters		
Pitch of components	P	12.7 ± 1.0
Lead spacing	F	5.0 + 0.6 / - 0.1
Width of carrier tape	W	18.0 + 1.0 / - 0.5
Body to hole center	H	18.0 ± 2.0
Lead crimp to hole center	H <sub>0</sub>	16.0 ± 0.5
Height for cutting (max.)	L	11
Height for bending	C	2.5 + 0 / - 0.5
Height for insertion (max.)	H <sub>1</sub>	32





**HISTORICAL 12NC INFORMATION**

- The resistors had a 12-digit numeric code starting with 2312
- The subsequent 4 digits indicated the resistor type, specification and packaging; see the 12NC table
- The remaining 4 digits indicated the resistance value:
  - The first 3 digits indicated the resistance value
  - The last digit indicated the resistance decade in accordance with resistance decade table shown below

**Resistance Decade**

RESISTANCE DECADE	LAST DIGIT
10 Ω to 99.9 Ω	9
100 Ω to 999 Ω	1
1 kΩ to 9.99 kΩ	2
10 kΩ to 99.9 kΩ	3
100 kΩ to 999 kΩ	4
1 MΩ to 9.99 MΩ	5

**Historical 12NC Example**

The 12NC code of a MBA 0204 resistor, value 47 kΩ and TCR 25 with ± 0.1 % tolerance, supplied on bandolier in a box of 5000 units was: 2312 906 74703.

<b>HISTORICAL 12NC - Resistor type and packaging</b>							
DESCRIPTION			2312 ... ..... (BANDOLIER)				
			AMMOPACK		REEL		
TYPE	TCR	TOL.	C1 1000 UNITS	CT 5000 UNITS	R1 1000 UNITS	R2 2500 UNITS	RP 5000 UNITS
MBA 0204	± 25 ppm/K	± 0.25 %	901 6....	906 6....	701 6....	-	806 6....
		± 0.1 %	901 7....	906 7....	701 7....	-	806 7....
	± 15 ppm/K	± 0.25 %	902 6....	907 6....	702 6....	-	807 6....
		± 0.1 %	902 7....	907 7....	702 7....	-	807 7....
MBB 0207	± 25 ppm/K	± 0.25 %	911 6....	916 6....	711 6....	-	816 6....
		± 0.1 %	911 7....	916 7....	711 7....	-	816 7....
	± 15 ppm/K	± 0.25 %	912 6....	917 6....	712 6....	-	817 6....
		± 0.1 %	912 7....	917 7....	712 7....	-	817 7....
MBE 0414	± 25 ppm/K	± 0.25 %	921 6....	-	-	826 6....	-
		± 0.1 %	921 7....	-	-	826 7....	-
	± 15 ppm/K	± 0.25 %	922 6....	-	-	827 6....	-
		± 0.1 %	922 7....	-	-	827 7....	-



## Disclaimer

ALL PRODUCT, PRODUCT SPECIFICATIONS AND DATA ARE SUBJECT TO CHANGE WITHOUT NOTICE TO IMPROVE RELIABILITY, FUNCTION OR DESIGN OR OTHERWISE.

Vishay Intertechnology, Inc., its affiliates, agents, and employees, and all persons acting on its or their behalf (collectively, "Vishay"), disclaim any and all liability for any errors, inaccuracies or incompleteness contained in any datasheet or in any other disclosure relating to any product.

Vishay makes no warranty, representation or guarantee regarding the suitability of the products for any particular purpose or the continuing production of any product. To the maximum extent permitted by applicable law, Vishay disclaims (i) any and all liability arising out of the application or use of any product, (ii) any and all liability, including without limitation special, consequential or incidental damages, and (iii) any and all implied warranties, including warranties of fitness for particular purpose, non-infringement and merchantability.

Statements regarding the suitability of products for certain types of applications are based on Vishay's knowledge of typical requirements that are often placed on Vishay products in generic applications. Such statements are not binding statements about the suitability of products for a particular application. It is the customer's responsibility to validate that a particular product with the properties described in the product specification is suitable for use in a particular application. Parameters provided in datasheets and / or specifications may vary in different applications and performance may vary over time. All operating parameters, including typical parameters, must be validated for each customer application by the customer's technical experts. Product specifications do not expand or otherwise modify Vishay's terms and conditions of purchase, including but not limited to the warranty expressed therein.

Hyperlinks included in this datasheet may direct users to third-party websites. These links are provided as a convenience and for informational purposes only. Inclusion of these hyperlinks does not constitute an endorsement or an approval by Vishay of any of the products, services or opinions of the corporation, organization or individual associated with the third-party website. Vishay disclaims any and all liability and bears no responsibility for the accuracy, legality or content of the third-party website or for that of subsequent links.

Except as expressly indicated in writing, Vishay products are not designed for use in medical, life-saving, or life-sustaining applications or for any other application in which the failure of the Vishay product could result in personal injury or death. Customers using or selling Vishay products not expressly indicated for use in such applications do so at their own risk. Please contact authorized Vishay personnel to obtain written terms and conditions regarding products designed for such applications.

No license, express or implied, by estoppel or otherwise, to any intellectual property rights is granted by this document or by any conduct of Vishay. Product names and markings noted herein may be trademarks of their respective owners.