

# VM1PNOQ

ultrasonic sensor flat form + M18 - Sn508mm - NO - 12..24VDC - M12



## Main

Range of product	Hyde Park
Sensor type	Ultrasonic sensor
Series name	Virtu VM1
Device short name	VM1
Sensor design	Flat form + cylindrical M18
[Sn] nominal sensing distance	508 mm
Type of sensing window	Adjustable
Material	Plastic
Enclosure material	Valox
Front material	Glass epoxy
Type of output signal	Discrete
Discrete output function	1 NO
Wiring technique	4-wire
[Us] rated supply voltage	12...24 V DC (overload and short-circuit protection)
Supply voltage limits	10...28 V DC
Discrete output type	PNP
Electrical connection	1 male connector M12 4 pins
Product specific application	-

## Complementary

[Sd] sensing range	50.8...508 mm
[Sa] assured operating distance	50.8...508 mm with remote teach pushbutton
Blind zone	0...51 mm
Transmission frequency	300 kHz
Repeat accuracy	1.27 %
Beam angle	5 °
Minimum size of detected object	Cylinder diameter 2.5 mm - up to 200 mm sensing distance
Status LED	1 LED - green - output not active
Current consumption	40 mA
Maximum switching current	100 mA (reverse polarity protection)
Resistance to electrostatic discharge	8 kV (level 4) conforming to IEC 61000-4-2
Height	43.7 mm
Width	18 mm
Depth	43.7 mm
Length	59.69 mm
Product weight	0.033 kg

## Environment

Standards	EN 60947
Product certifications	UL
Marking	CE
NEMA degree of protection	NEMA 4X (indoor use only)
IP degree of protection	IP67
Ambient air temperature for operation	-30...70 °C

Ambient air temperature for storage	-40...85 °C
Relative humidity	100 % without condensation
Vibration resistance	+/-1 mm conforming to IEC 60068-2-6 10...55 Hz
Shock resistance	30 gn in all 3 axes for 11 ms conforming to IEC 60068-2-27
Resistance to electromagnetic fields	10 V/m (level 3) conforming to IEC 61000-4-3
Resistance to fast transients	1 kV (level 3) conforming to IEC 61000-4-4

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Schneider Electric:](#)

[VM1PNOQ](#)