



# 40x40x20 mm

San Ace 40 9P<sub>type</sub>

## General Specifications

- Material ..... Frame: Plastic (Flammability: UL 94V-0), Impeller: Plastic (Flammability: UL 94V-1)
- Expected life ..... See the table below. (L10 life: 90% survival rate for continuous operation in free air at 60°C, rated voltage)  
Expected life at 40°C is for reference only.
- Motor protection function ..... Locked rotor burnout protection, Reverse polarity protection  
For details, please refer to p. 599.
- Dielectric strength ..... 50/60 Hz, 500 VAC, for 1 minute (between lead wire conductors and frame)
- Insulation resistance ..... 10 MΩ or more with a 500 VDC megger (between lead wire conductors and frame)
- Sound pressure level (SPL) ..... At 1 m away from the air inlet
- Storage temperature ..... -30 to +70°C (Non-condensing)
- Lead wire ..... ⊕Red ⊖Black or Blue  Sensor Yellow
- Mass ..... 45 g

## Specifications

The models listed below **have ribs and pulse sensors.**

Model no.	Rated voltage [V]	Operating voltage range [V]	Rated current [A]	Rated input [W]	Rated speed [min <sup>-1</sup> ]	Max. airflow [m <sup>3</sup> /min] [CFM]	Max. static pressure [Pa] [inchH <sub>2</sub> O]	SPL [dB (A)]	Operating temperature [°C]	Expected life [h]		
▶▶▶ 109P0405J601	5	4.5 to 5.5	0.46	2.3	9800	0.28 9.9	98.5 0.396	39	-20 to +70	40000/60°C (70000/40°C)		
▶▶▶ 109P0405H601			0.32	1.6	8000	0.225 8.0	65.7 0.264	33				
▶▶▶ 109P0405F601			0.25	1.25	6500	0.183 6.5	45.1 0.181	28				
▶▶▶ 109P0405M601			0.12	0.6	5000	0.136 4.8	26.5 0.106	24				
▶▶▶ 109P0412G601	12	7 to 13.8	0.28	3.36	12500	0.35 12.4	153.8 0.618	44	-20 to +60	40000/60°C (70000/40°C)		
▶▶▶ 109P0412D601			0.18	2.16	11000	0.31 10.9	124 0.498	42				
▶▶▶ 109P0412E601			0.13	1.56	9200	0.26 9.2	87.3 0.351	37				
▶▶▶ 109P0412H601			0.11	1.32	8000	0.225 8.0	65.7 0.264	33				
▶▶▶ 109P0412F601			0.09	1.08	6500	0.183 6.5	45.1 0.181	28				
▶▶▶ 109P0412M601			0.06	0.72	5000	0.136 4.8	26.5 0.106	24				
▶▶▶ 109P0424G601	24	12 to 27.6	0.15	3.6	12500	0.35 12.4	153.8 0.618	44	-20 to +60	40000/60°C (70000/40°C)		
▶▶▶ 109P0424D601			0.13	3.12	11000	0.31 10.9	124 0.498	42				
▶▶▶ 109P0424H601			0.07	1.68	8300	0.233 8.2	69.6 0.28	35				
▶▶▶ 109P0424F601		0.06	1.44	6500	0.183 6.5	45.1 0.181	28					
▶▶▶ 109P0424B601		14 to 27.6	0.06	1.44	6500	0.183 6.5	45.1 0.181	28			-20 to +70	60000/60°C (90000/40°C)
		20.4 to 27.6	0.06	1.44	5200	0.14 4.9	28.3 0.114	25				


Note 1: Sensor and control options are available for selection. Refer to the table on pp. 621 to 622.

Note 2: The ▶▶▶ mark indicates Short LeadTime Service applicable models. See p. 654 for details.

## Airflow - Static Pressure Characteristics


109P0405J601 With pulse sensor

Operating voltage range




109P0405H601 With pulse sensor

Operating voltage range



109P0405F601 With pulse sensor


Operating voltage range



# Airflow - Static Pressure Characteristics


**109P0405M601** With pulse sensor

Operating voltage range




**109P0412G601** With pulse sensor

Operating voltage range




**109P0412D601** With pulse sensor

Operating voltage range




**109P0412E601** With pulse sensor

Operating voltage range




**109P0412H601** With pulse sensor

Operating voltage range




**109P0412F601** With pulse sensor

Operating voltage range




**109P0412M601** With pulse sensor

Operating voltage range




**109P0424G601** With pulse sensor

Operating voltage range




**109P0424D601** With pulse sensor

Operating voltage range




**109P0424H601** With pulse sensor

Operating voltage range




**109P0424F601** With pulse sensor

Operating voltage range




**109P0424B601** With pulse sensor


Operating voltage range



**Dimensions (unit: mm)**



**Reference Dimensions of Mounting Holes and Vent Opening (unit: mm)**



**Options**

Finger guards

page: p. 584

Model no.: 109-059, 109-059H