

SAFETY DATA SHEET

according to Regulation (EC) No. 1907/2006



KIMBERLY-CLARK PROFESSIONAL* MELODIE Fragrance Refill

Version	Revision Date:	SDS Number:	Date of last issue: 11.05.2023
1.19	12.05.2023	100000019443	Date of first issue: 29.01.2019

SECTION 1: Identification of the substance/mixture and of the company/undertaking

1.1 Product identifier

Trade name : KIMBERLY-CLARK PROFESSIONAL* MELODIE Fragrance Refill

Product code : 6135

1.2 Relevant identified uses of the substance or mixture and uses advised against

Use of the Substance/Mixture : Air Freshener

Recommended restrictions on use : For professional users only.

1.3 Details of the supplier of the safety data sheet

Company name of supplier : Kimberly-Clark Europe Limited

Address : Walton Oaks, Dorking Road
Tadworth
Surrey KT20 7NS
United Kingdom

Telephone : +44 1737 736000

E-mail address of person responsible for the SDS : sdscontact@kcc.com

1.4 Emergency telephone number

Emergency telephone number : +44 1235 239670 (24/7 Service)

Poison Center Name : NHS 111

Poison Center Telephone : 111

SECTION 2: Hazards identification

2.1 Classification of the substance or mixture

Classification (REGULATION (EC) No 1272/2008)

Eye irritation, Category 2 H319: Causes serious eye irritation.

SAFETY DATA SHEET

according to Regulation (EC) No. 1907/2006



KIMBERLY-CLARK PROFESSIONAL* MELODIE Fragrance Refill

Version	Revision Date:	SDS Number:	Date of last issue: 11.05.2023
1.19	12.05.2023	100000019443	Date of first issue: 29.01.2019

2.2 Label elements

Labelling (REGULATION (EC) No 1272/2008)

Hazard pictograms :



Signal word : Warning

Hazard statements : H319 Causes serious eye irritation.

Precautionary statements : **Response:**
P305 + P351 + P338 IF IN EYES: Rinse cautiously with water for several minutes. Remove contact lenses, if present and easy to do. Continue rinsing.
P337 + P313 If eye irritation persists: Get medical advice/attention.

Additional Labelling

EUH208 Contains 4-tert-butylcyclohexyl acetate. May produce an allergic reaction.

2.3 Other hazards

This substance/mixture contains no components considered to be either persistent, bioaccumulative and toxic (PBT), or very persistent and very bioaccumulative (vPvB) at levels of 0.1% or higher.

Ecological information: The substance/mixture does not contain components considered to have endocrine disrupting properties according to REACH Article 57(f) or Commission Delegated regulation (EU) 2017/2100 or Commission Regulation (EU) 2018/605 at levels of 0.1% or higher.

Toxicological information: The substance/mixture does not contain components considered to have endocrine disrupting properties according to REACH Article 57(f) or Commission Delegated regulation (EU) 2017/2100 or Commission Regulation (EU) 2018/605 at levels of 0.1% or higher.

SECTION 3: Composition/information on ingredients

3.2 Mixtures

Components

Chemical name	CAS-No. EC-No. Index-No. Registration number	Classification	Concentration (% w/w)
Butanol, 3-methoxy-3-methyl-	56539-66-3 260-252-4	Eye Irrit. 2; H319	>= 1 - < 10
propan-2-ol	67-63-0 200-661-7 603-117-00-0	Flam. Liq. 2; H225 Eye Irrit. 2; H319 STOT SE 3; H336	>= 1 - < 10

SAFETY DATA SHEET

according to Regulation (EC) No. 1907/2006



KIMBERLY-CLARK PROFESSIONAL* MELODIE Fragrance Refill

Version	Revision Date:	SDS Number:	Date of last issue: 11.05.2023
1.19	12.05.2023	100000019443	Date of first issue: 29.01.2019

4-tert-butylcyclohexyl acetate	32210-23-4 250-954-9	Skin Sens. 1B; H317	>= 0.1 - < 1
--------------------------------	-------------------------	---------------------	--------------

For explanation of abbreviations see section 16.

SECTION 4: First aid measures

4.1 Description of first aid measures

General advice : No hazards which require special first aid measures.

Protection of first-aiders : Not applicable

If inhaled : Not required under normal use.

In case of skin contact : Wash off with soap and plenty of water.
If skin irritation persists, call a physician.

In case of eye contact : Immediately flush eye(s) with plenty of water.

If swallowed : Do NOT induce vomiting.

4.2 Most important symptoms and effects, both acute and delayed

Symptoms : No information available.

4.3 Indication of any immediate medical attention and special treatment needed

Treatment : No information available.

SECTION 5: Firefighting measures

5.1 Extinguishing media

Suitable extinguishing media : Alcohol-resistant foam

Unsuitable extinguishing media : Do NOT use water jet.

5.2 Special hazards arising from the substance or mixture

Specific hazards during firefighting : No special precautions required.

5.3 Advice for firefighters

Special protective equipment for firefighters : In the event of fire, wear self-contained breathing apparatus.

Further information : Use water spray to cool unopened containers.

SAFETY DATA SHEET

according to Regulation (EC) No. 1907/2006



KIMBERLY-CLARK PROFESSIONAL* MELODIE Fragrance Refill

Version 1.19 Revision Date: 12.05.2023 SDS Number: 100000019443 Date of last issue: 11.05.2023
Date of first issue: 29.01.2019

SECTION 6: Accidental release measures

6.1 Personal precautions, protective equipment and emergency procedures

Personal precautions : Ensure adequate ventilation.

6.2 Environmental precautions

Environmental precautions : Prevent product from entering drains.

6.3 Methods and material for containment and cleaning up

Methods for cleaning up : Wipe up with absorbent material (e.g. cloth, fleece).

6.4 Reference to other sections

For personal protection see section 8.

SECTION 7: Handling and storage

7.1 Precautions for safe handling

Advice on safe handling : No special handling advice required.

Advice on protection against fire and explosion : Keep product and empty container away from heat and sources of ignition.

Hygiene measures : General industrial hygiene practice.

7.2 Conditions for safe storage, including any incompatibilities

Requirements for storage areas and containers : Keep container tightly closed in a dry and well-ventilated place.

Advice on common storage : No special restrictions on storage with other products.

Further information on storage stability : No decomposition if stored and applied as directed.

7.3 Specific end use(s)

Specific use(s) : Air Freshener

SECTION 8: Exposure controls/personal protection

8.1 Control parameters

Occupational Exposure Limits

Components	CAS-No.	Value type (Form of exposure)	Control parameters	Basis
propan-2-ol	ISOPROPY L ALCOHOL	TWA	400 ppm 999 mg/m ³	GB EH40

SAFETY DATA SHEET

according to Regulation (EC) No. 1907/2006



KIMBERLY-CLARK PROFESSIONAL* MELODIE Fragrance Refill

Version	Revision Date:	SDS Number:	Date of last issue: 11.05.2023
1.19	12.05.2023	100000019443	Date of first issue: 29.01.2019

		STEL	500 ppm 1,250 mg/m ³	GB EH40
--	--	------	------------------------------------	---------

8.2 Exposure controls

Personal protective equipment

Eye protection : Not required under normal use.

Hand protection

Remarks : Not required under normal use

Skin and body protection : Not required under normal use

Respiratory protection : Not required under normal use.

Protective measures : No special protective equipment required.

SECTION 9: Physical and chemical properties

9.1 Information on basic physical and chemical properties

Physical state : liquid

Colour : No data available

Odour : characteristic

Melting point/freezing point : 0 °C

Boiling point/boiling range : 100 °C

Flammability : Not classified as a flammability hazard

Upper explosion limit / Upper flammability limit : No data available

Lower explosion limit / Lower flammability limit : No data available

Flash point : 46 °C

pH : No information available.

Solubility(ies)
Water solubility : completely soluble

Vapour pressure : No data available

Particle characteristics
Particle size : No data available

SAFETY DATA SHEET

according to Regulation (EC) No. 1907/2006



KIMBERLY-CLARK PROFESSIONAL* MELODIE Fragrance Refill

Version	Revision Date:	SDS Number:	Date of last issue: 11.05.2023
1.19	12.05.2023	100000019443	Date of first issue: 29.01.2019

9.2 Other information

Not applicable and/or not determined for the mixture

9.2.1 Information with Regard to Physical Hazard Classes

No data available/applicable

9.2.2 Other Safety Characteristics

No data available/applicable

SECTION 10: Stability and reactivity

10.1 Reactivity

No decomposition if stored and applied as directed.

10.2 Chemical stability

No decomposition if stored and applied as directed.

10.3 Possibility of hazardous reactions

Hazardous reactions : Stable under recommended storage conditions.
No hazards to be specially mentioned.

10.4 Conditions to avoid

Conditions to avoid : No data available

10.5 Incompatible materials

Materials to avoid : Strong acids and oxidizing agents

10.6 Hazardous decomposition products

Stable under recommended storage conditions.

SECTION 11: Toxicological information

11.1 Information on hazard classes as defined in Regulation (EC) No 1272/2008

Acute toxicity

Components:

propan-2-ol:

Acute oral toxicity : LD50 Oral (Rat): 5,840 mg/kg
Method: OECD Test Guideline 401
GLP: no
Remarks: See User Free Text

LD50 Oral (Rat): 1,870 mg/kg

Acute inhalation toxicity : LC50 (Rat, male and female): > 10000 ppm

SAFETY DATA SHEET

according to Regulation (EC) No. 1907/2006



KIMBERLY-CLARK PROFESSIONAL* MELODIE Fragrance Refill

Version	Revision Date:	SDS Number:	Date of last issue: 11.05.2023
1.19	12.05.2023	100000019443	Date of first issue: 29.01.2019

Exposure time: 6 h
Test atmosphere: vapour
Method: OECD Test Guideline 403
GLP: yes

LC50 (Rat): 72,600 mg/m³
Exposure time: 4 h

Acute dermal toxicity : LD50 Dermal (Rabbit): 12,800 mg/kg
Method: OECD Test Guideline 402
GLP: no
Remarks: See User Free Text

LD50 Dermal (Rabbit): 4,059 mg/kg

Skin corrosion/irritation

Product:

Remarks : According to the classification criteria of the European Union, the product is not considered as being a skin irritant.

Components:

propan-2-ol:

Species : Rabbit
Exposure time : 4 hrs
Method : No information available.
Result : No skin irritation
GLP : no
Remarks : See User Free Text

4-tert-butylcyclohexyl acetate:

Species : human skin
Result : No skin irritation

Serious eye damage/eye irritation

Product:

Assessment : Irritating to eyes.

Components:

Butanol, 3-methoxy-3-methyl-:

Assessment : Irritating to eyes.

propan-2-ol:

Species : Rabbit
Method : OECD Test Guideline 405
Result : Irritating to eyes.

SAFETY DATA SHEET

according to Regulation (EC) No. 1907/2006



KIMBERLY-CLARK PROFESSIONAL* MELODIE Fragrance Refill

Version	Revision Date:	SDS Number:	Date of last issue: 11.05.2023
1.19	12.05.2023	100000019443	Date of first issue: 29.01.2019

GLP : no

Respiratory or skin sensitisation

Product:

Assessment : Does not cause skin sensitisation.

Germ cell mutagenicity

Product:

Germ cell mutagenicity-
Assessment : Contains no ingredient listed as a mutagen

Carcinogenicity

Product:

Carcinogenicity -
Assessment : Contains no ingredient listed as a carcinogen

Reproductive toxicity

Product:

Reproductive toxicity -
Assessment : Contains no ingredient listed as toxic to reproduction

STOT - single exposure

Product:

Remarks : No data available

STOT - repeated exposure

Product:

Remarks : No data available

11.2 Information on other hazards

Endocrine disrupting properties

Product:

Assessment : The substance/mixture does not contain components considered to have endocrine disrupting properties according to REACH Article 57(f) or Commission Delegated regulation (EU) 2017/2100 or Commission Regulation (EU) 2018/605 at levels of 0.1% or higher.

Further information

Product:

SAFETY DATA SHEET

according to Regulation (EC) No. 1907/2006



KIMBERLY-CLARK PROFESSIONAL* MELODIE Fragrance Refill

Version	Revision Date:	SDS Number:	Date of last issue: 11.05.2023
1.19	12.05.2023	100000019443	Date of first issue: 29.01.2019

Remarks : No data available

SECTION 12: Ecological information

12.1 Toxicity

Product:

Toxicity to fish : Remarks: No information available.

Toxicity to daphnia and other aquatic invertebrates : Remarks: No information available.

Toxicity to algae/aquatic plants : Remarks: No information available.

Components:

Butanol, 3-methoxy-3-methyl-:

Toxicity to fish : LC50 (Oryzias latipes (Orange-red killifish)): > 100 mg/l
Exposure time: 96 h
Test Type: semi-static test

propan-2-ol:

Toxicity to fish : LC50 (Pimephales promelas (fathead minnow)): 9,640 mg/l
End point: mortality
Exposure time: 96 h
Test Type: flow-through test
Analytical monitoring: yes
Method: OECD Test Guideline 203
GLP: no

LC50 (Pimephales promelas (fathead minnow)): 10,000 mg/l
End point: mortality
Exposure time: 96 h
Test Type: flow-through test
Analytical monitoring: yes
Method: OECD Test Guideline 203
GLP: no

LC50 (Pimephales promelas (fathead minnow)): 9,640 mg/l
Exposure time: 96 h
Test Type: flow-through test

LC50 (Pimephales promelas (fathead minnow)): 11,130 mg/l
Exposure time: 96 h
Test Type: static test

LC50 (Lepomis macrochirus (Bluegill sunfish)): > 1,400,000 µg/l
Exposure time: 96 h

SAFETY DATA SHEET

according to Regulation (EC) No. 1907/2006



KIMBERLY-CLARK PROFESSIONAL* MELODIE Fragrance Refill

Version	Revision Date:	SDS Number:	Date of last issue: 11.05.2023
1.19	12.05.2023	100000019443	Date of first issue: 29.01.2019

Toxicity to daphnia and other aquatic invertebrates : EC50 (Daphnia magna (Water flea)): 9,714 mg/l
Exposure time: 24 h
Test Type: static test
Method: OECD Test Guideline 202
GLP: no

EC50 (Daphnia magna (Water flea)): 13,299 mg/l
Exposure time: 48 h

Toxicity to algae/aquatic plants : EC10 (Scenedesmus quadricauda (Green algae)): 1,800 mg/l
End point: See User Free Text
Exposure time: 168 h
Test Type: static test
Analytical monitoring: no
Method: See User Free Text
GLP: no

EC50 (Desmodesmus subspicatus (green algae)): > 1,000 mg/l
Exposure time: 96 h

EC50 (Desmodesmus subspicatus (green algae)): > 1,000 mg/l
Exposure time: 72 h

12.2 Persistence and degradability

Product:

Biodegradability : Remarks: No information available.

Components:

propan-2-ol:

Biodegradability : Test Type: aerobic
Inoculum: activated sludge, adapted
Biodegradation: 53 %
Related to: Chemical oxygen demand
Exposure time: 5 d
Remarks: Readily biodegradable, according to appropriate OECD test.

4-tert-butylcyclohexyl acetate:

Biodegradability : Result: Readily biodegradable.

12.3 Bioaccumulative potential

Product:

Bioaccumulation : Remarks: Does not bioaccumulate.

SAFETY DATA SHEET

according to Regulation (EC) No. 1907/2006



KIMBERLY-CLARK PROFESSIONAL* MELODIE Fragrance Refill

Version	Revision Date:	SDS Number:	Date of last issue: 11.05.2023
1.19	12.05.2023	100000019443	Date of first issue: 29.01.2019

Components:

propan-2-ol:

Bioaccumulation : Remarks: No bioaccumulation is to be expected (log Pow <= 4).

12.4 Mobility in soil

Product:

Mobility : Remarks: No information available.

Components:

propan-2-ol:

Stability in soil : Remarks: Adsorbs on soil.

12.5 Results of PBT and vPvB assessment

Product:

Assessment : This substance/mixture contains no components considered to be either persistent, bioaccumulative and toxic (PBT), or very persistent and very bioaccumulative (vPvB) at levels of 0.1% or higher..

Components:

propan-2-ol:

Assessment : This substance is not considered to be persistent, bioaccumulating and toxic (PBT).. This substance is not considered to be very persistent and very bioaccumulating (vPvB)..

12.6 Endocrine disrupting properties

Product:

Assessment : The substance/mixture does not contain components considered to have endocrine disrupting properties according to REACH Article 57(f) or Commission Delegated regulation (EU) 2017/2100 or Commission Regulation (EU) 2018/605 at levels of 0.1% or higher.

12.7 Other adverse effects

Product:

Additional ecological information : No data available

SAFETY DATA SHEET

according to Regulation (EC) No. 1907/2006



KIMBERLY-CLARK PROFESSIONAL* MELODIE Fragrance Refill

Version	Revision Date:	SDS Number:	Date of last issue: 11.05.2023
1.19	12.05.2023	100000019443	Date of first issue: 29.01.2019

SECTION 13: Disposal considerations

13.1 Waste treatment methods

- Product : Dispose of in accordance with local regulations.
- Contaminated packaging : Dispose of as unused product.
- Do not re-use empty containers.
- Empty containers should be taken to an approved waste handling site for recycling or disposal.

SECTION 14: Transport information

14.1 UN number or ID number

Not regulated as a dangerous good

14.2 UN proper shipping name

Not regulated as a dangerous good

14.3 Transport hazard class(es)

Not regulated as a dangerous good

14.4 Packing group

Not regulated as a dangerous good

14.5 Environmental hazards

Not regulated as a dangerous good

14.6 Special precautions for user

Not applicable

14.7 Maritime transport in bulk according to IMO instruments

Not applicable for product as supplied.

SECTION 15: Regulatory information

15.1 Safety, health and environmental regulations/legislation specific for the substance or mixture

REACH - Candidate List of Substances of Very High Concern for Authorisation (Article 59). : Not applicable

REACH - List of substances subject to authorisation (Annex XIV) : Not applicable

Regulation (EC) No 1005/2009 on substances that deplete the ozone layer : Not applicable

Regulation (EC) No 850/2004 on persistent organic pollutants : Not applicable

SAFETY DATA SHEET

according to Regulation (EC) No. 1907/2006



KIMBERLY-CLARK PROFESSIONAL* MELODIE Fragrance Refill

Version	Revision Date:	SDS Number:	Date of last issue: 11.05.2023
1.19	12.05.2023	100000019443	Date of first issue: 29.01.2019

15.2 Chemical safety assessment

No information available.

SECTION 16: Other information

Full text of H-Statements

H225	: Highly flammable liquid and vapour.
H317	: May cause an allergic skin reaction.
H319	: Causes serious eye irritation.
H336	: May cause drowsiness or dizziness.

Full text of other abbreviations

Eye Irrit.	: Eye irritation
Flam. Liq.	: Flammable liquids
Skin Sens.	: Skin sensitisation
STOT SE	: Specific target organ toxicity - single exposure
GB EH40	: UK. EH40 WEL - Workplace Exposure Limits
GB EH40 / TWA	: Long-term exposure limit (8-hour TWA reference period)
GB EH40 / STEL	: Short-term exposure limit (15-minute reference period)

ADN - European Agreement concerning the International Carriage of Dangerous Goods by Inland Waterways; ADR - European Agreement concerning the International Carriage of Dangerous Goods by Road; AICS - Australian Inventory of Chemical Substances; ASTM - American Society for the Testing of Materials; bw - Body weight; CLP - Classification Labelling Packaging Regulation; Regulation (EC) No 1272/2008; CMR - Carcinogen, Mutagen or Reproductive Toxicant; DIN - Standard of the German Institute for Standardisation; DSL - Domestic Substances List (Canada); ECHA - European Chemicals Agency; EC-Number - European Community number; ECx - Concentration associated with x% response; ELx - Loading rate associated with x% response; EmS - Emergency Schedule; ENCS - Existing and New Chemical Substances (Japan); ErCx - Concentration associated with x% growth rate response; GHS - Globally Harmonized System; GLP - Good Laboratory Practice; IARC - International Agency for Research on Cancer; IATA - International Air Transport Association; IBC - International Code for the Construction and Equipment of Ships carrying Dangerous Chemicals in Bulk; IC50 - Half maximal inhibitory concentration; ICAO - International Civil Aviation Organization; IECSC - Inventory of Existing Chemical Substances in China; IMDG - International Maritime Dangerous Goods; IMO - International Maritime Organization; ISHL - Industrial Safety and Health Law (Japan); ISO - International Organisation for Standardization; KECI - Korea Existing Chemicals Inventory; LC50 - Lethal Concentration to 50 % of a test population; LD50 - Lethal Dose to 50% of a test population (Median Lethal Dose); MARPOL - International Convention for the Prevention of Pollution from Ships; n.o.s. - Not Otherwise Specified; NO(A)EC - No Observed (Adverse) Effect Concentration; NO(A)EL - No Observed (Adverse) Effect Level; NOELR - No Observable Effect Loading Rate; NZIoC - New Zealand Inventory of Chemicals; OECD - Organization for Economic Co-operation and Development; OPPTS - Office of Chemical Safety and Pollution Prevention; PBT - Persistent, Bioaccumulative and Toxic substance; PICCS - Philippines Inventory of Chemicals and Chemical Substances; (Q)SAR - (Quantitative) Structure Activity Relationship; REACH - Regulation (EC) No 1907/2006 of the European Parliament and of the Council concerning the Registration, Evaluation, Authorisation and Restriction of Chemicals; RID - Regulations concerning the International Carriage of Dangerous Goods by Rail; SADT - Self-Accelerating Decomposition Temperature; SDS - Safety Data Sheet; SVHC - Substance of Very High Concern; TCSI - Taiwan Chemical Substance Inventory; TRGS - Technical Rule for

SAFETY DATA SHEET

according to Regulation (EC) No. 1907/2006



KIMBERLY-CLARK PROFESSIONAL* MELODIE Fragrance Refill

Version	Revision Date:	SDS Number:	Date of last issue: 11.05.2023
1.19	12.05.2023	100000019443	Date of first issue: 29.01.2019

Hazardous Substances; TSCA - Toxic Substances Control Act (United States); UN - United Nations; vPvB - Very Persistent and Very Bioaccumulative

Further information

Classification of the mixture:

Eye Irrit. 2

H319

Classification procedure:

Based on product data or assessment

The information provided in this Safety Data Sheet is correct to the best of our knowledge, information and belief at the date of its publication. The information given is designed only as a guidance for safe handling, use, processing, storage, transportation, disposal and release and is not to be considered a warranty or quality specification. The information relates only to the specific material designated and may not be valid for such material used in combination with any other materials or in any process, unless specified in the text.

GB / EN