


REV.	DESCRIPTION	DRAWN	CHECKED	APPROVED
A	NEW RELEASE	YCH 09/06/10'		



NOTES:

- SPECIFICATIONS:
 - CONTACT RESISTANCE: 30mΩ(max.) INITIAL FOR VBUS AND GND CONTACTS. 50mΩ(max.) INITIAL FOR ALL OTHER CONTACTS.
 - INSULATOR RESISTANCE: 100MΩ min. AT 100V DC.
 - CURRENT RATING: 1.8A FOR VBUS PIN AND ITS CORESPONDING GND PIN. 0.25A (MIN.) FOR ALL OTHER CONTACTS
 - VOLTAGE RATING: 30V AC/DC.
 - DIELECTRIC STRENGTH: AC 100V FOR 1 Minute.
 - OPERATING TEMPERATURE: -55°C ~ +85°C.

2. MATERIALS:

- HOUSING: THERMOPLASTIC (UL 94-0).
- CONTACT: COPPER ALLOY
- SHELL: COPPER ALLOY.

3. PRODUCT NUMBER CODE:

DS1108-01 - X X X

- Contact plating
 - 0: selective gold flash
 - C 3u" gold
 - 3: 30u" gold
- Shell plating
 - 6: tin
 - N: nickel
 - 8: full gold
- Color of housing
 - W: white
 - B: black
 - L: Blue

Tel:86-574-63508797
 Fax:86-574-63510317
 E-mail:sale@zher...com.cn
 Http://www.connfly.com

GENERAL TOLERANCE		ANGLE TOLERANCE		PROJECTION		TITLE	USB 3.0 B TYPE MALE SOLDER TYPE		
X.	±0.60	X.	±5°	UNITS	mm	SHEET SIZE	A4	SERIES	DS1108-01
.X	±0.38	.X	±3°						
.XX	±0.25	.XX	±2°						
DRAWING TYPE		CUSTOMER				晨翔电子有限公司			
SCALE		1:1	SHEET	1 OF 1		CONNFLY CONNFLY ELECTRONIC CO. LTD			
DRAWING NO.		C-DS1108-01-XXX							