| NOTE: | | 222F - 90 | | REVISIONS | |
|--|--------------------|--|------------------------------------|--|---|
| 1. UNLESS OTHERWISE SPECIFIED.TOLERANCES ARE ±0.004 [0.1 MM] | | DRAWING NO THIRD ANGLE PROJ. | | DESCRIPTION RELEASE TO MFG. | DATE ECO APPR 07-Sep-09 HR |
| 2. RETURN LOSS - 1GHz >18dB. 2GHz > 12dB. 3GHz > 8dB | | INIKU ANGLE PROJ. | B | UPDATED DIMENSIONS | |
| | Ø 0.032 [0.80] | 0.882±0.01 [22.40±0.30] 0.295 7.50] | В | | · · · · · · · · · · · · · · · · · · · |
| UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN INCHES AND TOLERANCES ARE: 2 PLACE DECIMAL 3 PLACE DECIMAL ANGLES ±.015 (0,381 mm) ±.005 (0,127 mm) ± 1° NOTICE - These drawings, specifications, or other data (1) are, and remain the property of Amphenol Corp. (2) must be returned upon request; and (3) are confidential and not to be disclosed to any person other than those to whom they are given by Amphenol Corp. The furnishing of these drawings, specifications, or other data by Amphenol Corp., or to any other person to anyone for any purpose is | MATERIAL REFERENCE | DRAWN GOPI M ENGINEER CLEMENT APPROVED | DATE 23-Jan-12 DATE 07-Sep-09 DATE | 7 CAP 6 HEX NUT 5 CONTACT P 4 BODY-REAR 3 CONTACT PIN 2 INSULATOR 1 BODY-FRONT S.NO. DESCRIPTION TITLE F MALE TO FEMALE R/A ADAPTER | ALUMINNUM 1 BRASS 1 NICKEL PHOSPHOR BRONZE 1 TIN ZINC 1 NICKEL BRASS 1 TIN DELRIN 1 BRASS 1 NICKEL MATERIAL QTY FINISH Amphenol Connex |
| not to be regarded by implication or otherwise in any manner licensing, granting rights or permitting such holder or any other person to manufacture, use or sell any product, process or design, patented or otherwise, that may in any way be related to or disclosed by said drawings, specifications, or other data. | TASK - 847 | CAD FILE | | DWG SIZE DRAWING N | SCALE: 5.5:1 SHEET OF |

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Amphenol:

222F-90 222122