

## End clamp - E/MBK - 1401637

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://download.phoenixcontact.com>)

End clamp, width: 6.2 mm, color: gray




### Why buy this product

- Can be screwed onto NS 15 DIN rails
- Can be mounted directly on the mounting plate as an MBK terminal block base
- Large-surface labeling



### Key commercial data

Packing unit	100 pc
GTIN	 4 017918 020484
Weight per Piece (excluding packing)	1.62 g
Custom tariff number	39269097
Country of origin	Poland

### Technical data

#### Dimensions

Height	11.4 mm
Length	22 mm
Width	6.1 mm

#### General

Material	PA
Coating	3.2 mm fixing hole
Color	gray

### Classifications

eCl@ss

eCl@ss 4.0	27141199
------------	----------

# End clamp - E/MBK - 1401637

## Classifications

### eCl@ss

eCl@ss 4.1	27141199
eCl@ss 5.0	27141135
eCl@ss 5.1	27141145
eCl@ss 6.0	27141135
eCl@ss 7.0	27141135
eCl@ss 8.0	27141135

### ETIM

ETIM 2.0	EC000761
ETIM 3.0	EC001041
ETIM 4.0	EC001041
ETIM 5.0	EC001041

### UNSPSC

UNSPSC 6.01	30212109
UNSPSC 7.0901	39121708
UNSPSC 11	39121708
UNSPSC 12.01	39121708
UNSPSC 13.2	39121708

## Accessories

### Accessories

#### Mounting rail

DIN rail, unperforated - NS 15 UNPERF 2000MM - 1401695



DIN rail, material: Steel, unperforated, height 5.5 mm, width 15 mm, length: 2 m

DIN rail perforated - NS 15 PERF 2000MM - 1401682



DIN rail, material: steel galvanized and passivated with a thick layer, perforated, height 5.5 mm, width 15 mm, length: 2000 mm

## End clamp - E/MBK - 1401637

### Accessories

DIN rail perforated - NS 15 AL PERF 2000MM - 1401763



DIN rail, material: Aluminum, perforated, height 5.5 mm, width 15 mm, length: 2 m

---

DIN rail perforated - NS 15 WH PERF 2000MM - 1204096



DIN rail, material: steel, perforated, height 5.5 mm, width 15 mm, length: 2 m

---

### Drawings

## End clamp - E/MBK - 1401637

Dimensioned drawing

