


## **SPECIFICATION**

Part No.	:	AA.108.301111
Product Name	:	Titan GPS/GALILEO Antenna AA.108
Features	:	Adhesive Mount Covert stylish design Wide band input voltage IP-67 Waterproof 3M RG-174 SMA(M) Connector Cable and connector customizable RoHS Compliant





## **1. Introduction**

Our AA.108 Titan adhesive mount external antenna is ideal for robust, covert installations where durability and small size is paramount. It is ideal for telematics and M2M applications for commercial vehicle installations for fleet management etc.

Titan antennas are also widely used for consumer GPS/GALILEO devices when extra sensitivity is required, e.g. navigation devices and speed trap detectors.

The AA.108 is first tier automotive approved IP67 antenna, the part AA.108.301F21 (with GT5 connector) is listed in the global automotive IMDS databases, it has gone through full PPAP design, reliability and quality audits, including audits at the production facility.



## 2. Specifications

Ceramic Patch							
Outline Dimension	25*25*4mm						
Ground Size	25*25*4mm						
Center Frequency	1575.42±3MHz						
Bandwidth	10MHz						
VSWR	1.92 Max						
Axial ratio	3dB Typ.						
Gain @ Zenith	2dBic Typ.						
Impedance	50Ω						
Polarization	RHCP						

LNA Specification									
Frequency	1575.42MHz								
Impedance	50Ω								
VSWR	1.92 Max.								
DC Power Input	1.8V 2.5V 2.7V 3.3V 5V 1								
Gain	21.8dB	28dB	29dB 31dB						
Noise Figure	1.4dB 1.38dB 1.3dB								
Power Consumption	4.5mA 6.6mA 7mA								
Band Attenuation	40dB @fo±50MHz								
Operating temp	-40°C ~ +85°C								
Storage Temp	-40°C ~ +90°C								

\*Formula = Patch Antenna Average Gain + LNA typical gain – RG174 cable loss @1.2dB per meter = Gain at connector


Gain at the Connector - Patch Gain 2dB + LNA Gain 30dB - Cable loss of 1.2dB per metre (@3m = 3.6dB) = 28.4dB approx.



# 3. Ceramic Antenna Radiation Pattern (with housing)




## **3.1. Ceramic Antenna S11 (with housing)**






### 3.2. XZ Plane & YZ Plane






#### 3.3. LNA gain




#### 3.4. LNA S22






## 4. Drawing (Unit: mm)



	Name	Material	Finish	QTY
1	GPS Antenna Housing Top	PC	Black	1
2	GPS Antenna Housing Bottom	PC	Black	1
3	Double Sided Adhesive	3M 4612	White	1
4	Heat Shrink Tube	PE	Black	1
	Mama	Spor	Finish	
	Name	Spec	FILISH	QIT
ww	Connector Type	SMA(M) ST	Gold	1
XX	Cable Length	3000±30mm	Black	1
YY	Cable Type	RG174	Black	1





Jacket Braid Shield


Conductor

## 5. RG-174 Cable Specification

# RG-174 Coaxial Cable

Cable conforming to 2002/95/CE (RoHS)

#### **Structure and Dimensions**



#### **Electrical & Physical Specification**

1	Temperature rating:	80°C
2	Voltage	30V
3	Capacitance nominal (1KHz):	30.8 pF/ft
4	Conductor Resistance at 20°C	MAX 26AWG: 148.94Ω/km
5	Impedance:	$50\pm5~\Omega$

RG-174 Cable Attenuation(dB/100mm)												
GHz	0.5	1	1.5	2	2.5	3	3.5	4	4.5	5	5.5	6
RG-174	67	110	127	153	168	183	207	229	252	272	291	311

Taoglas makes no warranties based on the accuracy or completeness of the contents of this document and reserves the right to make changes to specifications and product descriptions at any time without notice. Taoglas reserves all rights to this document and the information contained herein.

Reproduction, use or disclosure to third parties without express permission is strictly prohibited.

Copyright © Taoglas Ltd.