Vishay High Power Products

Schottky Rectifier, 2 x 3.5 A

FEATURES

- Popular D-PAK outline
- Center tap configuration
- Small foot print, surface mountable
- Low forward voltage drop
- High frequency operation
- Guard ring for enhanced ruggedness and long term reliability
- Compliant to RoHS directive 2002/95/EC
- AEC-Q101 qualified

DESCRIPTION


The 6CWQ03FNPbF surface mount, center tap, Schottky rectifier series has been designed for applications requiring low forward drop and small foot prints on PC board. Typical applications are in disk drives, switching power supplies, converters, freewheeling diodes, battery charging, and reverse battery protection.

MAJOR RATINGS AND CHARACTERISTICS					
SYMBOL	CHARACTERISTICS	VALUES	UNITS		
I _{F(AV)}	Rectangular waveform	7	A		
V _{RRM}		30	V		
I _{FSM}	$t_p = 5 \ \mu s \ sine$	535	A		
V _F	3 Apk, T _J = 125 °C (per leg)	0.35	V		
TJ	Range	- 40 to 150	°C		

VOLTAGE RATINGS					
PARAMETER	SYMBOL	6CWQ03FNPbF	UNITS		
Maximum DC reverse voltage	V _R	30	V		
Maximum working peak reverse voltage	V _{RWM}	30	v		

ABSOLUTE MAXIMUM RATINGS						
PARAMETER		SYMBOL	TEST CONDITIONS		VALUES	UNITS
Maximum average forward currentper legSee fig. 5per device		I _{F(AV)}	50 % duty cycle at T_C = 134 °C, rectangular waveform		3.5	А
					7	
Maximum peak one cycle non-repetitive surge current per leg See fig. 7		I _{FSM}	5 μs sine or 3 μs rect. pulse	Following any rated load condition and with rated	535	
			10 ms sine or 6 ms rect. pulse	V _{RRM} applied	90	
Non-repetitive avalanche energy per leg		E _{AS}	$T_J = 25 \text{ °C}, I_{AS} = 2 \text{ A}, L = 4 \text{ mH}$		8	mJ
Repetitive avalanche current per leg I _{AR}		I _{AR}	Current decaying linearly to zero in 1 μ s Frequency limited by T _J maximum V _A = 1.5 x V _B typical		1	А

For technical questions, contact: diodestech@vishay.com



PRODUCT SUMMARY

I_{F(AV)}

 V_R

Base

2 x 3.5 A

30 V





6CWQ03FNPbF

Vishay High Power Products

Schottky Rectifier, 2 x 3.5 A



ELECTRICAL SPECIFICATIONS					
PARAMETER	SYMBOL	TEST CO	VALUES	UNITS	
	V _{FM} ⁽¹⁾	3 A	T _ 25 °C	0.45	V
Maximum forward		6 A	T _J = 25 °C	0.52	
voltage drop per leg See fig. 1		3 A	T 405.00	0.35	
		6 A	– T _J = 125 °C	0.46	
Maximum reverse	I _{RM} ⁽¹⁾	$T_J = 25 \ ^{\circ}C$	$V_{\rm B} = \text{Rated } V_{\rm B}$	2	mA
leakage current per leg See fig. 2		T _J = 125 °C	$ v_{\rm R} = naleu v_{\rm R}$	50	
Threshold voltage	V _{F(TO)}	T _J = T _J maximum		0.22	V
Forward slope resistance	r _t			32.86	mΩ
Typical junction capacitance per leg	CT	$V_{R} = 5 V_{DC}$, (test signal rat	290	pF	
Typical series inductance per leg	L _S	Measured lead to lead 5 m	5.0	nH	
Maximum voltage rate of change	dV/dt	Rated V _R	10 000	V/µs	

Note

 $^{(1)}\,$ Pulse width < 300 $\mu s,$ duty cycle < 2 %

THERMAL - MECHANICAL SPECIFICATIONS					
PARAMETER		SYMBOL	TEST CONDITIONS	VALUES	UNITS
Maximum junction and storage temperature range		T_{J} ⁽¹⁾ , T_{Stg}		- 40 to 150	°C
Maximum thermal resistance, junction to case p	per leg	- R _{th-IC}	DC operation See fig. 4	4.7	°C/W
	per device			2.35	
Approximate weight				0.3	g
				0.01	oz.
Marking device			Case style D-PAK (similar to TO-252AA)	6CWC	03FN

Note

(1) $\frac{dP_{tot}}{dT_J} < \frac{1}{R_{thJA}}$ thermal runaway condition for a diode on its own heatsink






Fig. 4 - Maximum Thermal Impedance Z_{thJC} Characteristics (Per Leg)


6CWQ03FNPbF


Vishay High Power Products

Schottky Rectifier, 2 x 3.5 A












Fig. 7 - Maximum Non-Repetitive Surge Current (Per Leg)


Note

- ⁽¹⁾ Formula used: $T_C = T_J (Pd + Pd_{REV}) \times R_{thJC};$ $Pd = Forward power loss = I_{F(AV)} \times V_{FM} at (I_{F(AV)}/D)$ (see fig. 6); $Pd_{REV} = Inverse power loss = V_{R1} \times I_R (1 D); I_R at V_{R1} = 80 \% rated V_R$



Vishay High Power Products

ORDERING INFORMATION TABLE



LINKS TO RELATED DOCUMENTS				
Dimensions	www.vishay.com/doc?95016			
Part marking information	www.vishay.com/doc?95059			
Packaging information	www.vishay.com/doc?95033			



Vishay

Disclaimer

All product specifications and data are subject to change without notice.

Vishay Intertechnology, Inc., its affiliates, agents, and employees, and all persons acting on its or their behalf (collectively, "Vishay"), disclaim any and all liability for any errors, inaccuracies or incompleteness contained herein or in any other disclosure relating to any product.

Vishay disclaims any and all liability arising out of the use or application of any product described herein or of any information provided herein to the maximum extent permitted by law. The product specifications do not expand or otherwise modify Vishay's terms and conditions of purchase, including but not limited to the warranty expressed therein, which apply to these products.

No license, express or implied, by estoppel or otherwise, to any intellectual property rights is granted by this document or by any conduct of Vishay.

The products shown herein are not designed for use in medical, life-saving, or life-sustaining applications unless otherwise expressly indicated. Customers using or selling Vishay products not expressly indicated for use in such applications do so entirely at their own risk and agree to fully indemnify Vishay for any damages arising or resulting from such use or sale. Please contact authorized Vishay personnel to obtain written terms and conditions regarding products designed for such applications.

Product names and markings noted herein may be trademarks of their respective owners.