


### Features

- 200 W peak pulse power ( $t_p=8/20\mu s$ )
- Bidirectional configurations
- Solid-state silicon-avalanche technology
- Low clamping voltage
- Low leakage current
- IEC 61000-4-2  $\pm 30kV$  contact  $\pm 30kV$  air
- IEC 61000-4-4 (EFT) 40A(5/50ns)
- IEC 61000-4-5 (Lightning) 3A(8/20 $\mu s$ )



### Applications

- Dataline
- Automatic Teller Machines
- Net works
- Power line

### Mechanical Data

- SOT-23 package
- Molding compound flammability rating: UL 94V-0
- Packaging: Tape and Reel
- RoHS/WEEE Compliant

### Absolute Maximum Rating


| Rating   | Symbol    | Value        | Units |
|--|-----------|--------------|-------|
| Peak Pulse Power ( $t_p=8/20\mu s$ )                           | $P_{pp}$  | 200          | W     |
| Peak Pulse Current ( $t_p=8/20\mu s$ ) (note1)                 | $I_{pp}$  | 3            | A     |
| ESD per IEC 61000-4-2 (Air)<br>ESD per IEC 61000-4-2 (Contact) | $V_{ESD}$ | 30<br>30     | kV    |
| Lead Soldering Temperature                                     | $T_L$     | 260          | °C    |
| Junction Temperature   | $T_J$     | -55 to + 125 | °C    |
| Storage Temperature  | $T_{stg}$ | -55 to + 125 | °C    |

### Electrical Characteristics

| Parameter                 | Symbol    | Conditions                   | Min  | Typical | Max  | Units   |
|---------------------------|-----------|------------------------------|------|---------|------|---------|
| Reverse Stand-Off Voltage | $V_{RWM}$ |                              |      |         | 24.0 | V       |
| Reverse Breakdown Voltage | $V_{BR}$  | $I_T=1mA$                    | 25.5 | 27.6    | 30.3 | V       |
| Reverse Leakage Current   | $I_R$     | $V_{RWM}=24V, T=25^{\circ}C$ |      | 0.1     | 0.5  | $\mu A$ |
| Peak Pulse Current        | $I_{PP}$  | $t_p=8/20\mu s$              |      |         | 3    | A       |
| Clamping Voltage          | $V_C$     | $I_{PP}=3A, t_p=8/20\mu s$   |      |         | 70   | V       |
| Junction Capacitance      | $C_j$     | $V_R=0V, f=1MHz$             |      | 12      | 15   | pF      |

### Electrical Parameters (TA = 25°C unless otherwise noted)

| Symbol    | Parameter                                   |
|-----------|---|
| $I_{PP}$  | Maximum Reverse Peak Pulse Current          |
| $V_C$     | Clamping Voltage @ $I_{PP}$                 |
| $V_{RWM}$ | Working Peak Reverse Voltage                |
| $I_R$     | Maximum Reverse Leakage Current @ $V_{RWM}$ |
| $V_{BR}$  | Breakdown Voltage @ $I_T$                   |
| $I_T$     | Test Current                                |
|           |   |
|           |   |



Note: 8/20 $\mu s$  pulse waveform.

## Typical Characteristics

Figure 1: Peak Pulse Power vs. Pulse Time




Figure 2: Power Derating Curve




Figure 3: Pulse Waveform






Figure 4: Clamping Voltage vs.  $I_{pp}$



### Outline Drawing – SOT-23



| DIMENSIONS |            |       |           |       |
|------------|------------|-------|-----------|-------|
| SYMBOL     | MILLIMETER |       | INCHES    |       |
|            | MIN        | MAX   | MIN       | MAX   |
| A          | 0.900      | 1.150 | 0.035     | 0.045 |
| A1         | 0.000      | 0.100 | 0.000     | 0.004 |
| A2         | 0.900      | 1.050 | 0.035     | 0.041 |
| D          | 2.800      | 3.000 | 0.110     | 0.118 |
| b          | 0.300      | 0.500 | 0.012     | 0.020 |
| E          | 2.250      | 2.550 | 0.089     | 0.100 |
| E1         | 1.200      | 1.400 | 0.047     | 0.055 |
| e          | 0.950 BSC  |       | 0.037 BSC |       |
| L          | 0.300      | 0.500 | 0.012     | 0.020 |
| θ          | 0          | 8°    | 0         | 8°    |

### Marking



### Ordering information

| Order code   | Package | Base qty | Delivery mode |
|--------------|---------|----------|---------------|
| UMW PESD1CAN | SOT-23  | 3000     | Tape and reel |