

Power strips used within a patient care vicinity may be permanently attached so that it can only be removed with a tool. Choose the PSCLAMP for a safe and secure mounting solution.

Safe-IT UL 60601-1 Medical-Grade Power Strip for Patient-Care Vicinity, 4 15A Hospital-Grade Outlets, Safety Covers, 15 ft. Cord

MODEL NUMBER: PS-415-HGULTRA



Full 60601-1 compliance, integrated locking safety covers and a 15 ft. cord make this medical-grade power strip ideal for all areas inside and outside of patient care vicinities.

Description

The PS-415-HGULTRA Medical-Grade Power Strip -- patent # 7,375,939 -- is the first power strip with full 60601-1 compliance and agency listing, making it ideal for standalone use in all patient care vicinities. This 120V, 50/60 Hz power strip features a NEMA 5-15P-HG hospital-grade plug and four NEMA 5-15R-HG hospital-grade outlets that include integrated locking safety covers.

A patented protection circuit guards against shock hazards by preventing power from reaching the unit's outlets in the presence of a fault. The protection circuit automatically resets itself and restores power once the fault threat is gone.

The power strip is protected by a patented antimicrobial powder coating with EPA-registered and FDA-compliant silver ionic technology. The antimicrobial surface protection is 99.9 percent effective in inhibiting the growth of bacteria and reducing the risk of HAIs in hospitals and other medical environments. The coating meets the requirements of JIS Z 2801:2000, an international standard for evaluating efficacy in antimicrobial products.

Mounting tabs and flanges let you install the PS-415-HGULTRA on a wide variety of surfaces. The all-metal housing ensures safety and is guaranteed to last a long time in demanding environments.

With a switchless design that prevents accidental shutoff and a 15-foot (4.57 m) power cord that can reach a distant power source, the PS-415-HGULTRA is a recommended replacement for all non-compliant power strips.

Features

Power Distribution Anywhere in Any Medical Facility Ideal for standalone use in patient-care vicinities, therapy rooms, imaging environments and administrative areas
Patented protection circuit guards against shock hazards with automatic site fault protection
Circuit breaker resets itself once fault threat is gone
120V, 50/60 Hz power strip complies with UL 60601-1 and UL 60950-1 specifications
Patent # 7,375,939

Highlights

- Patented antimicrobial coating is 99.9% effective in inhibiting the growth of bacteria
- Approved for standalone use in all patient-care vicinities
- Complies with UL 60601-1 and UL 60950-1 specifications
- Patented protection circuit guards against shock hazards
- 4 NEMA 5-15R-HG hospital-grade outlets with locking safety covers

Package Includes

- PS-415-HGULTRA UL 60601-1 Medical-Grade Power Strip
- Owner's manual with maintenance requirements



Exclusive, Patented Antimicrobial Protection Silver ionic powder coating is 99.9% effective in inhibiting the growth of bacteria. Patented coating helps to reduce the risk of healthcare-acquired infections (HAIs) in hospitals and other medical environments. Coating meets the requirements of JIS Z 2801:2000, an international standard for evaluating efficacy in antimicrobial products.

Versatile Medical-Grade Solution 4 NEMA 5-15R-HG hospital-grade outlets provide consistent power. 15-ft. (4.57 m) power cord provides ample reach to the power source. Rugged all-metal housing for long life in demanding environments.

Premium Safety Features Integrated locking outlet safety covers block access to unused outlets. Built-in 15A circuit breaker protects against dangerous overloads. Switchless design prevents accidental shut-off.

Ready to Use Right Out of the Box Built-in mounting tabs and flanges for easy installation on a variety of surfaces.

Specifications

OVERVIEW	
UPC Code	037332128430
INPUT	
Nominal Input Voltage(s) Supported	120V AC
Recommended Electrical Service	15A 120V
Input Plug Features	Hospital Grade Plug
Voltage Compatibility (VAC)	120
Input Plug Type	NEMA 5-15P-HG
Input Cord Length (ft.)	15
Input Cord Length (m)	4.57
Integrated Cord Clip	No
OUTPUT	
Frequency Compatibility	50 / 60 Hz
Output (Watts)	1800
Output Receptacles	(4) 5-15R-HG
Circuit Breaker (amps)	15
Overload Protection	15A resettable circuit breaker
Transformer Accommodation	(2) Yes
Outlet Orientation	Single row of 4
Right-Angle Outlets	No
USER INTERFACE, ALERTS & CONTROLS	
Switches	No power switch



SURGE / NOISE SUPPRESSION	
Automatic Shut-Off	Yes
PHYSICAL	
Color	White
Material of Construction	Metal
Antimicrobial	Yes
Power Cord Color	White
Housing Color	White
Included Mounting Accessories	Mounting tabs and flanges
Mounting Holes or Slots	Yes
Slot or Hole Mount Measurement (Center to Center)	Distance between keyhole tabs = 261.92mm; Distance between end tabs = 334.01mm
Outlets Measurement (Center to Center)	92mm
Receptacle Color	White
Shipping Dimensions (hwd / cm)	35.99 x 15.19 x 5.51
Shipping Dimensions (hwd / in.)	14.17 x 5.98 x 2.17
Shipping Weight (kg)	1.63
Shipping Weight (lbs.)	3.60
Unit Dimensions (hwd / cm)	3.8 x 34.9 x 6.4
Unit Dimensions (hwd / in.)	1.5 x 13.75 x 2.5
Unit Weight (kg)	1.45
Unit Weight (lbs.)	3.20
Mounting Details	Includes flanges
FEATURES & SPECIFICATIONS	
Built-in Cable Management	No
Antibacterial	No
STANDARDS & COMPLIANCE	
Approvals	TUV tested to UL 60601-1 and UL 60950-1 (USA); TUV tested to CAN/CSA-C22.2 No. 601.1-M90 and 60950-1-03 (Canada)
Patented	Patent # 7,375,939
WARRANTY	
Product Warranty Period (Worldwide)	Lifetime limited warranty



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

© 2021 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies:
<https://www.tripplite.com/products/product-certification-agencies>