

# Load Cell - AL6N Series



- Aluminium-Alloy IP65 single point load cell
- Colourless anodized
- Suitable for single or double load cell structured platform scales
- Maximum platform size: 350 x 400 mm

| Capacity | Accuracy | Part-Number       |
|----------|----------|-------------------|
| 3 kg     | C3       | AL6N-C3-3kg-3B6   |
| 5 kg     | C3       | AL6N-C3-5kg-3B6   |
| 8 kg     | C3       | AL6N-C3-8kg-3B6   |
| 10 kg    | C3       | AL6N-C3-10kg-3B6  |
| 15 kg    | C3/C4    | AL6N-Cx-15kg-3B6  |
| 20 kg    | C3/C4    | AL6N-Cx-20kg-3B6  |
| 30 kg    | C3/C4    | AL6N-Cx-30kg-3B6  |
| 50 kg    | C3/C4    | AL6N-Cx-50kg-3B6  |
| 75 kg    | C3/C4    | AL6N-Cx-75kg-3B6  |
| 100 kg   | C3       | AL6N-C3-100kg-3B6 |




OIML test certificate no. D09-06.11 Revision 1  
 OIML C of C no. R60/2000-CNI-06.04  
 NTEP certificate no. 11-055




## Specification

| Accuracy class  |              | OIML R60 C3                          | OIML R60 C4        |
|---|--------------|--------------------------------------|--------------------|
| Output sensitivity (= FS)   | mV/V         | 2.0 ± 0.002                          |                    |
| Maximum capacity ( $E_{max}$ )                                    | kg           | 3, 5, 8, 10, 15, 20, 30, 50, 75, 100 | 15, 20, 30, 50, 75 |
| Maximum number of load cell intervals ( $n_{LC}$ )                |              | 3000                                 | 4000               |
| Ratio of minimum LC verification interval $Y = E_{max} / v_{min}$ |              | 12000                                | 20000              |
| Minimum Dead Load Output Return ( $Z = 1/2 * E_{max} / DR$ )      |              | 4000                                 |                    |
| Combined Error  | %FS          | ≤ ± 0.0230                           | ≤ ± 0.0175         |
| Minimum dead load   | kg           | 0                                    |                    |
| Safe overload   | of $E_{max}$ | 150%                                 |                    |
| Ultimate overload   | of $E_{max}$ | 300 %                                |                    |
| Zero balance  | of FS        | ≤ ± 2.0 %                            |                    |
| Excitation, recommended voltage                                   | V            | 5 ~ 12                               |                    |
| Excitation maximum  | V            | 18                                   |                    |
| Terminal resistance, input  | Ω            | 409 ± 6                              |                    |
| Terminal resistance, output                                       | Ω            | 350 ± 3                              |                    |
| Insulation impedance  | MΩ           | ≥ 5000 ( at 50VDC )                  |                    |
| Temperature range, compensated                                    | °C           | -10 ~ +40                            |                    |
| Temperature range, operating                                      | °C           | -35 ~ +65                            |                    |
| Element material  |              | Aluminium                            |                    |
| Recommended torque on fixation bolts                              | Nm           | 10                                   |                    |
| Ingress Protection (according to EN 60529)                        |              | IP65                                 |                    |

## Outline dimensions in mm



## Wiring



- Adopt a shielded, 6 conductor cable and cable jacket is PVC
- Cable length: 3.0 +/- 0.05 mm
- Cable diameter: 5.0 +/- 0.02 mm
- Shield is not connected to body