

# 2SD300C17A1 and 2SD300C17A1C Preliminary Datasheet

Dual-Channel High-quality and SCALE™-2 Driver Core

## Abstract

The SCALE™-2 dual-driver core 2SD300C17A1 / 2SD300C17A1C (Coated version using ELPEGUARD SL 1307 FLZ/2 from Lackwerke Peters) is designed for applications in which high reliability is expected.

The use of Power Integrations' highly integrated SCALE-2 chipset allows 63% of the components to be dispensed with compared to conventional drivers. This advantage is impressively reflected in increased reliability (function and MTBF).

The 2SD300C17A1(C) combines a complete two-channel driver core with all components required for driving, such as an isolated DC/DC converter, short-circuit protection, failure soft shut down, short pulse suppression as well as supply voltage monitoring. Each of the two output channels is electrically isolated from the primary side and the other secondary channel.

The driver provides a gate voltage swing of  $\pm 15V$ . An output current of 30A and 4W drive power is available per channel.

Its outstanding EMC with a  $dv/dt$  strength of more than 50V/ns allows safe and reliable operation in even the demanding industrial applications

## Product Highlights

- ✓ Dual channel driver
- ✓ Highly integrated SCALE-2 chipset
- ✓ Switching frequency up to 60kHz
- ✓ Gate current  $\pm 30A$
- ✓ 4W output power per channel
- ✓ Direct and half-bridge mode
- ✓ IGBT short-circuit protection
- ✓ Failure soft shut down
- ✓ Isolated DC/DC converter
- ✓ Safe isolation to EN 50178
- ✓ UL compliant
- ✓ Reliable, long service life

## Applications

- ✓ IGBTs up to 1700V

## Preliminary Data Sheet

### Safety Notice!

The data contained in this data sheet is intended exclusively for technically trained staff. Handling all high-voltage equipment involves risk to life. Strict compliance with the respective safety regulations is mandatory!

Any handling of electronic devices is subject to the general specifications for protecting electrostatic-sensitive devices according to international standard IEC 60747-1, Chapter IX or European standard EN 100015 (i.e. the workplace, tools, etc. must comply with these standards). Otherwise, this product may be damaged.

### Important Product Documentation

This data sheet contains only product-specific data. For a detailed description, must-read application notes and important information that apply to this product, please refer to "2SD300C17 Description & Application Manual" on [www.power.com/igbt-driver/go/2SD300C17](http://www.power.com/igbt-driver/go/2SD300C17).

### Absolute Maximum Ratings

Parameter	Remarks	Min	Max	Unit
Supply voltage $V_{DC}$	VDC to GND	0	16	V
Supply voltage $V_{DD}$	VDD to GND	0	16	V
Logic input voltages	INA, INB and Mod to GND	-0.5	20	V
Logic output voltages	SOA and SOB to GND	-0.5	VDD+0.5	V
SOx current	Failure condition, total current		20	mA
Gate peak current $I_{out}$	Note 1	-30	+30	A
Gate resistance	Turn-on and turn-off	1		$\Omega$
IGBT gate charge			50	$\mu$ C
Average supply current $I_{DC}$	Notes 2, 3		540	mA
Output power	Ambient temperature $\leq 70^{\circ}\text{C}$ (Notes 4, 5)		4	W
	Ambient temperature $\leq 85^{\circ}\text{C}$ (Note 4)		3	W
Switching frequency $f$			60	kHz
Test voltage (50Hz/1min.)	Primary to secondary (Note 11)		5000	$V_{AC(eff)}$
	Secondary to secondary (Note 11)		4000	$V_{AC(eff)}$
$ dV/dt $	Rate of change of input to output voltage		50	kV/ $\mu$ s
Operating voltage	Primary and secondary to secondary side		1700	$V_{peak}$
Operating temperature	Note 5	-40	85	$^{\circ}\text{C}$
Storage temperature	Note 14	-40	50	$^{\circ}\text{C}$
Surface temperature	Only for 2SD300C17A1C (Note 15)		125	$^{\circ}\text{C}$

## Preliminary Data Sheet

### Recommended Operating Conditions

Power Supply	Remarks	Min	Typ	Max	Unit
Supply voltage $V_{DC}$	VDC to GND	14	15	16	V
Supply voltage $V_{DD}$	VDD to GND	14	15	16	V
Input logic level	INx and Mod to GND, high level		VDD		V
Input logic level	INx and Mod to GND, low level		0		V

### Electrical Characteristics

All data refer to +25°C and  $V_{DC} = V_{DD} = 15V$  unless otherwise specified.

Power supply	Remarks	Min	Typ	Max	Unit
Supply current $I_{DC}$	Without load		65		mA
Supply current $I_{DD}$	Direct mode, $f = 0Hz$		14		mA
Supply current $I_{DD}$	Direct mode, $f = 60kHz$		21		mA
Coupling capacitance $C_{i0}$	Primary to secondary, per channel		22		pF
	Secondary to secondary		15		pF

Power Supply Monitoring	Remarks	Min	Typ	Max	Unit
Supply threshold $V_{DD}$	Primary side, clear fault	11.9	12.6	13.3	V
	Primary side, set fault (Note 6)	11.3	12.0	12.7	V
Monitoring hysteresis	Primary side, set/clear fault	0.35			V
Supply threshold $V_{x+}-V_{COMx}$	Secondary side, clear fault	12.1	12.6	13.1	V
	Secondary side, set fault (Note 7)	11.5	12.0	12.5	V
Monitoring hysteresis	Secondary side, set/clear fault	0.35			V
Supply threshold $V_{COMx}-V_{x-}$	Secondary side, clear fault	5	5.15	5.3	V
	Secondary side, set fault (Note 7)	4.7	4.85	5	V
Monitoring hysteresis	Secondary side, set/clear fault	0.15			V

Logic Inputs and Outputs	Remarks	Min	Typ	Max	Unit
Input impedance	INx and Mod		3.9		k $\Omega$
Turn-on threshold	V(INx)		8.1		V
Turn-off threshold	V(INx)		4.8		V
SOx output voltage	Failure condition, $I(SOx) < 20mA$			0.7	V

Short-Circuit Protection	Remarks	Min	Typ	Max	Unit
Rth value	Between RCx and COM x	2		70	k $\Omega$
Blocking time	Note 10		27		ms

## Preliminary Data Sheet

External Fault input	Remarks	Min	Typ	Max	Unit
Threshold level	Between E.x and COM x		5		V
Timing Characteristics	Remarks	Min	Typ	Max	Unit
Turn-on delay $t_{d(on)}$	Direct mode (Note 8)		630		ns
Turn-off delay $t_{d(off)}$	Direct mode (Note 8)		490		ns
Short pulse suppression	Turn-on command pulse width		470		ns
	Turn-off command pulse width		300		ns
Dead time between channels	Half-bridge mode, with CA = CB = 0pF (Note 13)		1.3		$\mu$ s
Transmission delay of fault state	Note 9		450		ns
Output Voltage	Remarks	Min	Typ	Max	Unit
Turn-on voltage	Gate x to COM x		15		V
Turn-off voltage	Gate x to COM x		-15		V
Electrical Isolation	Remarks	Min	Typ	Max	Unit
Test voltage (50Hz/1s)	Primary to secondary side (Note 11)	5000	5050	5100	$V_{eff}$
	Secondary to secondary side (Note 11)	4000	4050	4100	$V_{eff}$
Partial discharge extinction volt.	Primary to secondary side (Note 12)	1768			$V_{peak}$
	Secondary to secondary side (Note 12)	1700			$V_{peak}$
Creepage distance	Primary to secondary side	16.2			mm
	Secondary to secondary side	14.2			mm
Clearance distance	Primary to secondary side	16.2			mm
	Secondary to secondary side	6.5			mm
Output	Remarks	Min	Typ	Max	Unit
Blocking capacitance	Vx+ to COM x		9.4		$\mu$ F
	COM x to Vx-		9.4		$\mu$ F

### Footnotes to the Key Data

- 1) The maximum peak gate current refers to the highest current level occurring during the product lifetime. It is an absolute value and does also apply for short pulses.
- 2) The average supply input current is limited for thermal reasons. Higher values than specified by the absolute maximum rating are permissible (e.g. during power supply start up) if the average remains below the given value, provided the average is taken over a time period which is shorter than the thermal time constants of the driver in the application.
- 3) There is no means of actively controlling or limiting the input current in the driver. In the case of start-up with very high blocking capacitor values, or in case of short circuit at the output, the supply input current has to be limited externally.
- 4) The maximum output power must not be exceeded at any time during operation. The absolute maximum rating must also be observed for time periods shorter than the thermal time constants of the driver in the application.
- 5) An extended output power range is specified for maximum ambient temperatures of 70°C.

---

## Preliminary Data Sheet

- 6) Undervoltage monitoring of the primary-side supply voltage ( $V_{DD}$  to GND). If the voltage drops below this limit, a fault is transmitted to both outputs SOA and SOB and the IGBTs are switched off.
- 7) Undervoltage monitoring of the secondary-side supply voltage ( $V_{x+}$  to COM x and COM x to  $V_{x-}$  which correspond with the approximate turn-on and turn-off gate-emitter voltages). If the corresponding voltage drops below this limit, the IGBT is switched off and a fault is transmitted to the corresponding SOx output on the primary side.
- 8) The delay time is measured between 50% of the input signal and 10% (turn-on) or 90% (turn-off) of the corresponding output.
- 9) Transmission delay of fault state from the secondary side to the primary status output.
- 10) The blocking time sets a minimum time span between the end of any fault state and the start of normal operation (remove fault from pin SOx). The value of the blocking time is programmed on the driver and cannot be modified externally.
- 11) HiPot testing (= dielectric testing) must generally be restricted to suitable components. This gate driver is suited for HiPot testing. Nevertheless, it is strongly recommended to limit the testing time to 1s slots as stipulated by EN 50178. Excessive HiPot testing at voltages much higher than  $1200V_{AC(eff)}$  may lead to insulation degradation. No degradation has been observed over 1min. testing at  $5000V_{AC(eff)}$ . The transformer of every production sample shipped to customers has undergone 100% testing at the given value for 1s.
- 12) Partial discharge measurement is performed in accordance with IEC 60270 and isolation coordination specified in EN 50178. The partial discharge extinction voltage between primary and either secondary side is coordinated for safe isolation to EN 50178.
- 13) The dead time is measured between 50% voltage swing of the gate-emitter voltage which is turned off and 50% voltage swing of the gate-emitter voltage which is turned-on.
- 14) The storage temperature inside the original package (1) or in case the coating material of coated products may touch external parts (2) must be limited to the given value. Otherwise, it is limited to 90°C.
- 15) The component surface temperature, which may strongly vary depending on the operating condition, must be limited to the given value for coated driver versions to ensure long-term reliability of the coating material.

### Legal Disclaimer

The statements, technical information and recommendations contained herein are believed to be accurate as of the date hereof. All parameters, numbers, values and other technical data included in the technical information were calculated and determined to our best knowledge in accordance with the relevant technical norms (if any). They may base on assumptions or operational conditions that do not necessarily apply in general. We exclude any representation or warranty, express or implied, in relation to the accuracy or completeness of the statements, technical information and recommendations contained herein. No responsibility is accepted for the accuracy or sufficiency of any of the statements, technical information, recommendations or opinions communicated and any liability for any direct, indirect or consequential loss or damage suffered by any person arising therefrom is expressly disclaimed.

---

## Preliminary Data Sheet

### Ordering Information

Our international terms and conditions of sale apply.

Type Designation	Description
2SD300C17A1	Dual-channel SCALE-2 driver core (PCB thickness: 1.55mm)
2SD300C17A1C	Dual-channel SCALE-2 driver core (PCB thickness: 1.55mm, conformal coating)

Product home page: [www.power.com/igbt-driver/go/2SD300C17](http://www.power.com/igbt-driver/go/2SD300C17)

Refer to [www.power.com/igbt-driver/go/nomenclature](http://www.power.com/igbt-driver/go/nomenclature) for information on driver nomenclature

### Information about Other Products

**For other drivers, product documentation, and application support**

Please click: [www.power.com](http://www.power.com)

---

Preliminary Data Sheet

**Power Integrations Sales Offices**
**WORLD HEADQUARTERS**

5245 Hellyer Avenue  
San Jose, CA 95138 USA  
Tel: +1-408-414-9200  
Fax: +1-408-414-9765  
Email: [usasales@power.com](mailto:usasales@power.com)

**AMERICAS WEST**

5245 Hellyer Avenue  
San Jose, CA 95138 USA  
Tel: +1-408-414-8778  
Fax: +1-408-414-3760  
Email: [usasales@power.com](mailto:usasales@power.com)

**GERMANY** (AC-DC/LED Sales)

Lindwurmstrasse 114  
80337 München, Germany  
Tel: +49-89-5527-39100  
Fax: +49-89-1228-5374  
Email: [eurosales@power.com](mailto:eurosales@power.com)

**INDIA** (Mumbai)

Unit: 106-107, Sagar Tech Plaza-B  
Sakinaka, Andheri Kurla Road  
Mumbai, Maharashtra 400072 India  
Tel 1: +91-22-4003-3700  
Tel 2: +91-22-4003-3600  
Email: [indiasales@power.com](mailto:indiasales@power.com)

**JAPAN**

Kosei Dai-3 Bldg.  
2-12-11, Shin-Yokohama, Kohoku-ku  
Yokohama-shi, Kanagawa  
Japan 222-0033  
Tel: +81-45-471-1021  
Fax: +81-45-471-3717  
Email: [japansales@power.com](mailto:japansales@power.com)

**TAIWAN**

5F, No. 318, Nei Hu Rd., Sec. 1  
Nei Hu Dist.  
Taipei, 114 Taiwan  
Tel: +886-2-2659-4570  
Fax: +886-2-2659-4550  
Email: [taiwansales@power.com](mailto:taiwansales@power.com)

**AMERICAS EAST**

7360 McGinnis Ferry Road  
Suite 225  
Suwanee, GA 30024 USA  
Tel: +1-678-957-0724  
Fax: +1-678-957-0784  
Email: [usasales@power.com](mailto:usasales@power.com)

**CHINA** (Shanghai)

Room 2410, Charity Plaza  
No. 88 North Caoxi Road  
Shanghai, 200030 China  
Tel: +86-21-6354-6323  
Fax: +86-21-6354-6325  
Email: [chinasales@power.com](mailto:chinasales@power.com)

**GERMANY** (Gate Driver Sales)

HellwegForum 1  
59469 Ense, Germany  
Tel: +49-2938-64-39990  
Email: [igbt-driver.sales@power.com](mailto:igbt-driver.sales@power.com)

**INDIA** (New Dehli)

#45, Top Floor  
Okhla Industrial Area, Phase - III  
New Dehli, 110020 India  
Tel 1: +91-11-4055-2351  
Tel 2: +91-11-4055-2353  
Email: [indiasales@power.com](mailto:indiasales@power.com)

**KOREA**

RM602, 6FL, 22  
Teheran-ro 87-gil, Gangnam-gu  
Seoul, 06164 Korea  
Tel: +82-2-2016-6610  
Fax: +82-2-2016-6630  
Email: [koreasales@power.com](mailto:koreasales@power.com)

**UNITED KINGDOM**

Bulding 5, Suite 21  
The Westbrook Centre  
Milton Road  
Cambridge, CB4 1YG United Kingdom  
Tel: +44-7823-557-484  
Email: [eurosales@power.com](mailto:eurosales@power.com)

**AMERICAS CENTRAL**

333 Sheridan Road  
Winnetka, IL 60093 USA  
Tel: +1-847-721-6293  
Email: [usasales@power.com](mailto:usasales@power.com)

**CHINA** (Shenzhen)

17/F, Hivac Building, No 2  
Keji South 8th Road, Nanshan District  
Shenzhen, 518057 China  
Tel: +86-755-8672-8689  
Fax: +86-755-8672-8690  
Email: [chinasales@power.com](mailto:chinasales@power.com)

**INDIA** (Bangalore)

#1, 14th Main Road  
Vasanthangar  
Bangalore, 560052 India  
Tel 1: +91-80-4113-8020  
Tel 2: +91-80-4113-8028  
Fax: +91-80-4113-8023  
Email: [indiasales@power.com](mailto:indiasales@power.com)

**ITALY**

Via Milanese 20  
20099 Sesto San Giovanni (MI), Italy  
Tel: +39-02-4550-8708  
Email: [eurosales@power.com](mailto:eurosales@power.com)

**SINGAPORE**

51 Newton Road  
#19-01/05 Goldhill Plaza  
Singapore, 308900  
Tel 1: +65-6358-2160  
Tel 2: +65-6358-4480  
Fax: +65-6358-2015  
Email: [singaporesales@power.com](mailto:singaporesales@power.com)

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Power Integrations:](#)

[2SD300C17A1](#)