

SIOV metal oxide varistors

Leaded varistors, AdvanceD-MP, S10 series

Series/Type: B722*

Date: January 2018

© EPCOS AG 2018. Reproduction, publication and dissemination of this publication, enclosures hereto and the information contained therein without EPCOS' prior express consent is prohibited.

EPCOS AG is a TDK Group Company.



Leaded varistors B722°

AdvanceD-MP, S10 series

Construction

- Round varistor element, leaded
- Coating: epoxy resin, flame-retardant to UL 94 V-0
- Terminals: tinned wire

Features

- Wide operating voltage range 175 ... 680 V_{RMS}
- All types duty cycle @ 6 kV/ 3 kA = >10 pulses, according to IEC 62368-1; G.8.2 and IEC 60950-1; Annex Q. IEC 61051-2
- All types I_n @ 2 kA => 15 impules acc. to UL, 4th edition surge current generator (8/20 µs), tpye 5 listed
- Multiple pulse handling capability

Approvals

- UL
- CSA
- VDE
- IEC

Delivery mode

- Bulk (standard), taped versions on reel or in Ammo pack upon request.
- For further details refer to chapter "Taping, packaging and lead configuration" for leaded varistors.

General technical data

Climatic category	to IEC 60068-1	40/105/56	
Operating temperature	to IEC 61051	-40 +105	°C
Storage temperature		-40 +125	°C
Electric strength	to IEC 61051	≥ 2.5	kV _{RMS}
Insulation resistance	to IEC 61051	≥ 100	$M\Omega$



AdvanceD-MP, S10 series



Electrical specifications and ordering codes Maximum ratings ($T_A = 105$ °C)

Ordering code	Туре	V_{RMS}	V_{DC}	i _{max}	I _n 1)	W _{max}	P _{max}
	(untaped)			(8/20 µs)	(8/20 µs)	(2 ms)	
	SIOV-			1 time	15 times		
		V	V	Α	Α	J	W
B72210P2171K101	S10K175E2K1	175	225	3500	2000	40.0	0.40
B72210P2271K101	S10K275E2K1	275	350	3500	2000	60.0	0.40
B72210P2301K101	S10K300E2K1	300	385	3500	2000	65.0	0.40
B72210P2321K101	S10K320E2K1	320	420	3500	2000	72.0	0.40
B72210P2351K101	S10K350E2K1	350	460	3500	2000	77.0	0.40
B72210P2381K101	S10K385E2K1	385	505	3500	2000	82.0	0.40
B72210P2421K101	S10K420E2K1	420	560	3500	2000	87.0	0.40
B72210P2461K101	S10K460E2K1	460	615	3500	2000	92.0	0.40
B72210P2511K101	S10K510E2K1	510	670	3500	2000	92.0	0.40
B72210P2551K101	S10K550E2K1	550	745	3500	2000	97.0	0.40
B72210P2621K101	S10K625E2K1	625	825	3500	2000	105.0	0.40
B72210P2681K101	S10K680E2K1	680	895	3500	2000	115.0	0.40

¹⁾ **Note:** Nominal discharge current I_n according to UL 1449, 4th edition.

Characteristics (T_A = 25 $^{\circ}$ C)

Ordering code	Туре	V_{v}	ΔV_{v}	$V_{c,max}$	i _c	C_{typ}
•	(untaped)	(1 mA)	(1 mA)	(i _c)		(1 kHz)
	SIOV-	V	%	V	Α	pF
B72210P2171K101	S10K175E2K1	270	±10	455	25.0	500
B72210P2271K101	S10K275E2K1	430	±10	710	25.0	315
B72210P2301K101	S10K300E2K1	470	±10	775	25.0	285
B72210P2321K101	S10K320E2K1	510	±10	840	25.0	265
B72210P2351K101	S10K350E2K1	560	±10	910	25.0	240
B72210P2381K101	S10K385E2K1	620	±10	1025	25.0	230
B72210P2421K101	S10K420E2K1	680	±10	1120	25.0	210
B72210P2461K101	S10K460E2K1	750	±10	1240	25.0	190
B72210P2511K101	S10K510E2K1	820	±10	1355	25.0	180
B72210P2551K101	S10K550E2K1	910	±10	1500	25.0	160
B72210P2621K101	S10K625E2K1	1000	±10	1650	25.0	150
B72210P2681K101	S10K680E2K1	1100	±10	1815	25.0	135






AdvanceD-MP, S10 series

B722*

Dimensional drawings



1) Seating plane to IEC 60717

VAR0408-C-E

Weight

Nominal diameter	V_{RMS}	Weight
mm	٧	g
10	175 680	1.7 3.5

The weight of varistors in between these voltage classes can be interpolated.

Dimensions

Ordering code	[e] ±1	a (typical)	W _{max}	th _{max}	h _{max}	I _{min}	d ±0.05
	mm	mm	mm	mm	mm	mm	mm
B72210P2171K101	7.5	2.4	12.0	5.1	16.0	25.0	0.8
B72210P2271K101	7.5	3.2	12.0	5.9	16.0	25.0	0.8
B72210P2301K101	7.5	3.5	12.0	6.1	16.0	25.0	0.8
B72210P2321K101	7.5	3.7	12.0	6.3	16.0	25.0	0.8
B72210P2351K101	7.5	3.9	12.5	6.7	16.5	25.0	0.8
B72210P2381K101	7.5	4.2	12.5	7.7	16.5	25.0	0.8
B72210P2421K101	7.5	4.5	12.5	8.1	16.5	25.0	0.8
B72210P2461K101	7.5	4.7	12.5	8.4	16.5	25.0	0.8
B72210P2511K101	7.5	4.8	13.0	8.8	17.0	25.0	0.8
B72210P2551K101	7.5	4.9	13.0	9.3	17.0	25.0	0.8
B72210P2621K101	7.5	5.2	13.0	9.8	17.0	25.0	0.8
B72210P2681K101	7.5	5.4	13.0	10.4	17.0	25.0	0.8



Leaded varistors B722* AdvanceD-MP, S10 series



Reliability data

Test	Test methods/conditions	Requirement
Varistor voltage	The voltage between two terminals with the specified measuring current applied is called V_V (1 mA _{DC} @ 0.2 2 s).	To meet the specified value
Clamping voltage	The maximum voltage between two terminals with the specified standard impulse current (8/20 µs) applied.	To meet the specified value
Endurance at upper category temperature	1000 h at UCT After having continuously applied the maximum allowable AC voltage at UCT ±2 °C for 1000 h, the specimen shall be stored at room temperature and normal humidity for 1 to 2 h. Thereafter, the change of V _V shall be measured.	IΔV/V (1 mA)I ≤10%
Surge current derating, 8/20 μs	10 surge currents (8/20 μs), unipolar, interval 30 s, amplitude corresponding to derating curve for 10 impulses at 20 μs	I∆V/V (1 mA)I ≤10% (measured in direction of surge current) No visible damage
Surge current derating, 2 ms	10 surge currents (2 ms), unipolar, interval 120 s, amplitude corresponding to derating curve for 10 impulses at 2 ms	I∆V/V (1 mA)I ≤10% (measured in direction of surge current) No visible damage
Electric strength	IEC 61051-1, test 4.9.2 Metal balls method, 2500 V _{RMS} , 60 s The varistor is placed in a container holding 1.6 ±0.2 mm diameter metal balls such that only the terminations of the varistor are protruding. The specified voltage shall be applied between both terminals of the specimen connected together and the electrode inserted between the metal balls.	No breakdown



B722*



Leaded varistors

AdvanceD-MP, S10 series

Test	Test methods/conditions	Requirement	
Climatic sequence	The specimen shall be subjected to: a) dry heat at UCT, 16 h, IEC 60068-2-2, test Ba b) damp heat, 1st cycle: 55 °C, 93% r. H., 24 h, IEC 60068-2-30, test Db c) cold, LCT, 2 h, IEC 60068-2-1, test Aa d) damp heat, additional 5 cycles: 55 °C/25 °C, 93% r. H., 24 h/cycle, IEC 60068-2-30, test Db.	$ \Delta V/V $ (1 mA) $ $ ≤10% $ $ R _{ins} ≥100 MΩ	
	Then the specimen shall be stored at room temperature and normal humidity for 1 to 2 h. Thereafter, the change of $V_{\rm V}$ shall be measured. Thereafter, insulation resistance $R_{\rm ins}$ shall be measured at $V=500~V$.		
Rapid change of temperature	IEC 60068-2-14, test Na, LCT/UCT, dwell time 30 min, 5 cycles	l∆V/V (1 mA)l ≤5% No visible damage	
Damp heat, steady state	IEC 60068-2-78, test Ca The specimen shall be subjected to 40 ± 2 °C, 90 to 95% r. H. for 56 days without load / with 10% of the maximum continuous DC operating voltage V _{DC} . Then stored at room temperature and normal humidity for 1 to 2 h. Thereafter, the change of V _V shall be measured. Thereafter, insulation resistance R _{ins} shall be measured at V = 500 V (insulated varistors only).	I ΔV/V (1 mA) I ≤10% R_{ins} ≥100 MΩ	



Leaded varistors B722* AdvanceD-MP, S10 series



Test Test methods/conditions Requirement Solderability IEC 60068-2-20, test Ta. The inspection shall be carried out under adequate method 1 with modified conditions for light with normal evesight or lead-free solder alloys: 245 °C. 3 s: with the assistance of a After dipping the terminals to a depth of magnifier capable of giving approximately 3 mm from the body in a a magnification of 4 to soldering bath of 245 °C for 3 s. the 10 times. The dipped terminals shall be visually examined. surface shall be covered with a smooth and bright solder coating with no more than small amounts of scattered imperfections such as pinholes or un-wetted or de-wetted areas. These imperfections shall not be concentrated in one area. Resistance to soldering IEC 60068-2-20, test Tb, method 1A, $|\Delta V/V (1 \text{ mA})| \leq 5\%$ 260 °C, 10 s: heat No visible damage Each lead shall be dipped into a solder bath having a temperature of 260 ±5 °C to a point 2.0 to 2.5 mm from the body of the specimen, be held there for 10 \pm 1 s and then be stored at room temperature and normal humidity for 1 to 2 h. The change of V_V shall be measured and the specimen shall be visually examined. Tensile strength IEC 60068-2-21, test Ua1 |ΔV/V (1 mA)| ≤5% After gradually applying the force No break of solder joint, specified below and keeping the unit no wire break fixed for 10 s. the terminal shall be visually examined for any damage. Force for wire diameter: 0.6 mm = 10 N0.8 mm = 10 N1.0 mm = 20 N





Leaded varistors B722* AdvanceD-MP, S10 series

Test	Test methods/conditions	Requirement
Vibration	IEC 60068-2-6, test Fc, method B4	l∆V/V (1 mA)l ≤5%
	Frequency range: $10 \dots 55 \text{ Hz}$ Amplitude: 0.75 mm or 98 m/s^2 Duration: $6 \text{ h} (3 \cdot 2 \text{ h})$ Pulse: sine wave After repeatedly applying a single harmonic vibration according to the table above. The change of V_V shall be measured and the specimen shall be visually examined.	No visible damage
Bump	IEC 60068-2-29, test Eb Pulse duration: 6 ms Max. acceleration: 400 m/s² Number of bumps: 4000 Pulse: half sine	l∆V/V (1 mA)l ≤5% No visible damage
Fire hazard	IEC 60695-11-5 (needle flame test) Severity: vertical 10 s	5 s max.

Note:

UCT = Upper category temperature LCT = Lower category temperature

 R_{ins} = Insulation resistance




Leaded varistors B722*

AdvanceD-MP, S10 series



v/i characteristics

v = f(i) - for explanation of the characteristics refer to "General technical information", 1.6.3 A = Leakage current, B = Protection level } for worst-case varistor tolerances



SIOV-S10 ... E2K1






AdvanceD-MP, S10 series

B722


Derating curves

Maximum surge current $i_{max} = f(t_r, pulse train)$

For explanation of the derating curves refer to "General technical information", section 1.8.1



SIOV-S10K175 ... K460E2K1



SIOV-S10K510 ... K680E2K1



Leaded varistors B722*


AdvanceD-MP, S10 series



Taping, packaging and lead configuration

1 EPCOS ordering code system

For leaded varistors








B722

AdvanceD-MP, S10 series


Taping and packaging of leaded varistors 2

Tape packaging for lead spacing @ = 5 fully conforms to IEC 60286-2, while for lead spacings e = 7.5 and 10 the taping mode is based on this standard.

2.1 Taping in accordance with IEC 60286-2 for lead spacing 5.0 mm



2.2 Taping based on IEC 60286-2 for lead spacing 7.5 and 10 mm





Leaded varistors B722*

AdvanceD-MP, S10 series



2.3 Tape dimensions (in mm)

Sym-	<i>e</i> = 5.0	Tolerance	<i>e</i> = 7.5	Tolerance	<i>e</i> = 10.0	Tolerance	Remarks
bol							
w		max.		max.		max.	see tables in
							each series
th		max.		max.		max.	under
							"Dimensions"
d	0.6	±0.05	0.8	±0.05	1.0	±0.05	
P_0	12.7	±0.3	12.71)	±0.3	12.7	±0.3	±1 mm/20
							sprocket holes
P ₁	3.85	±0.7	8.95	±0.8	7.7	±0.8	
F	5.0	+0.6/-0.1	7.5	±0.8	10.0	±0.8	
Δh	0	±2.0	depends of	n s	depends on	S	measured at
Δр	0	±1.3	0	±2.0	0	±2.0	top of compo-
							nent body
W	18.0	±0.5	18.0	±0.5	18.0	±0.5	
W_{o}	5.5	min.	11.0	min.	11.0	min.	Peel-off
							force ≥ 5 N
W_1	9.0	±0.5	9.0	+0.75/-0.5	9.0	+0.75/-0.5	
W_2	3.0	max.	3.0	max.	3.0	max.	
Н	18.0	+2.0/-0	18.0	+2.0/-0	18.0	+2.0/-0	2)
H_0	16.0	±0.5	16.0	±0.5	16.0	±0.5	3)
	(18.0)		(18.0)				
H ₁	32.2	max.	45.0	max.	45.0	max.	
$\overline{D_0}$	4.0	±0.2	4.0	±0.2	4.0	±0.2	
t	0.9	max.	0.9	max.	0.9	max.	without lead
L	11.0	max.	11.0	max.	11.0	max.	
L_1	0.5	max.					

¹⁾ Taping with $P_0 = 15.0$ mm upon request

²⁾ Applies only to uncrimped types

³⁾ Applies only to crimped types (H₀ = 18 upon request)



B722



Leaded varistors

AdvanceD-MP, S10 series

U U


2.4 Taping mode


Example: B72210S0271K1 5 1

Digit 14

Digit 14	Taping	Reel type	Seating plane height H ₀	Seating plane height H	Pitch distance
_	mode		for crimped types	for uncrimped types	P_0
			mm	mm	mm
0	_	Bulk	-	-	_
1	G	1	16	18	12.7
2	G2	I	18	_	12.7
3	G3	II	16	18	12.7
4	G4	II	18	_	12.7
5	G5	Ш	16	18	12.7
6	GA	Ammo pack	16	18	12.7
7	G2A	Ammo pack	18	_	12.7
Internal	coding fo	r special tapin	g		
	G6	Ш	18	_	12.7
	G10	II	16	18	15.0
	G11	II	18	_	15.0
	G10A	Ammo pack	16	18	15.0
	G11A	Ammo pack	18	_	15.0

2.5 Reel dimension





Dimensions (in mm)

Reel type	d	f	n	w
I	360 max.	31 ±1	approx. 45	54 max.
II	360 max.	31 ±1	approx. 55	64 max.
III	500 max.	23 ±1	approx. 59	72 max.


If reel type III is not compatible with insertion equipment because of its large diameter, nominal disk diameter 10 mm and 14 mm can be supplied on reel II upon request (taping mode G3).







2.6 Ammo pack dimensions



3 Lead configuration

Straight leads are standard for disk varistors. Other lead configurations as crimp style or customer-specific lead wire length according to 3.1, 3.2, 3.3 and 3.4 are optional. Crimped leads (non-standard) are differently crimped for technical reasons; the individual crimp styles are denoted by consecutive numbers (S, S2 through S5) as shown in the dimensional drawings below.

The crimp styles of the individual types can be seen from the type designation in the ordering tables.

3.1 Crimp style mode

Example: B72210S0271K 5 01 Digit 13

Digit 13 of ordering code	Crimp style	Figure
1	Standard, straight leads	1
2	S2	2
3	S3	3
5	S5	4
Available upon request	·	
Internal coding	_	5






B722⁹

AdvanceD-MP, S10 series


Standard leads and non-standard crimp styles 3.2

The basic dimensions in figure 1 to 5 are valid for types with either round or square (EnergetiQ series) component head.

Standard, straight leads




Non-standard, crimp style S2



1) Seating plane to IEC 60717 VAR0411-F-E

Non-standard, crimp style S3




1) Seating plane to IEC 60717 VAR0396-R-E

Figure 1

Figure 2

Figure 3

Non-standard, crimp style S5



1) Seating plane to IEC 60717 VAR0726-M-E

Figure 4



Leaded varistors B722*

AdvanceD-MP, S10 series




3.3 Trimmed leads (non-standard)

Varistors with cut leads available upon request.

Lead length tolerances:

Straight leads +/-0.8 mmCrimped leads +/-0.5 mmMinimum lead length 3.0 mm



- 1) Seating plane to IEC 60717
- *) For round component head
- **) For EnergetiQ series, square component head

Figure 5





R722

AdvanceD-MP, S10 series

Cautions and warnings

General

- EPCOS metal oxide varistors are designed for specific applications and should not be used for purposes not identified in our specifications, application notes and data books unless otherwise agreed with EPCOS during the design-in-phase.
- Ensure suitability of SIOVs through reliability testing during the design-in phase. SIOVs should be evaluated taking into consideration worst-case conditions.
- 3. For applications of SIOVs in line-to-ground circuits based on various international and local standards there are restrictions existing or additional safety measures required.

Storage

- 1. Store SIOVs only in original packaging. Do not open the package prior to processing.
- 2. Recommended storage conditions in original packaging:

Storage temperature: -25 °C ... +45 °C,

Relative humidity: <75% annual average,

<95% on maximum 30 days a year.

Dew precipitation: is to be avoided.

- 3. Avoid contamination of an SIOV's during storage, handling and processing.
- 4. Avoid storage of SIOVs in harmful environments that can affect the function during long-term operation (examples given under operation precautions).
- The SIOV type series should be soldered after shipment from EPCOS within the time specified:

SIOV-S, -Q, -LS, -B, -SNF 24 months ETFV/ T series. -CU 12 months.

Handling

- 1. SIOVs must not be dropped.
- 2. Components must not be touched with bare hands. Gloves are recommended.
- Avoid contamination of the surface of SIOV electrodes during handling, be careful of the sharp edge of SIOV electrodes.

Soldering (where applicable)

- 1. Use rosin-type flux or non-activated flux.
- Insufficient preheating may cause ceramic cracks.
- 3. Rapid cooling by dipping in solvent is not recommended.
- 4. Complete removal of flux is recommended.
- Temperatures of all preheat stages and the solder bath must be strictly controlled especially for T series (T14 and T20).



Leaded varistors B722* AdvanceD-MP, S10 series



Mounting

- Potting, sealing or adhesive compounds can produce chemical reactions in the SIOV ceramic that will degrade the component's electrical characteristics.
- 2. Overloading SIOVs may result in ruptured packages and expulsion of hot materials. For this reason SIOVs should be physically shielded from adjacent components.

Operation

- 1. Use SIOVs only within the specified temperature operating range.
- 2. Use SIOVs only within the specified voltage and current ranges.
- Environmental conditions must not harm SIOVs. Use SIOVs only in normal atmospheric conditions. Avoid use in deoxidizing gases (chlorine gas, hydrogen sulfide gas, ammonia gas, sulfuric acid gas etc), corrosive agents, humid or salty conditions. Contact with any liquids and solvents should be prevented.

Display of ordering codes for EPCOS products

The ordering code for one and the same EPCOS product can be represented differently in data sheets, data books, other publications, on the EPCOS website, or in order-related documents such as shipping notes, order confirmations and product labels. The varying representations of the ordering codes are due to different processes employed and do not affect the specifications of the respective products. Detailed information can be found on the Internet under www.epcos.com/orderingcodes





B722*

AdvanceD-MP, S10 series

Symbols and terms

Symbol	Term
С	Capacitance
C_{typ}	Typical capacitance
i	Current
i _c	Current at which V _{c, max} is measured
I _{leak}	Leakage current
i _{max}	Maximum surge current (also termed peak current)
I _{max}	Maximum discharge current
I _n	Nominal discharge current to UL 1449
LCT	Lower category temperature
L_{typ}	Typical inductance
P_{max}	Maximum average power dissipation
R_{ins}	Insulation resistance
R_{min}	Minimum resistance
T_A	Ambient temperature
t _r	Duration of equivalent rectangular wave
UCT	Upper category temperature
v	Voltage
V_{clamp}	Clamping voltage
V _{c, max}	Maximum clamping voltage at specified current i _c
V_{DC}	DC operating voltage
V_{jump}	Maximum jump start voltage
V_{max}	Maximum voltage
V_{op}	Operating voltage
V_{RMS}	AC operating voltage, root-mean-square value
$V_{RMS,\;op,\;max}$	Root-mean-square value of max. DC operating voltage incl. ripple current
V_{surge}	Super imposed surge voltage
V_{v}	Varistor voltage
ΔV_{V}	Tolerance of varistor voltage
W_{LD}	Maximum load dump
W_{max}	Maximum energy absorption
е	Lead spacing

All dimensions are given in mm.

The commas used in numerical values denote decimal points.



Important notes

The following applies to all products named in this publication:

- 1. Some parts of this publication contain statements about the suitability of our products for certain areas of application. These statements are based on our knowledge of typical requirements that are often placed on our products in the areas of application concerned. We nevertheless expressly point out that such statements cannot be regarded as binding statements about the suitability of our products for a particular customer application. As a rule we are either unfamiliar with individual customer applications or less familiar with them than the customers themselves. For these reasons, it is always ultimately incumbent on the customer to check and decide whether a product with the properties described in the product specification is suitable for use in a particular customer application.
- 2. We also point out that in individual cases, a malfunction of electronic components or failure before the end of their usual service life cannot be completely ruled out in the current state of the art, even if they are operated as specified. In customer applications requiring a very high level of operational safety and especially in customer applications in which the malfunction or failure of an electronic component could endanger human life or health (e.g. in accident prevention or life-saving systems), it must therefore be ensured by means of suitable design of the customer application or other action taken by the customer (e.g. installation of protective circuitry or redundancy) that no injury or damage is sustained by third parties in the event of malfunction or failure of an electronic component.
- 3. The warnings, cautions and product-specific notes must be observed.
- 4. In order to satisfy certain technical requirements, some of the products described in this publication may contain substances subject to restrictions in certain jurisdictions (e.g. because they are classed as hazardous). Useful information on this will be found in our Material Data Sheets on the Internet (www.tdk-electronics.tdk.com/material). Should you have any more detailed questions, please contact our sales offices.
- 5. We constantly strive to improve our products. Consequently, the products described in this publication may change from time to time. The same is true of the corresponding product specifications. Please check therefore to what extent product descriptions and specifications contained in this publication are still applicable before or when you place an order.
 - We also **reserve the right to discontinue production and delivery of products**. Consequently, we cannot guarantee that all products named in this publication will always be available. The aforementioned does not apply in the case of individual agreements deviating from the foregoing for customer-specific products.
- 6. Unless otherwise agreed in individual contracts, all orders are subject to our General Terms and Conditions of Supply.
- 7. Our manufacturing sites serving the automotive business apply the IATF 16949 standard. The IATF certifications confirm our compliance with requirements regarding the quality management system in the automotive industry. Referring to customer requirements and customer specific requirements ("CSR") TDK always has and will continue to have the policy of respecting individual agreements. Even if IATF 16949 may appear to support the acceptance of unilateral requirements, we hereby like to emphasize that only requirements mutually agreed upon can and will be implemented in our Quality Management System. For clarification purposes we like to point out that obligations from IATF 16949 shall only become legally binding if individually agreed upon.



Important notes

8. The trade names EPCOS, CeraCharge, CeraDiode, CeraLink, CeraPad, CeraPlas, CSMP, CTVS, DeltaCap, DigiSiMic, ExoCore, FilterCap, FormFit, LeaXield, MiniBlue, MiniCell, MKD, MKK, MotorCap, PCC, PhaseCap, PhaseCube, PhaseMod, PhiCap, PowerHap, PQSine, PQvar, SIFERRIT, SIFI, SIKOREL, SilverCap, SIMDAD, SiMic, SIMID, SineFormer, SIOV, ThermoFuse, WindCap are trademarks registered or pending in Europe and in other countries. Further information will be found on the Internet at www.tdk-electronics.tdk.com/trademarks.

Release 2018-10

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

EPCOS / TDK:

B72210P2271K101	B72210P2301K101	B72210P2321K101	B72210P2381K101	B72210P2421K101
B72210P2461K101	B72210P2171K101	B72210P2621K101	B72210P2511K101	B72210P2351K101
B72210P2551K101	B72210P2681K101	B72210P2301K151	B72210P2141K592	B72210P2271K191
B72210P2271K392	B72210P2301K192	B72210P2301K302	B72210P2351K692	B72210P2381K151
B72210P2381K903	B72210P2421K391	B72210P2421K504	B72210P2301K391	B72210P2301K502
B72210P2301K691	B72210P2321K202	B72210P2321K903	B72210P2351K103	