

Cascadable Amplifier 5 to 300 MHz

Rev. V7

Features

- AVAILABLE IN SURFACE MOUNT
- HIGH GAIN 18.5 dB (TYP.)
- HIGH OUTPUT POWER +18.5 dBm (TYP.)
- HIGH THIRD ORDER IP +30 dBm (TYP.)

Description

The A88-1 RF amplifier is a discrete thin film hybrid design, which incorporates the use of thin film manufacturing processes for accurate performance and high reliability. This single stage bipolar transistor feedback amplifier design displays impressive performance over a broadband frequency range. An active DC biasing network is used for temperature-stable performance, in addition to an RF Choke, used for power supply decoupling.


Both TO-8 and Surface Mount packages are hermetically sealed, and MIL-STD-883 environmental screening is available.

Ordering Information

Part Number	Package	
MAAM-010132-0A8801	TO-8	
SMA88-1	Surface Mount	
MAAM-010132-CA8801	SMA Connectorized **	

^{**} The connectorized version is not RoHs compliant.

Product Image



Electrical Specifications: $Z_0 = 50\Omega$, $V_{CC} = +15 V_{DC}$

Parameter	Units	Typical	Guaranteed	
Farameter		25°C	0º to 50ºC	-54º to +85ºC*
Frequency	MHz	2-300	5-300	5-300
Small Signal Gain (min)	dB	18.5	17.5	17.0
Gain Flatness (max)	dB	±0.4	±0.6	±0.8
Reverse Isolation	dB	22		
Noise Figure (max)	dB	3.8	5.0	5.5
Power Output @ 1 dB comp. (min)	dBm	18.5	17.0	16.5
IP3	dBm	+30		
IP2	dBm	+42		
Second Order Harmonic IP	dBm	+48		
VSWR Input / Output (max)		1.4:1 / 1.4:1	1.7:1 / 1.7:1	1.9:1 / 1.9:1
DC Current @ 15 Volts (max)	mA	63	65	67

Absolute Maximum Ratings

Parameter	Absolute Maximum	
Storage Temperature	-62°C to +125°C	
Case Temperature	+125°C	
DC Voltage	+17 V	
Continuous Input Power	+13 dBm	
Short Term Input power (1 minute max.)	100 mW	
Peak Power (3 µsec max.)	0.5 W	
"S" Series Burn-In Temperature (case)	+125°C	

Thermal Data: $V_{CC} = +15 V_{DC}$

Parameter	Rating
Thermal Resistance θ_{jc}	45°C/W
Transistor Power Dissipation P _d	0.393 W
Junction Temperature Rise Above Case T _{jc}	18°C

^{*} Over temperature performance limits for part number CA8801, guaranteed from 0°C to +50°C only.

typical. Mechanical outline has been fixed. Engineering samples and/or test data may be available. Commitment to produce in volume is not guaranteed.

ADVANCED: Data Sheets contain information regarding a product M/A-COM Technology Solutions is considering for development. Performance is based on target specifications, simulated results, and/or prototype measurements. Commitment to develop is not guaranteed.

PRELIMINARY: Data Sheets contain information regarding a product M/A-COM Technology Solutions has under development. Performance is based on engineering tests. Specifications are

[•] North America Tel: 800.366.2266 • Europe Tel: +353.21.244.6400

<sup>India Tel: +91.80.43537383
India Tel: +91.80.43537383
China Tel: +86.21.2407.1588
Visit www.macomtech.com for additional data sheets and product information.</sup>




Cascadable Amplifier 5 to 300 MHz

Rev. V7


Typical Performance Curves at +25°C

Gain 350 200 250 300 Noise Figure 12740 -15Vdc +57 de 150 200 250 300 FREQUENCY - MHz Power Output* 1250 FREQUENCY - MHz Intercept Point 3rd ORDER TWO-TON 100 150 200 250 300 350 FRECUENCY - MHz VSWR 3.0 2.5 NPUT OUTPUT-5 2.0 150 200 250 300 350 FREQUENCY - MHz


Outline Drawing: TO-8 *



Outline Drawing: Surface Mount



Outline Drawing: SMA Connectorized



* Dimensions are inches (millimeters) ±0.015 (0.38) unless otherwise specified.

• North America Tel: 800.366.2266 • Europe Tel: +353.21.244.6400