

Fork-type cable lug - C-FCI 1,5/M3,5 - 3240033

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)




Fork-type cable lug, red, 0.5 - 1.5 mm², M3,5

Your advantages

- ✓ The fork-type cable lugs without plastic sleeve feature a hard-soldered neck. In conjunction with the CRIMPFOX-RC ... and CRIMPFOX-RCI ... pliers they can be used to achieve maximum conductor pull-out forces
- ✓ The insulated versions are halogen-free and feature "EASY ENTRY" technology

Key Commercial Data

| | |
|--------------|---|
| Packing unit | 100 pc |
| GTIN |  4 046356 451109 |
| GTIN | 4046356451109 |

Technical data

Dimensions

| | |
|---|---------|
| Length (b) | 22 mm |
| Width (a) | 5.7 mm |
| Maximum stripping length | 7 mm |
| Length of insulation sleeve (c) | 10.5 mm |
| Inner dimension of the insulating collar (d) | 4.1 mm |
| Distance between the center and the insulation sleeve (e) | 7.2 mm |
| Inner diameter (f) | 3.7 mm |
| Material thickness (g) | 0.75 mm |

General

| | |
|--|--------------|
| Color | red |
| Stripping length | 7 mm |
| Components | halogen-free |
| Flammability rating according to UL 94 | V2 |

Fork-type cable lug - C-FCI 1,5/M3,5 - 3240033

Technical data

General

| | |
|---------------------|------------|
| Material | Copper |
| Insulating material | PA |
| Coating | tin-plated |

Standards and Regulations


| | |
|--|----|
| Flammability rating according to UL 94 | V2 |
|--|----|

Environmental Product Compliance

| | |
|------------|---|
| China RoHS | Environmentally friendly use period: unlimited = EFUP-e |
| | No hazardous substances above threshold values |

Drawings

Dimensional drawing



Classifications

eCl@ss

| | |
|---------------|----------|
| eCl@ss 10.0.1 | 27400204 |
|---------------|----------|

Fork-type cable lug - C-FCI 1,5/M3,5 - 3240033

Classifications

eCl@ss

| | |
|------------|----------|
| eCl@ss 4.0 | 27060700 |
| eCl@ss 4.1 | 27060700 |
| eCl@ss 5.0 | 27400200 |
| eCl@ss 5.1 | 27400200 |
| eCl@ss 6.0 | 27400200 |
| eCl@ss 7.0 | 27400204 |
| eCl@ss 8.0 | 27400204 |
| eCl@ss 9.0 | 27400204 |

ETIM

| | |
|----------|----------|
| ETIM 2.0 | EC000005 |
| ETIM 3.0 | EC000005 |
| ETIM 4.0 | EC001052 |
| ETIM 5.0 | EC001052 |
| ETIM 6.0 | EC001052 |
| ETIM 7.0 | EC001052 |

UNSPSC

| | |
|---------------|----------|
| UNSPSC 6.01 | 27113201 |
| UNSPSC 7.0901 | 27121703 |
| UNSPSC 11 | 27121703 |
| UNSPSC 12.01 | 27121703 |
| UNSPSC 13.2 | 27121707 |
| UNSPSC 18.0 | 27121707 |
| UNSPSC 19.0 | 27121707 |
| UNSPSC 20.0 | 27121707 |
| UNSPSC 21.0 | 27121707 |

Phoenix Contact 2020 © - all rights reserved
<http://www.phoenixcontact.com>

PHOENIX CONTACT GmbH & Co. KG
Flachsmarktstr. 8
32825 Blomberg
Germany
Tel. +49 5235 300
Fax +49 5235 3 41200
<http://www.phoenixcontact.com>

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Phoenix Contact:](#)

[3240033](#)