# Single-phase, primary switched mode power supply **PM-0124-010-0**



### Advantages

Stabilised and adjustable output voltage
Low stand-by consumption <1 W
Constant current characteristic
DC OK signalling
Parallel operation optien
Push-in terminals
Panel installation on mounting rails
Conform to EN 60335-1

## Applications

Efficient, primary switched mode power supply in slim plastic housing. A powerful and flexible option that's still light and compact. Our real all-rounders, these power supply units are suitable for a highly diverse range of applications in solar, measurement and control technology as well as industrial and building automation. The devices cover the lower and average power requirements from 25 W to 100 W. Versions with 12 V, 24 V, and 48 V are available, enabling a whole range of applications. A version with 3.8 A rated current is available for establishing NEC Class 2 circuits. All power supplies also comply with the EN 60335-1 standard for domestic appliances. The output voltage can be easily set using the rotary potentiometer on the front of the housing. The DIN rail fastening method and push-in connection terminals enable fast and secure mounting.

#### Standards

Primary switched mode power supply to UL 60950, UL 508

Safety: EN 61558-2-16, EN 60950-1, EN 60335-1

EMC: EN 61204-3





UL/CSA 60950 recognised, UL508 listed, Germanischer Lloyd





# Single-phase, primary switched mode power supply **PM-0124-010-0**

PM-0124-010-0		Туре	PM-0124-010-0
		71	I III OIL I OILO O
	30	Input	
100 - 240 Vac		Connections input (direct plug-in technology Push-	max 2,5 mm²
85 - 264 Vac (120 - 373 Vdc)		ln)	
-2.5 %/Vac < 95 Vac	ta	Output	
44 Hz - 66 Hz / 0 Hz	qa	Connections output (direct plug-in technology Push-	max 2,5 mm²
0.43 A (100 Vac) / 0.2 A (240 Vac)	<u> </u>	ln)	
< 30 A, NTC	ici	Signaling	
	lar	Connections signalling (direct plug-in technology	max 2,5 mm <sup>2</sup>
	<u>C</u>	Push-In)	
	Ve	Measures and weights	
6 A, 10 A, 16 A, characteristic B, C	~	Weight Dimension (W x H x D)	0.13 kg 22.5 x 90 x 90.5 mm
20 ms (100 Vac) / 120 ms (230 Vac)			
Varistor			
			*
24 Vdc		3.5	and the second second
23 - 28,5 Vdc			and the second se
1 A			A A A A A A A A A A A A A A A A A A A
1.25 1.4 A (constant current)			
Yes			
Yes			
Yes		45.0	
		22.5	Aller Sizes
			$\checkmark$
86 %			
LED green			
cURus, cULus, GL			
,,			
-25° C +85° C			
-25° C +70° C			
-3 %/K > +50° C			
horizontal for standard rail DIN TH 35			
Natural convection			
0 mm			
50 mm			
IP 20			
II, without PE connection			
PM-0124-010-0			
	0.43 A (100 Vac) / 0.2 A (240 Vac) < 30 A, NTC 2.3 s (100 Vac) / 0.74 s (230 Vac) 0.48 2 A 6 A, 10 A, 16 A, characteristic B, C 20 ms (100 Vac) / 120 ms (230 Vac) Varistor 24 Vdc 23 - 28,5 Vdc 1 A 1.25 14 A (constant current) Yes Yes Yes < 1 W / 4 W (230 Vac) 5 W (100 Vac / 24 V / 1 A) typ. 20 mVss 35 Vdc max 39 Vdc 86 % - - LED green Lout > typ. 21.5 Vdc LED lit permanently Active high signal Lout > typ. 21.5 Vdc max 20 mA@24 Vdc short circuit proof cURus, cULus, GL -25° C +85° C -25° C +70° C -3 %/K > +50° C horizontal for standard rail DIN TH 35 Natural convection 0 mm 50 mm	0.43 A (100 Vac) / 0.2 A (240 Vac)    < 30 A, NTC	U43 A100 Vecl / U2 A 1220 Vecl   23 s 100 Vecl / 0.74 s 1230 Vecl   0.48   2A   6A 10 A 16 A   characteristic B, C   20 million (100 Vecl / 120 ms 1230 Vecl)   Varistor   24 Vdc   23 - 28,5 Vdc   1A   125 _ 14 A (constant current)   Yes

