

COMPLIANT

# 12.5 mm Modular Panel Potentiometer **High Dielectric Strength**



# **FEATURES**

- High dielectric strength potentiometer up to 5000 V<sub>RMS</sub>
- 12.5 mm square single turn panel control
- · Plastic shaft and bushing
- Two shaft lengths and 29 terminal styles
- P11P: Cermet element
- P11D: Conductive plastic element
- Multiple assemblies up to seven modules
- Test according to CECC 41000 or IEC 60393-1
- Shaft and panel sealed version
- Up to twenty-one indent positions
- · Rotary switch options
- · Custom designs on request
- Compliant to RoHS Directive 2002/95/EC

4.65

(0.183)


**VERSATILE MODULAR** COMPACT **ROBUST** 

#### **CONFIGURATION EXAMPLE** - Dimensions in mm (inches) $\pm 0.5$ mm ( $\pm 0.02$ ") Single module, single shaft, solder lugs, imperial bushing and shaft 9.5 (0.374) 12.5 8 (0.315) Ø 6.35 (Ø 0.25) 1.8 (0.071)12.5 (0.492) 5.5

Single module, single shaft, vertical mounting, PC pins with support plate, imperial bushing and shaft


0.9 (0.035)

**DETAIL A** 



22.2


(0.874)




(0.183)

Single module, single shaft, solder lugs, imperial bushing and shaft

(0.278)





For technical questions, contact: sfer@vishay.com Document Number: 51059 See also Application Note: <a href="https://www.vishay.com/doc?51001">www.vishay.com/doc?52029</a> and <a href="https://www.vishay.com/doc?51001">www.vishay.com/doc?51001</a> and <a href="https://www.vishay.com/doc?51001">www.vishay.com/doc?52029</a> Revision: 21-Feb-11



# Vishay Sfernice

#### **GENERAL SPECIFICATIONS**

ELECTRICAL (initial)				
		P11D	P11P	
Resistive Element		Conductive plastic Cermet		
Electrical Travel		270° ± 10° 270° ± 10°		
Resistance Range (1)	Linear Taper	1 k $\Omega$ to 1 M $\Omega$	20 $\Omega$ to 10 M $\Omega$	
	Non-Linear Taper	470 Ω to 500 kΩ	100 Ω to 2.2 MΩ	
Tolerance	Standard	± 20 %	± 20 %	
	On Request	<u>-</u>	± 5 % or ± 10 %	
Taper	L  50 % al travel 270 °C trical travel switch 238° cal travel 300 °C			
Circuit Diagram		$ \begin{array}{c} a \\ \bigcirc \\ (1) \end{array} $ $ \begin{array}{c} c \\ \bigcirc \\ b \\ \longrightarrow \\ cw \end{array} $ $ \begin{array}{c} c \\ (3) \end{array} $ $ \begin{array}{c} c \\ (3) \end{array} $		
Linear Taper		0.5 W at + 70 °C	1 W at + 70 °C	
	Non-Linear Taper	0.25 W at + 70 °C	0.5 W at + 70 °C	
	Multiple Assemblies	0.25 W at + 70 °C per module	0.5 W at + 70 °C per module	
Power Rating at 70 °C		1.25 P11P Linear Taper 0.5 P11P Non-Linear Taper 0.25 P11D Non-Linear Taper 0 10 20 30 40 50	60 70 80 90 100 110 120 130 Ambient Temperature (°C)	
Temperature Coefficient, - 40 °C to + 100 °C (Typical)		± 500 ppm	± 150 ppm	
Limiting Element Voltage		350 V	350 V	
End Resistance (Typical)		2 Ω	2 Ω	
Contact Resistance Variation	Linear Taper	1 %	2 % or 3 Ω	
Independent Linearity (Typical)	Linear Taper	± 5 %	± 5 %	
Insulation Resistance		$10^6\mathrm{M}\Omega$ min.	$10^6$ M $\Omega$ min.	
Dialogtria Strongth	Leads to Support Plate	3000 V <sub>RMS</sub> min.	3000 V <sub>RMS</sub> min.	
Dielectric Strength  Leads to Shaft and Bushing			5000 V <sub>RMS</sub> min.	
	Leads to Shaft and Bushing	5000 V <sub>RMS</sub> min.	5000 V <sub>RMS</sub> min.	

<sup>(1)</sup> Consult Vishay Sfernice for other ohmic values

# 12.5 mm Modular Panel Potentiometer High Dielectric Strength



MECHANICAL (initial)						
Mechanical Travel	300° ± 5°					
Operating Torque (Typical)						
Single and Dual Assemblies	0.2 Ncm to 1 Ncm max. (0.3 ozinch to 1.4 ozinch max.)					
Three to Seven Modules (Per Module)	0.2 Ncm to 0.3 Ncm max. (0.3 ozinch to 0.45 ozinch max.)					
End Stop Torque	80 Ncm max. (6.8 lb-inch max.)					
Tightening Torque	150 Ncm max. (13 lb-inch max.)					
Weight						
Single Assemblies	3.5 g					
Two to Seven Modules (Per Module)	1.5 g to 2 g (0.25 oz. to 0.32 oz.)					

ENVIRONMENTAL							
	P11D	P11P					
Operating Temperature Range	- 40 °C to + 100 °C	- 40 °C to + 100 °C					
Climatic Category	40/100/21	40/100/56					
Sealing	IP64	IP64					
Storage Temperature	- 40 °C to + 100 °C	- 40 °C to + 100 °C					

#### **MARKING**

#### • Potentiometer Module

Vishay logo, nominal ohmic value  $(\Omega, k\Omega, M\Omega)$ , two stars identify P11D version, tolerance in % - variation law, manufacturing date (four digits), "3" for the lead 3

#### • Switch Module

Version, manufacturing date (four digits), "c" for common lead

#### • Indent Module


Version, manufacturing date (four digits)

# PACKAGING • Box

PERFORMANCES									
TESTS	CONDITIONS	TYPICAL VALUE AND DRIFTS							
12313	CONDITIONS		P11D	P11P					
Electrical Endurance	1000 h at rated power 90'/30' - ambient temp. 70 °C	$\Delta R_{\rm T}/R_{\rm T}$ Contact resistance variation	± 10 % ± 5 %	± 2 % ± 4 %					
Change of Temperature	- 40 °C to + 100 °C, 5 cycles	± 0.5 %	± 0.2 %						
Damp Heat, Steady State	p Heat, Steady State + 40 °C, 93 % relative humidity P11P: 56 days, P11D: 21 days		± 5 % > 10 MΩ	± 2 % > 1000 MΩ					
Mechanical Endurance	50 000 cycles	$\Delta R_{\rm T}/R_{\rm T}$ Contact resistance variation	± 6 % ± 4 %	± 5 % ± 5 %					
Climatic Sequence	cold - 55 °C/damp neat, 5 cycles		-	± 1 %					
Shock			± 0.2 % ± 0.5 %	± 0.2 % ± 0.5 %					
Vibration	10 Hz to 55 Hz 0.75 mm or 10 g's, 6 h	$\Delta R_{T}/R_{T} \ \Delta V_{1-2}/V_{1-3}$	± 0.2 % ± 0.5 %	± 0.2 % ± 0.5 %					




Vishay Sfernice





			P11P C		P11A CONDUCTIVE PLASTIC				
STANDARD		LINEAR TAPI	ER	NC	ON-LINEAR TA	APER		ER	
RESISTANCE VALUES	MAX. POWER AT 70 °C	MAX. WORKING VOLTAGE	MAX. CUR. THROUGH WIPER	MAX. POWER AT 70 °C	MAX. WORKING VOLTAGE	MAX. CUR. THROUGH WIPER	MAX. POWER AT 70 °C	MAX. WORKING VOLTAGE	MAX. CUR THROUGH WIPER
Ω	W	V	mA	W	V	mA	W	V	mA
22	1	4.69	213						
47	1	6.85	146						
50	1	7.07	141						
100	1	10	100	0.5	7.1	70.7			
200	1	14.8	67.4	0.5	10.0	50.0			
470	1	21.6	46.1	0.5	15.3	32.7			
500	1	22.4	44.7	0.5	15.8	31.6			
1K	1	31.6	31.6	0.5	22.4	22.4	0.5	22.4	22.4
2.2K	1	46.9	21.3	0.5	33.2	15.1	0.5	33.2	15.1
4.7K	1	63.5	14.5	0.5	48.5	10.3	0.5	48.5	10.3
5K	1	70.7	14.1	0.5	50.0	10.0	0.5	50.0	10.0
10K	1	100	10	0.5	79.7	7.07	0.5	79.7	7.07
22K	1	148	6.7	0.5	105	4.77	0.5	105	4.77
47K	1	217	4.6	0.5	153	3.26	0.5	153	3.26
50K	1	224	4.47	0.5	158	3.16	0.5	158	3.16
100K	1	316	3.16	0.5	224	2.24	0.5	224	2.24
220K	0.56	350	1.59	0.5	332	1.51	0.5	332	1.51
470K	0.26	350	0.75	0.26	350	0.74	0.26	350	0.74
500K	0.25	350	0.70	0.25	350	0.70	0.25	350	0.70
1M	0.12	350	0.35	0.12	350	0.35	0.12	350	0.35
2.2M	0.05	350	0.16	0.05	350	0.07			
4.7M	0.02	350	0.07						

# 12.5 mm Modular Panel Potentiometer High Dielectric Strength










#### Note

• Hardware supplied in separate bags




Vishay Sfernice



#### **LOCATING PEGS** (Anti-Rotation Lug)

The locating peg is provided by a plate mounted on the bushing and positioned by the module sides. Four set positions are available, clock face orientation: 12, 3, 6, 9.

Bushings have a double flat. When panel mounting holes have been punched accordingly, an anti-rotation lug is not necessary.



CODE	Ø d L (mm)		EFFECTIVE HIGH PEG	
Α	2	6.2	0.7	
В	2	7.75	0.7	
С	3.5	13.5	1.1	


# PANEL AND SHAFT SEALED O ring plate can not be used with locating pegs


#### Note

• Locating pegs and panel o ring are supplied in separate bags with nuts and washers

# 12.5 mm Modular Panel Potentiometer High Dielectric Strength










Vishay Sfernice



	FIRST DIGIT							
Υ	Soldering lugs							
	PCB pins							
Z	PCB pins with front support plate							

PCB pins with front and back support plates
 PCB pins - vertical mounting with 2 extra pins - 1 module only

SECOND DIGIT
Y = 4.65 (0.183")
A V 7 M F 00 (0 00011) -:

**0** A, X, Z, W = 5.08 (0.200") pin spacing pins section 0.9 x 0.3 (0.035" x 0.012")


1 2.54 (0.100") pin spacing pin section 0.6 x 0.3 (0.024" x 0.012")

2 5.08 (0.200") pin spacing pins section 0.6 x 0.3 (0.024" x 0.012")

#### THIRD DIGIT


0	5.08 (0.200") space between modules
3	7.62 (0.300") space between modules

10.16 (0.400") space between modules



# 12.5 mm Modular Panel Potentiometer High Dielectric Strength





#### **SPECIAL CODES GIVEN BY VISHAY**

Option available:

- Custom design on request
- Specific linearity
- · Specific interlinerarity
- · Specific taper
- Multiple assemblies with various modules



# Vishay Sfernice

#### **P11 OPTION: ROTARY SWITCH MODULES**



- · Rotary switchs
- Current up to 2 A
- · Actuation CW or CCW position
- Sealing IP60

# MODULES: RS ON/OFF SWITCH RSI CHANGEOVER SWITCH

The position of each module is free.

RS and RSI rotary switches are housed in a standard P11 module size 12.7 mm x 12.7 mm x 5.08 mm (0.5" x 0.5" x 0.2"). They have the same terminal styles as the assembled electrical modules.

An assembly can comprise 1 or more switch modules.

Switch actuation is described as seen from the shaft end. D:means actuation in maximum CCW position F:means actuation in maximum CW position

The switch actuation travel is 25° with a total mechanical travel of  $300^{\circ} \pm 5^{\circ}$  and electrical travel of electrical modules is  $238^{\circ} \pm 10^{\circ}$ .

Leads finish: Gold plated.

#### RDS SINGLE POLE SWITCH, NORMALLY OPEN

In full CCW position, the contact between 1 and 3 is open. It is made at the beginning of the travel in CW direction.

#### RSF SINGLE POLE SWITCH, NORMALLY OPEN

In full CW position, the contact between 1 and 3 is open. It is made at the beginning of the travel in CCW direction.

#### **RSID SINGLE POLE CHANGEOVER**

In full CCW position, the contact is made between 3 and 2 and open between 3 and 1. Switch actuation (CW direction) reverses these positions.

#### **RSIF SINGLE POLE CHANGEOVER**

In full CW position, the contact is made between 1 and 2 and open between 1 and 3. Switch actuation (CCW direction) reverses these positions.

SWITCH SPE	SWITCH SPECIFICATIONS								
Switching Pov	62.5 VA v 15 VA =								
Switching Cur	0.25 A 250 V v 0.5 A 30 V =								
Maximum Cu	2 A								
Contact Resis	100 mΩ								
Dielectric Strength	Terminal to Terminal	1000 V <sub>RMS</sub>							
	Terminal to Bushing	5000 V <sub>RMS</sub>							
Maximum Vol	250 V v 30 V =								
Insulation Res	$10^6\mathrm{M}\Omega$								
Life at P <sub>max.</sub>	10 000 actuations								
Minimal Trave	l	25°							
Operating Ter	nperature	- 40 °C to + 85 °C							

#### **ELECTRICAL DIAGRAM**

Note

Common

RSD RSID RSIF
RSF CCW POSITION CW POSITION







ORDERING INFORMATION (First order only)

RSID

**RSIF** 

RSD SPST: Single pole, open switch in CCW position - 2 pins
RSF SPST: Single pole, open switch in CW position - 2 pins
RSID SPDT: Single pole, changeover switch in CCW position - 3 pins

SPDT: Single pole, changeover switch in CW position - 3 pins

Document Number: 51059

Revision: 21-Feb-11

For technical questions, contact: <a href="mailto:sfer@vishay.com/doc?51001">sfer@vishay.com/doc?51001</a> and <a href="mailto:www.vishay.com/doc?51001">www.vishay.com/doc?51001</a> and <a href="mailto:www.vishay.com/doc?51001">www.vishay.com/doc?51001</a> and <a href="mailto:www.vishay.com/doc?52029">www.vishay.com/doc?51001</a> and <a href="mailto:www.vishay.com/doc?52029">www.vishay.com/doc?51001</a> and <a href="mailto:www.vishay.com/doc?52029">www.vishay.com/doc?51001</a> and <a href="mailto:www.vishay.com/doc?51001">www.vishay.com/doc?51001</a> and <a href="mailto:www.vishay.com/doc.">www.vishay.com/doc?51001</a> and <a href="mailto:www.vishay.com/doc.">www.vishay.com/doc.</a> and <a href="mailto:www.vishay.com/doc.">www.vishay.com/doc.</a> and <a href="mailto:www.vishay.com/doc.">www.vishay.com/doc.</a> and <a href="mailto:www.vishay.com/doc.">www.vishay.com/doc.</a> and <a href="mailto:www.vishay.com/doc.">www.vishay.com/doc.</a>

# 12.5 mm Modular Panel Potentiometer High Dielectric Strength



#### **P11 OPTION: DETENT MODULES**


The detents mechanism is housed in a standard P11 module. Up to 21 detent positions available.

Count detents as follows: 1 for CCW position, 1 for full CW position, plus the other positions forming equal resistance

increments (linear taper) - not equal angles. Available: CVID - CVIF - CVIM

CV3 - CV11 - CV21

Mechanical endurance: 10 000 cycles



ORDERING INFORMATION (First order only for special code creation)

#### CV1M

CV1M 1 detent at half travel

CV1M J84 CV1M with accuracy of center point  $\pm$  2 % (all tapers except S)

CV1D 1 detent at CCW position
CV1F 1 detent at CW position

CV3 3 detents CV11 11 detents CV21 21 detents

#### **P11 OPTION: NEUTRAL MODULES "EN"**

Neutral or screen module is housed in a standard P11 module.

It is used as a screen between two electrical modules.

The leads can be connected to ground.

ORDERING INFORMATION (First order only for special code creation)


EN


**EN** Neutral module


#### P11 OPTION: CENTER CURRENT TAP "J"

The extra terminal is a solder lug connected at 50 % of electrical travel and siluated in the potentiometer module opposite the terminals.

Center tap presents a short circuit of 11° of travel.









• Sealing IP60

**ORDERING INFORMATION** (First order only)


J

J Center tap



# Vishay Sfernice

#### **P11 OPTION: SPECIAL LINEARITY - CONFORMITY**



The independent linearity (conformity for the non linear laws) is the maximum gap  $\Delta V$  between the actual variation curve and the theorical variation curve the nearest to it. The linearity and the conformity are expressed in percentage of the total applied voltage E

linearity conformity = 
$$\frac{\pm \Delta V_{max.}}{E}$$

They are measured over 90 % of actual electrical travel (centered).

On request linearity can be guaranteed in linear law.


#### **ORDERING INFORMATION** (First order only)

J123

J123 Independent linearity  $\pm$  3 % (linear taper)
J145 Independent linearity  $\pm$  2 % (linear taper)

For other request, contact us.

#### P11 OPTION: SPECIAL INTERLINEARITY - INTERCONFORMITY



It is the maximum deviation between the actual voltage outputs of 2 or more pot modules in the same assembly. It is expressed as a percentage of the total applied voltage, or in dB attenuation.

Interlinearity is measured between 2 pot modules, over 10 to 90 % of the attenuation.

The interlinearity or interconformity is expressed as a percentage of the total applied voltage:

Or in decibels by comparison between outputs V1 and V2

$$I dB = 20 log \frac{V_1}{V_2}$$

#### **ORDERING INFORMATION** (First order only)


J44

J44 Interlinearity ± 2 % (linear taper)

For other request, contact us.

# 12.5 mm Modular Panel Potentiometer High Dielectric Strength





PART	PART NUMBER DESCRIPTION (used on some Vishay document or label, for information only)											
P11P	3	F	0	GG	S	Y00	10K	20 %	Α			e3
MODEL	MODULES	BUSHING	OPTION	SHAFT	SHAFT STYLE	LEADS	VALUE	TOL.	TAPER	SPECIAL	SPECIAL	LEAD (Pb)-FREE





Vishay

# **Disclaimer**

ALL PRODUCT, PRODUCT SPECIFICATIONS AND DATA ARE SUBJECT TO CHANGE WITHOUT NOTICE TO IMPROVE RELIABILITY, FUNCTION OR DESIGN OR OTHERWISE.

Vishay Intertechnology, Inc., its affiliates, agents, and employees, and all persons acting on its or their behalf (collectively, "Vishay"), disclaim any and all liability for any errors, inaccuracies or incompleteness contained in any datasheet or in any other disclosure relating to any product.

Vishay makes no warranty, representation or guarantee regarding the suitability of the products for any particular purpose or the continuing production of any product. To the maximum extent permitted by applicable law, Vishay disclaims (i) any and all liability arising out of the application or use of any product, (ii) any and all liability, including without limitation special, consequential or incidental damages, and (iii) any and all implied warranties, including warranties of fitness for particular purpose, non-infringement and merchantability.

Statements regarding the suitability of products for certain types of applications are based on Vishay's knowledge of typical requirements that are often placed on Vishay products in generic applications. Such statements are not binding statements about the suitability of products for a particular application. It is the customer's responsibility to validate that a particular product with the properties described in the product specification is suitable for use in a particular application. Parameters provided in datasheets and/or specifications may vary in different applications and performance may vary over time. All operating parameters, including typical parameters, must be validated for each customer application by the customer's technical experts. Product specifications do not expand or otherwise modify Vishay's terms and conditions of purchase, including but not limited to the warranty expressed therein.

Except as expressly indicated in writing, Vishay products are not designed for use in medical, life-saving, or life-sustaining applications or for any other application in which the failure of the Vishay product could result in personal injury or death. Customers using or selling Vishay products not expressly indicated for use in such applications do so at their own risk and agree to fully indemnify and hold Vishay and its distributors harmless from and against any and all claims, liabilities, expenses and damages arising or resulting in connection with such use or sale, including attorneys fees, even if such claim alleges that Vishay or its distributor was negligent regarding the design or manufacture of the part. Please contact authorized Vishay personnel to obtain written terms and conditions regarding products designed for such applications.

No license, express or implied, by estoppel or otherwise, to any intellectual property rights is granted by this document or by any conduct of Vishay. Product names and markings noted herein may be trademarks of their respective owners.

Document Number: 91000 www.vishay.com Revision: 11-Mar-11