

SN55173, SN65173, SN75173 QUADRUPLE DIFFERENTIAL LINE RECEIVERS

SLLS144E – OCTOBER 1980 – REVISED APRIL 2000


- Meet or Exceed the Requirements of TIA/EIA-422-B, TIA/EIA-423-B, and TIA/EIA-485-A and ITU Recommendations V.10, V.11, X.26, and X.27
- Designed for Multipoint Bus Transmission on Long Bus Lines in Noisy Environments
- 3-State Outputs
- Common-Mode Input Voltage Range of -12 V to 12 V
- Input Sensitivity . . . $\pm 200\text{ mV}$
- Input Hysteresis . . . 50 mV Typ
- High Input Impedance . . . $12\text{ k}\Omega\text{ Min}$
- Operate From Single 5-V Supply
- Low Power Requirements
- Pin-to-Pin Replacement for AM26LS32

description


The SN55173, SN65173, and SN75173 are monolithic quadruple differential line receivers with 3-state outputs. They are designed to meet the requirements of TIA/EIA-422-B, TIA/EIA-423-B, TIA/EIA-485-A, and several ITU recommendations. The standards are for balanced multipoint bus transmission at rates up to 10 megabits per second. The four receivers share two OR enable inputs, one active when high, the other active when low. These devices feature high input impedance, input hysteresis for increased noise immunity, and input sensitivity of $\pm 200\text{ mV}$ over a common-mode input voltage range of -12 V to 12 V . Fail-safe design specifies that if the inputs are open circuited, the outputs are always high. The SN65173 and SN75173 are designed for optimum performance when used with the SN75172 or SN75174 quad differential line drivers.

The SN55173 is characterized over the full military temperature range of -55°C to 125°C . The SN65173 is characterized for operation from -40°C to 85°C . The SN75173 is characterized for operation from 0°C to 70°C .

SN55173 . . . J PACKAGE
SN65173, SN75173 . . . D OR N PACKAGE
(TOP VIEW)



SN55173 . . . FK PACKAGE
(TOP VIEW)



NC—No internal connection

**THE SN55173 IS NOT RECOMMENDED
FOR NEW DESIGNS.**



Please be aware that an important notice concerning availability, standard warranty, and use in critical applications of Texas Instruments semiconductor products and disclaimers thereto appears at the end of this data sheet.

PRODUCTION DATA information is current as of publication date. Products conform to specifications per the terms of Texas Instruments standard warranty. Production processing does not necessarily include testing of all parameters.

**TEXAS
INSTRUMENTS**

POST OFFICE BOX 655303 • DALLAS, TEXAS 75265

Copyright © 2000, Texas Instruments Incorporated

SN55173, SN65173, SN75173 QUADRUPLE DIFFERENTIAL LINE RECEIVERS

SLLS144E – OCTOBER 1980 – REVISED APRIL 2000

AVAILABLE OPTIONS

| T _A | PACKAGED DEVICES | | | |
|----------------|---------------------------|---------------------------|-----------------|-----------------|
| | PLASTIC SMALL OUTLINE (D) | PLASTIC CHIP CARRIER (FK) | CERAMIC DIP (J) | PLASTIC DIP (N) |
| 0°C to 70°C | SN75173D | — | — | SN75173N |
| –40°C to 85°C | SN65173D | — | — | SN65173N |
| –55°C to 125°C | — | SN55173FK | SN55173J | — |


The D package is available taped and reeled. Add the suffix R to the device type (e.g., SN75173DR).

FUNCTION TABLE (each receiver)

| DIFFERENTIAL A–B | ENABLES | | OUTPUT Y |
|---------------------------|---------|-----------|----------|
| | G | \bar{G} | |
| $V_{ID} \geq 0.2 V$ | H | X | H |
| | X | L | H |
| $-0.2 V < V_{ID} < 0.2 V$ | H | X | ? |
| | X | L | ? |
| $V_{ID} \leq -0.2 V$ | H | X | L |
| | X | L | L |
| X | L | H | Z |
| Open circuit | X | L | H |
| | H | X | H |

H = high level, L = low level, ? = indeterminate, X = irrelevant, Z = high impedance (off)

logic symbol †




† This symbol is in accordance with ANSI/IEEE Std 91-1984 and IEC Publication 617-12. Pin numbers shown are for the D, J, and N packages.

SN55173, SN65173, SN75173 QUADRUPLE DIFFERENTIAL LINE RECEIVERS


SLLS144E – OCTOBER 1980 – REVISED APRIL 2000

logic diagram (positive logic)



Pin numbers shown are for the D, J, and N packages.

schematics of inputs and outputs



SN55173, SN65173, SN75173 QUADRUPLE DIFFERENTIAL LINE RECEIVERS

SLLS144E – OCTOBER 1980 – REVISED APRIL 2000

absolute maximum ratings over operating free-air temperature range (unless otherwise noted)†

| | |
|--|------------------------------|
| Supply voltage, V_{CC} (see Note 1) | 7 V |
| Input voltage (V_I or B inputs) | ± 25 V |
| Differential input voltage, V_{ID} (see Note 2) | ± 25 V |
| Enable input voltage, V_I | 7 V |
| Low-level output current, I_{OL} | 50 mA |
| Package thermal impedance, θ_{JA} (see Note 3): D package | 73°C/W |
| N package | 67°C/W |
| Continuous total dissipation | See Dissipation Rating Table |
| Case temperature for 60 seconds, T_C : FK package | 260°C |
| Lead temperature 1,6 mm (1/16 inch) from case for 10 seconds: D or N package | 260°C |
| Lead temperature 1,6 mm (1/16 inch) from case for 60 seconds: J package | 300°C |
| Storage temperature range, T_{stg} | -65°C to 150°C |

† Stresses beyond those listed under “absolute maximum ratings” may cause permanent damage to the device. These are stress ratings only, and functional operation of the device at these or any other conditions beyond those indicated under “recommended operating conditions” is not implied. Exposure to absolute-maximum-rated conditions for extended periods may affect device reliability.

- NOTES: 1. All voltage values, except differential input voltage, are with respect to network ground terminal.
 2. Differential input voltage is measured at the noninverting input with respect to the corresponding inverting input.
 3. The package thermal impedance is calculated in accordance with JESD 51.

DISSIPATION RATING TABLE

| PACKAGE | $T_A \leq 25^\circ\text{C}$ POWER RATING | DERATING FACTOR | $T_A = 70^\circ\text{C}$ POWER RATING | $T_A = 125^\circ\text{C}$ POWER RATING |
|---------|---|--------------------|--|---|
| FK | 1375 mW | 11 mW/°C | 880 mW | 275 mW |
| J | 1375 mW | 11 mW/°C | 880 mW | 275 mW |

recommended operating conditions

| | | MIN | NOM | MAX | UNIT |
|---|------------------|------|-----|----------|---------------|
| Supply voltage, V_{CC} | SN55173 | 4.5 | 5 | 5.5 | V |
| | SN65173, SN75173 | 4.75 | 5 | 5.25 | V |
| Common-mode input voltage, V_{IC} | | | | ± 12 | V |
| Differential input voltage, V_{ID} | | | | ± 12 | V |
| High-level enable-input voltage, V_{IH} | | 2 | | | V |
| Low-level enable-input voltage, V_{IL} | | | | 0.8 | V |
| High-level output current, I_{OH} | | | | -400 | μA |
| Low-level output current, I_{OL} | | | | 16 | mA |
| Operating free-air temperature, T_A | SN55173 | -55 | | 125 | °C |
| | SN65173 | -40 | | 85 | |
| | SN75173 | 0 | | 70 | |



SN55173, SN65173, SN75173 QUADRUPLE DIFFERENTIAL LINE RECEIVERS

SLLS144E – OCTOBER 1980 – REVISED APRIL 2000

electrical characteristics over recommended ranges of common-mode input voltage, supply voltage, and operating free-air temperature

| PARAMETER | | TEST CONDITIONS | | MIN | TYP† | MAX | UNIT |
|-----------|--|--------------------------------------|------------------------------------|-------------------------|------|----------|---------------|
| V_{IT+} | Positive-going input threshold voltage | $V_O = 2.7\text{ V}$, | $I_O = -0.4\text{ mA}$ | | | 0.2 | V |
| V_{IT-} | Negative-going input threshold voltage | $V_O = 0.5\text{ V}$, | $I_O = 16\text{ mA}$ | -0.2‡ | | | V |
| V_{hys} | Hysteresis ($V_{IT+} - V_{IT-}$) | See Figure 4 | | | 50 | | mV |
| V_{IK} | Enable-input clamp voltage | $I_I = -18\text{ mA}$ | | | | -1.5 | V |
| V_{OH} | High-level output voltage | $V_{ID} = 200\text{ mV}$, | $I_{OH} = -400\text{ }\mu\text{A}$ | SN55173 | | 2.5 | V |
| | | | | SN65173, SN75173 | | 2.7 | V |
| V_{OL} | Low-level output voltage | $V_{ID} = -200\text{ mV}$, | See Figure 1 | $I_{OL} = 8\text{ mA}$ | | 0.45 | V |
| | | | | $I_{OL} = 16\text{ mA}$ | | 0.5 | |
| I_{OZ} | High-impedance-state output current | $V_O = 0.4\text{ V to }2.4\text{ V}$ | | | | ± 20 | μA |
| I_I | Line input current | Other input at 0 V, | See Note 3 | $V_I = 12\text{ V}$ | | 1 | mA |
| | | | | $V_I = -7\text{ V}$ | | -0.8 | |
| I_{IH} | High-level enable-input current | $V_{IH} = 2.7\text{ V}$ | | | | 20 | μA |
| I_{IL} | Low-level enable-input current | $V_{IL} = 0.4\text{ V}$ | | | | -100 | μA |
| r_i | Input resistance | | | | 12 | | k Ω |
| I_{OS} | Short-circuit output current | | | -15 | | -85 | mA |
| I_{CC} | Supply current | Outputs disabled | | | | 70 | mA |

† All typical values are at $V_{CC} = 5\text{ V}$, $T_A = 25^\circ\text{C}$.

‡ The algebraic convention, in which the less positive (more negative) limit is designated as minimum, is used in this data sheet for threshold voltage levels only.

NOTE 3: Refer to TIA/EIA-422-B and TIA/EIA-423-B for exact conditions.

switching characteristics, $V_{CC} = 5\text{ V}$, $T_A = 25^\circ\text{C}$



| PARAMETER | | TEST CONDITIONS | | MIN | TYP | MAX | UNIT |
|-----------|--|--|--------------|-----|-----|-----|------|
| t_{PLH} | Propagation delay time, low-to-high-level output | $V_{ID} = -1.5\text{ V to }1.5\text{ V}$, | | | 20 | 35 | ns |
| t_{PHL} | Propagation delay time, high-to-low-level output | $C_L = 15\text{ pF}$, | See Figure 1 | | 22 | 35 | ns |
| t_{PZH} | Output enable time to high level | $C_L = 15\text{ pF}$, | See Figure 2 | | 17 | 22 | ns |
| t_{PZL} | Output enable time to low level | $C_L = 15\text{ pF}$, | See Figure 3 | | 20 | 25 | ns |
| t_{PHZ} | Output disable time from high level | $C_L = 5\text{ pF}$, | See Figure 2 | | 21 | 30 | ns |
| t_{PLZ} | Output disable time from low level | $C_L = 5\text{ pF}$, | See Figure 3 | | 30 | 40 | ns |



SN55173, SN65173, SN75173 QUADRUPLE DIFFERENTIAL LINE RECEIVERS

SLLS144E – OCTOBER 1980 – REVISED APRIL 2000

PARAMETER MEASUREMENT INFORMATION





† Voltage for the SN55173 only.

NOTES: A. C_L includes probe and jig capacitance.

B. The input pulse is supplied by a generator having the following characteristics: PRR = 1 MHz, duty cycle = 50%, $t_r \leq 6$ ns, $t_f \leq 6$ ns, $Z_0 = 50 \Omega$.

Figure 1. t_{PLH} , t_{PHL} Test Circuit and Voltage Waveforms



† Voltage for the SN55173 only.

NOTES: A. C_L includes probe and jig capacitance.


B. The input pulse is supplied by a generator having the following characteristics: PRR = 1 MHz, duty cycle = 50%, $t_r \leq 6$ ns, $t_f \leq 6$ ns, $Z_0 = 50 \Omega$.

C. All diodes are 1N916, or equivalent.

D. To test the active-low enable \overline{G} , ground G and apply an inverted input waveform to \overline{G} .

Figure 2. t_{PHZ} , t_{PZH} Test Circuit and Voltage Waveforms

PARAMETER MEASUREMENT INFORMATION



- NOTES: A. C_L includes probe and jig capacitance.
 B. The input pulse is supplied by a generator having the following characteristics: PRR = 1 MHz, duty cycle = 50%, $t_r \leq 6$ ns, $t_f \leq 6$ ns, $Z_O = 50 \Omega$.
 C. All diodes are 1N916, or equivalent.
 D. To test the active-low enable \overline{G} , ground G and apply an inverted input waveform to \overline{G} .

Figure 3. t_{pZL} , t_{pLZ} Test Circuit and Voltage Waveforms

SN55173, SN65173, SN75173 QUADRUPLE DIFFERENTIAL LINE RECEIVERS

SLLS144E – OCTOBER 1980 – REVISED APRIL 2000

TYPICAL CHARACTERISTICS†




Figure 4




Figure 5

† Operation of the device at these or any other conditions beyond those indicated under "recommended operating conditions" is not implied.

TYPICAL CHARACTERISTICS†




Figure 6




Figure 7




Figure 8




Figure 9

† Operation of the device at these or any other conditions beyond those indicated under "recommended operating conditions" is not implied.

SN55173, SN65173, SN75173 QUADRUPLE DIFFERENTIAL LINE RECEIVERS

SLLS144E – OCTOBER 1980 – REVISED APRIL 2000

TYPICAL CHARACTERISTICS




Figure 10





Figure 11

APPLICATION INFORMATION



NOTE A: The line should be terminated at both ends in its characteristic impedance. Stub lengths off the main line should be kept as short as possible.

Figure 12. Typical Application Circuit

IMPORTANT NOTICE

Texas Instruments and its subsidiaries (TI) reserve the right to make changes to their products or to discontinue any product or service without notice, and advise customers to obtain the latest version of relevant information to verify, before placing orders, that information being relied on is current and complete. All products are sold subject to the terms and conditions of sale supplied at the time of order acknowledgment, including those pertaining to warranty, patent infringement, and limitation of liability.

TI warrants performance of its semiconductor products to the specifications applicable at the time of sale in accordance with TI's standard warranty. Testing and other quality control techniques are utilized to the extent TI deems necessary to support this warranty. Specific testing of all parameters of each device is not necessarily performed, except those mandated by government requirements.

Customers are responsible for their applications using TI components.

In order to minimize risks associated with the customer's applications, adequate design and operating safeguards must be provided by the customer to minimize inherent or procedural hazards.

TI assumes no liability for applications assistance or customer product design. TI does not warrant or represent that any license, either express or implied, is granted under any patent right, copyright, mask work right, or other intellectual property right of TI covering or relating to any combination, machine, or process in which such semiconductor products or services might be or are used. TI's publication of information regarding any third party's products or services does not constitute TI's approval, warranty or endorsement thereof.