

July 2008

FDP032N08

N-Channel PowerTrench® MOSFET **75V**, **235A**, **3.2m**Ω

Features

- $R_{DS(on)} = 2.5 m\Omega$ (Typ.)@ $V_{GS} = 10 V$, $I_{D} = 75 A$
- · Fast switching speed
- · Low gate charge
- High performance trench technology for extremely low R_{DS(on)}
- · High power and current handling capability
- · RoHS compliant

Description

This N-Channel MOSFET is produced using Fairchild Semiconductor's adcanced PowerTrench process that has been especially tailored to minimize the on-state resistance and yet maintain superior switching performance.

Application

• DC to DC convertors / Synchronous Rectification







MOSFET Maximum Ratings T_C = 25°C unless otherwise noted*

Symbol		Parameter		FDP032N08	Units
V _{DSS}	Drain to Source Voltage		75	V	
V _{GSS}	Gate to Source Voltage	Gate to Source Voltage			V
	Drain Current	- Continuous (T _C = 25°C, Sili	con Limited)	235*	Α
I _D		- Continuous (T _C = 100°C, Sil	icon Limited)	165*	А
		- Continuous (T _C = 25°C, Pa	ckage Limited)	120	Α
I _{DM}	Drain Current	- Pulsed (Note 1)		940	Α
E _{AS}	Single Pulsed Avalanche Energy (Note 2)		(Note 2)	1995	mJ
dv/dt	Peak Diode Recovery dv	/dt	(Note 3)	5.5	V/ns
<u> </u>	Dawan Diagination	$(T_C = 25^{\circ}C)$		375	W
P_{D}	Power Dissipation	- Derate above 25°C		2.5	W/°C
T _J , T _{STG}	Operating and Storage Temperature Range			-55 to +175	°С
T _L	Maximum Lead Temperature for Soldering Purpose, 1/8" from Case for 5 Seconds			300	°C

*Calculated continuous current based on maximum allowable junction temperature. Package limitation current is 120A.

Thermal Characteristics

Symbol	Parameter	Ratings	Units
$R_{\theta JC}$	Thermal Resistance, Junction to Case	0.4	
$R_{\theta CS}$	Thermal Resistance, Case to Sink Typ.	0.5	°C/W
$R_{\theta JA}$	Thermal Resistance, Junction to Ambient	62.5	

Package Marking and Ordering Information $T_C = 25^{\circ}C$ unless otherwise noted

Device Marking	Device	Package	Reel Size	Tape Width	Quantity
FDP032N08	FDP032N08	TO-220	=	=	50

Electrical Characteristics

Symbol	Parameter	Test Conditions	Min.	Тур.	Max.	Units
Off Charac	cteristics					
BV _{DSS}	Drain to Source Breakdown Voltage	$I_D = 250 \mu A$, $V_{GS} = 0 V$, $T_C = 25 ^{\circ} C$	75	-	-	V
$\frac{\Delta BV_{DSS}}{\Delta T_J}$	Breakdown Voltage Temperature Coefficient	$I_D = 250\mu\text{A}$, Referenced to 25°C	=	0.05	-	V/°C
1	Zero Gate Voltage Drain Current	$V_{DS} = 75V, V_{GS} = 0V$	-	-	1	^
IDSS	Zero Gate Voltage Drain Current	$V_{DS} = 75V, T_{C} = 150^{\circ}C$	-	-	500	μΑ
I _{GSS}	Gate to Body Leakage Current	$V_{GS} = \pm 20V, V_{DS} = 0V$	-	-	±100	nA

On Characteristics

V _{GS(th)}	Gate Threshold Voltage	$V_{GS} = V_{DS}$, $I_D = 250\mu A$	2.5	3.5	4.5	V
R _{DS(on)}	Static Drain to Source On Resistance	$V_{GS} = 10V, I_D = 75A$	ı	2.5	3.2	mΩ
g _{FS}	Forward Transconductance	$V_{DS} = 10V, I_D = 75A$ (Note 4)	ı	180	-	S

Dynamic Characteristics

C _{iss}	Input Capacitance	V 05V V 0V		11400	15160	pF
C _{oss}	Output Capacitance	$V_{DS} = 25V, V_{GS} = 0V$ f = 1MHz	-	1360	1810	pF
C _{rss}	Reverse Transfer Capacitance	1 - 11/11/2	ı	595	800	pF
Q _{g(tot)}	Total Gate Charge at 10V		-	169	220	nC
Q_{gs}	Gate to Source Gate Charge	$V_{DS} = 60V, I_{D} = 75A$	-	60	-	nC
Q _{gd}	Gate to Drain "Miller" Charge	V _{GS} = 10V (Note 4, 5)	-	47	-	nC

Switching Characteristics

t _{d(on)}	Turn-On Delay Time		-	230	470	ns
t _r	Turn-On Rise Time	$V_{DD} = 37.5V, I_{D} = 75A$	-	191	392	ns
t _{d(off)}	Turn-Off Delay Time	$R_{GEN} = 25\Omega, V_{GS} = 10V$	-	335	680	ns
t _f	Turn-Off Fall Time	(Note 4, 5)	-	121	252	ns

Drain-Source Diode Characteristics

Is	Maximum Continuous Drain to Source Diode Forward Current			=	-	235	Α
I _{SM}	Maximum Pulsed Drain to Source Diode Forward Current			-	-	940	Α
V_{SD}	Drain to Source Diode Forward Voltage	$V_{GS} = 0V$, $I_{SD} = 75A$		-	-	1.3	V
t _{rr}	Reverse Recovery Time	V _{GS} = 0V, I _{SD} = 75A		=	53	-	ns
Q _{rr}	Reverse Recovery Charge	$dI_F/dt = 100A/\mu s$	(Note 4)	-	77	-	nC

Notes:

- Repetitive Rating: Pulse width limited by maximum junction temperature
- 2. L = 0.71mH, I_{AS} = 75A, V_{DD} = 50V, R_{G} = 25 Ω , Starting T_{J} = 25°C
- 3. $I_{SD} \le 75 A$, $di/dt \le 200 A/\mu s$, $V_{DD} \le BV_{DSS}$, Starting $T_J = 25^{\circ}C$
- 4. Pulse Test: Pulse width $\leq 300 \mu s, \, \text{Duty Cycle} \leq 2\%$
- 5. Essentially Independent of Operating Temperature Typical Characteristics

Typical Performance Characteristics

Figure 1. On-Region Characteristics




Figure 3. On-Resistance Variation vs.

Drain Current and Gate Voltage




Figure 5. Capacitance Characteristics




Figure 2. Transfer Characteristics




Figure 4. Body Diode Forward Voltage Variation vs. Source Current and Temperature





Figure 6. Gate Charge Characteristics



FDP032N08 Rev. A3 www.fairchildsemi.com

Typical Performance Characteristics (Continued)

Figure 7. Breakdown Voltage Variation vs. Temperature




Figure 9. Maximum Safe Operating Area




Figure 8. On-Resistance Variation vs.

Temperature

Figure 10. Maximum Drain Current vs. Case Temperature

50


T_J, Junction Temperature [°C]

100

150

200

0








Figure 11. Transient Thermal Response Curve

0.0


-100




Gate Charge Test Circuit & Waveform




Resistive Switching Test Circuit & Waveforms





Unclamped Inductive Switching Test Circuit & Waveforms





Peak Diode Recovery dv/dt Test Circuit & Waveforms







Forward Voltage Drop

Mechanical Dimensions

TO-220











TRADEMARKS

The following includes registered and unregistered trademarks and service marks, owned by Fairchild Semiconductor and/or its global subsidianries, and is not intended to be an exhaustive list of all such trademarks.

Build it Now™ CorePLUS™ CorePOWER™

 $CROSSVOLT^{\text{TM}}$ CTL™

Current Transfer Logic™ EcoSPARK®

EfficentMax™ EZSWITCH™ *

Fairchild® Fairchild Semiconductor®

FACT Quiet Series™ **FACT** FAST®

FastvCore™ FlashWriter® * **FPS™** F-PFS™ FRFFT®

Global Power ResourceSM

Green FPS™ Green FPS™ e-Series™

GTO™ IntelliMAX™ ISOPLANAR™ MegaBuck™

MICROCOUPLER™ MicroFFT™ MicroPak™ MillerDrive™

MotionMax™ Motion-SPM™ OPTOLOGIC® OPTOPLANAR® PDP SPM™ Power-SPM™ PowerTrench®

Programmable Active Droop™

QFET® QS™ Quiet Series™

RapidConfigure™ Saving our world, 1mW at a time™

SmartMax™ SMART START™

SPM®

STEALTH™ SuperFET™ SuperSOT™-3 SuperSOT™-6 SuperSOT™-8 SupreMOS™ SyncFET™

SYSTEM ®

The Power Franchise®

p wer franchise TinyBoost™ TinyBuck™ TinyLogic[®] TINYOPTO™ TinyPower™ TinyPWM™ Tinẏ́Wire™

UHC® Ultra FRFET™ UniFFT™ VCX™

VisualMax™

* EZSWITCH™ and FlashWriter® are trademarks of System General Corporation, used under license by Fairchild Semiconductor.

DISCLAIMER

FAIRCHILD SEMICONDUCTOR RESERVES THE RIGHT TO MAKE CHANGES WITHOUT FURTHER NOTICE TO ANY PRODUCTS HEREIN TO IMPROVE RELIABILITY, FUNCTION, OR DESIGN. FAIRCHILD DOES NOT ASSUME ANY LIABILITY ARISING OUT OF THE APPLICATION OR USE OF ANY PRODUCT OR CIRCUIT DESCRIBED HEREIN; NEITHER DOES IT CONVEY ANY LICENSE UNDER ITS PATENT RIGHTS, NOR THE RIGHTS OF OTHERS. THESE SPECIFICATIONS DO NOT EXPAND THE TERMS OF FAIRCHILD'S WORLDWIDE TERMS AND CONDITIONS, SPECIFICALLY THE WARRANTY THEREIN, WHICH COVERS THESE PRODUCTS.

LIFE SUPPORT POLICY

FAIRCHILD'S PRODUCTS ARE NOT AUTHORIZED FOR USE AS CRITICAL COMPONENTS IN LIFE SUPPORT DEVICES OR SYSTEMS WITHOUT THE EXPRESS WRITTEN APPROVAL OF FAIRCHILD SEMICONDUCTOR CORPORATION.

- Life support devices or systems are devices or systems which, (a) are intended for surgical implant into the body or (b) support or sustain life, and (c) whose failure to perform when properly used in accordance with instructions for use provided in the labeling, can be reasonably expected to result in a significant injury of the user.
- A critical component in any component of a life support, device, or system whose failure to perform can be reasonably expected to cause the failure of the life support device or system, or to affect its safety or effectiveness.

ANTI-COUNTERFEITING POLICY

Fairchild Semiconductor Corporation's Anti-Counterfeiting Policy. Farichild's Anti-Counterfeiting Policy is also stated on our external website, www.fairchildsemi.com, under Sales Support.

Counterfeiting of semiconductor parts is a growing problem in the industry. All manufactures of semiconductor products are experiencing counterfeiting of their parts. Customers who inadvertently purchase counterfeit parts experience many problems such as loss of brand reputation, substandard performance, failed application, and increased cost of production and manufacturing delays. Fairchild is taking strong measures to protect ourselves and our customers from the proliferation of counterfeit parts. Farichild strongly encourages customers to purchase Farichild parts either directly from Fairchild or from Authorized Fairchild Distributors who are listed by country on our web page cited above. Products customers buy either from fairchild directly or from Authorized Fairchild Distributors are genuine parts, have full traceability, meet Fairchild's quality standards for handing and storage and provide access to Fairchild's full range of up-to-date technical and product information. Fairchild and our Authorized Distributors will stand behind all warranties and will appropriately address and warranty issues that may arise. Fairchild will not provide any warranty coverage or other assistance for parts bought from Unauthorized Sources. Farichild is committed to committed to combat this global problem and encourage our customers to do their part in stopping this practice by buying direct or from authorized distributors

PRODUCT STATUS DEFINITIONS **Definition of Terms**

Datasheet Identification	Product Status	Definition				
dvance Information Formative / In Design		Datasheet contains the design specifications for product development. Specifications may change in any manner without notice.				
Preliminary	First Production	Datasheet contains preliminary data; supplementary data will be published at a later date. Fairchild Semiconductor reserves the right to make changes at any time without notice to improve design.				
No Identification Needed	Full Production	Datasheet contains final specifications. Fairchild Semiconductor reserves the right to make changes at any time without notice to improve the design.				
Obsolete Not In Production		Datasheet contains specifications on a product that is discontinued by Fairchild Semiconductor. The datasheet is for reference information only.				