



Pos.	Dimension		
	A	B	C
06	15.70	12.80	5.08
08	17.78	15.48	7.62
10	20.30	18.10	10.16
12	22.84	20.64	12.70
14	25.38	23.18	15.24
16	27.92	25.72	17.78
20	33.00	30.80	22.86
24	38.08	35.88	27.94
26	40.62	38.72	30.48
30	45.70	43.50	35.56
34	50.80	48.58	40.64
40	58.40	56.20	48.26
44	63.48	61.28	53.34
50	71.12	68.90	60.96
60	83.80	81.60	73.66
64	88.88	86.68	78.74

Material

- Insulator: PBT
 - Flammability: UL94V-0
 - Color: Black
 - Contacts: Brass
 - Plating termination: Gold Flash
- contact OST for other plating availability, may require MOQ

Ratings

- Current: 3A
- Contact Resistance: <20mΩ at DC 100mA
- Insulation Resistance: >5,000MΩ at DC 500V
- Dielectric Withstanding Voltage: 500V for one minute
- Operating Temperature: -40°C ±105°C
- Solderability: 180°C for 3~5 seconds
- Durability: 500 mating cycles

RoHS Compliant

PART NUMBER:

302-SXX1

Number of circuits

Dim. D

- 3.20 - leave blank (standard)
 - 2.80 - add 2.8 to end of p/n
- may require MOQ

OST ON-SHORE TECHNOLOGY, INC.
302 Series - 2.54mm Dual Row Vertical Box Header

TITLE	302 Series - 2.54mm Dual Row Vertical Box Header	
PART NO.	302-SXX1	DWG NO. 302-SXX1.DWG
APPROVED	CHECKED	DESIGNED
Marvin 2009.02.26	Marvin 2009.02.26	Marvin 2009.02.26
		DRAWN
		1200
		UNIT: mm
		SCALE: NONE
		Tolerance
		X.X ±0.20
		X.XX ±0.10
		SHEET: 01/01
		REV.: C

THESE DRAWINGS AND SPECIFICATIONS ARE THE PROPERTY OF ON-SHORE TECHNOLOGY, INC. AND SHALL NOT BE REPRODUCED, COPIED OR USED IN ANY MANNER WITHOUT THE PRIOR WRITTEN CONSENT OF ON-SHORE TECHNOLOGY, INC.

Recommended P.C.B Layout

