



Search within category GO

BUY NOW

DESIGN / INSTALL



FTD75-8-D

Polypropylene insulated ferrules – twin wire white DIN end sleeve, 22 AWG (0.5mm²), 0.31" (8.0mm) pin length.

Specs	Packaging Details	Tools	Documents	★ Add to Favorites	🛒 Add to BOM
Pin Length In. (mm)	0.31 (8)				
Style	Twin Wire				
Wire Range In. (mm ²)	20 AWG (0.5)				
Barrel Type	Seamless				
Base Material	Copper				
Insulation	Polypropylene				
Panduit Color Code	White				
Plating Type	Tinned				
Part Number Series	FTD				
Length In (mm)	0.59 (15)				
Max. Insulation Diameter In. (mm)	0.87 (2.2)				
Wire Strip Length In. (mm)	7/16" (.4375) - (11.2mm)				
Flammability Rating	HB				
Temperature Rating	221 Degrees Fahrenheit (105 Degrees Celsius)				
Tool	CT-1002, CT-1003, CT-1123				
CSA Certified	C22.2 No. 291-14				
Standards	DIN 46228 Part 1, UL 486F Listed, UL 508A Certified				
Packaging Type	Bag				
Pieces Per Reel	-				
Inside Diameter (In.)	0.06				
Inside Diameter (mm)	1.5				
Part Features	<ul style="list-style-type: none"> • Twin Wire Polypropylene insulation housing conforms to DIN color requirements • Meets DIN, UL and CSA standards for single wire containment • Funnel entry for faster insertion and lower installed cost • Designed with a seamless barrel to contain loose wire strands for superior terminations • Eases insertion of wire into terminal block • Suitable for limited space panel applications • Multiple pin lengths available for a variety of terminal blocks 				
Wire Range	20 AWG				
RoHS Compliancy Status	Compliant				
Min. Order Qty.	500.0000				