


## 1565894-1 Product Details

### Have a Question?

Chat with a Product Information Specialist



**1565894-1**

TE Internal Number: 1565894-1

Active

View 3D PDF

### 0.025 Series and Hybrid Connectors and Contacts

Always EU RoHS/ELV Compliant ([Statement of Compliance](#))

#### Product Highlights:

- Connector
- Housing
- Connector Style = Receptacle
- Contact Type = Pin
- Receptacle Configuration = 025

[View all Features](#)

#### Quick Links

- ▶ [Check Pricing & Availability](#)
- ▶ [Search for Tooling](#)
- ▶ [Product Feature Selector](#)
- ▶ [Contact Us About This Product](#)

Add to My Part List Request Sample Find Similar Products Buy Product

### Documentation & Additional Information

#### Product Drawings:

- [025 SERIES CONNECTOR 12POSITION CAP HOUSING ASSEMBLY](#) (PDF, Japanese)

#### Catalog Pages/Data Sheets:

- None Available

#### Product Specifications:

- [.025 IDC Connectors \(1\)](#) (PDF, Japanese)
- [.025 IDC Connectors \(2\)](#) (PDF, Japanese)
- [025 SERIES I/O CONNECTORS \(H-Type V-Type 2Row, W... \(1\)](#) (PDF, Japanese)
- [025 SERIES I/O CONNECTORS \(H-Type V-Type 2Row, W... \(2\)](#) (PDF, Japanese)

#### Application Specifications:

- [.025 IDC Connectors](#) (PDF, Japanese)
- [Crimping of 025 Tab Contact](#) (PDF, Japanese)

#### Instruction Sheets:

- [025 WIRE TO WIRE MALE CONNECTOR \(1\)](#) (PDF, Japanese)
- [025 WIRE TO WIRE MALE CONNECTOR \(2\)](#) (PDF, Japanese)

#### CAD Files: ([CAD Format & Compression Information](#))

- [2D Drawing](#) (DXF, Version B)
- [3D Model](#) (IGES, Version B)
- [3D Model](#) (STEP, Version B)

#### Additional Information:

- [Product Line Information](#)

#### Related Products:

- [Tooling](#)

[List all Documents](#)

### Product Features (Please use the Product Drawing for all design activity)

#### Product Type Features:

- [Product Type](#) = Connector
- [Connector Type](#) = Housing
- [Receptacle Configuration](#) = 025
- [Mount](#) = Free Hanging

#### Body Related Features:

- [Number of Positions](#) = 12
- [Wire Range/Signal \(mm<sup>2</sup>\)](#) = 0.08, 0.22, CAVS/CAVUS 0.22-0.5, AVSS/AVSSH-f 0.3-0.5

#### Contact Related Features:

- [Contact Type](#) = Pin

#### Housing Related Features:

- [Connector Style](#) = Receptacle
- [Housing Material](#) = PBT - GF
- [Housing Color](#) = Natural

#### Industry Standards:

- [RoHS/ELV Compliance](#) = RoHS compliant, ELV compliant
- [Lead Free Solder Processes](#) = Not relevant for lead free process
- [RoHS/ELV Compliance History](#) = Always was RoHS compliant

#### Conditions for Usage:

- [Applies To](#) = Wire

#### Packaging Related Features:

- [Packaging Method](#) = Paper Box, Plastic Bag

#### Other:

- [Brand](#) = AMP

BOOKMARK

#### Corporate Information

[Who We Are](#)  
[Investors](#)  
[News Room](#)  
[Supplier Portal](#)  
[Careers](#)

#### Quick Links

[Check Distributor Inventory](#)  
[Cross Reference](#)  
[Find Documents & Drawings](#)  
[Product Compliance Support Center](#)  
[Site Map](#)

#### Customer Support

[Email or Chat with Us](#)  
[Find a Phone Number](#)  
[Search Knowledge Base](#)  
[Manage Your Account](#)

#### Sign up for our eNewsletter

Enter your email address

#### Follow Us On:



#### Visit Us On:

