

DC-to-DC Converter Control Circuits

DESCRIPTION

The MC33063 series is a monolithic control circuit containing primary functions required for DC-to-DC converters.


These devices consist of an internal temperature-compensated reference, comparator, controlled duty cycle oscillator with an active current limit circuit, driver and high current output switch. This series was specifically designed to be incorporated in step-down and step-up and voltage-inverting applications with a minimum number of external components.


ORDERING INFORMATION

DEVICE	Package Type	MARKING	Packing	Packing Qty
MC33063N	DIP8	MC33063	TUBE	2000/box
MC33063M/TR	SOP8	MC33063	REEL	2500/reel


FEATURES

- Operation from 3.0V to 40V input •
- Low standby current
- Current limiting
- Output switch current up to 1.5A
- Adjustable output voltage
- Operation at frequencies up to 100kHz
- Precision reference (2%)





PIN CONNECTIONS





l_{pk} Sense

Comparator

Inverting Input

 $V_{\rm CC}$

ABSOLUTE MAXIMUM RATINGS


Rating	Symbol	Value	Unit
Power supply voltage	V _{cc}	40	V
Comparator input voltage range	V _{IR}	-0.3 to +40	V
Switch collector voltage	V _{C(Switch)}	40	V
Switch emitter voltage (V _{Pin1} =40V)	V _{E(Switch)}	40	V
Switch collector-to-emitter voltage	V _{CE(Switch)}	40	V
Driver collector voltage	V _{C(Driver)}	40	V
Driver collector current (Note 1)	I _{C(Driver)}	100	mA
Switch current	I _{Sw}	1.5	Α
Operating junction temperature	TJ	+150	°C
Operating ambient temperature range	T _A	-40 to +85	°C
Storage temperature range	T _{STG}	-65 to + 150	°C
ESD (HBM)		2500	V

ELECTRICAL CHARACTERISTICS (V _{cc} =5.0V, Characteristics	Symbol	Min	Тур	Max	Unit
OSCILLATOR	e jiiikei			max	•
Frequency (V _{Pin5} =0V, C _T =1.0nF, T _A =25°C)	f _{osc}	24	33	42	kHz
Charge current ($V_{CC}=5.0V$ to 40V, $T_A=25^{\circ}C$)	I _{chg}	24	35	42	μA
Discharge current $(V_{CC}=5.0V \text{ to } 40V, T_A=25^{\circ}C)$	I _{dischg}	140	220	260	μA
Discharge-to-charge current ratio (Pin7 to V_{CC} , $T_A=25^{\circ}C$)	I _{dischg} /I _{chg}	5.2	6.5	7.5	-
Current limit sense voltage $(I_{chg}=I_{dischg}, T_A=25^{\circ}C)$	V _{Ipk(sense)}	250	300	350	mV
OUTPUT SWITCH (Note 2)				•	
Saturation voltage, Darlington connection I_{Sw} =1.0A, Pins1, 8 connected	V _{CE(sat)}	-	1.0	1.3	V
Saturation voltage, Darlington connection (I_{Sw} =1.0A, R_{Pin8} =82 Ω to V _{CC} , forced β =20)	V _{CE(sat)}	-	0.45	0.7	V
DC current gain (I_{Sw} =1.0A, V _{CE} =5.0, T _A =25°C)	h _{FE}	50	75	-	-
Collector off-state current (V _{CE} =40V)	I _{C(off)}	-	1.0	100	μA
COMPARATOR					
Threshold voltage	V _{th}	1.225 1.21	1.25 -	1.275 1.29	V
Threshold voltage line regulation (V _{CC} =3.0V to 40V)	Reg _{line}	-	1.4	5.0	mV
Input bias current (V _{in} =0V)	I _{IB}	-	-20	-400	nA
TOTAL DEVICE	·····				
Supply current (V_{CC} =5.0V to 40V, C_T =1.0nF, Pin7= V_{CC} , V_{Pin5} > V_{th} , Pin2=Gnd, remaining pins - open	Icc	-	-	4.0	mA

Notes:

Maximum package power dissipation limits must be observed.
Low duty cycle pulse techniques are used during the test to maintain the junction temperature as close to the ambient temperature as possible.





TYPICAL PERFORMANCE CHARACTERISTICS



APPLICATION INFORMATION





Fig.2. External current boost connections for I_{C Peak} greater than 1.5A2a. External NPN switch2b. External NPN saturated switch









Fig.3. Step-down Converter

Fig.4. External current boost connections for I_{C Peak} greater than 1.5A4a. External NPN switch4b. External PNP saturated switch









Fig.5. Voltage inverting converter

Fig.6. External current boost connections for $I_{C Peak}$ greater than 1.5A

6a. External NPN switch

6b. External PNP saturated switch





Calculation	Step-up	Step-down	Voltage-inverting
t _{on}	$\frac{V_{out} + V_F - V_{in(min)}}{V_{in(min)} - V_{sat}}$	$\frac{V_{out} + V_F}{V_{in(min)} - V_{sat} - V_{out}}$	$\frac{\left V_{out}\right + V_{F}}{V_{in} + V_{sat}}$
$(t_{on} + t_{off})$ max	$\frac{1}{f_{min}}$	$\frac{1}{f_{\min}}$	$\frac{1}{f_{min}}$
CT	4.0 x 10 ⁻⁵ t _{on}	$4.0 \times 10^{-5} t_{on}$	4.0 x 10 ⁻⁵ t _{on}
I _{pk(switch)}	$2I_{out(max)}\left(\frac{t_{on}}{t_{off}}+1\right)$	$2I_{out(max)}$	$2I_{out(max)}\left(\frac{t_{on}}{t_{off}}+1\right)$
R _{sc}	0.3/I _{pk(Switch)}	0.3/I _{pk(Switch)}	0.3/I _{pk(Switch)}
$L_{(min)}$	$\left(\frac{V_{in(min)} - V_{sat}}{I_{pk(switch)}}\right) \times t_{on(max)}$	$\left(\frac{V_{in(min)} - V_{sat} - V_{out}}{I_{pk(switch)}}\right) \times t_{on(max)}$	$\left(\frac{V_{in(min)} - V_{sat}}{I_{pk(switch)}}\right) \times t_{on(max)}$
Co	$9rac{I_{out}t_{on}}{V_{ripple(pp)}}$	$\frac{I_{pk(switch)}(t_{on} + t_{off})}{8V_{ripple(pp)}}$	$9rac{I_{out}t_{on}}{V_{ripple(pp)}}$

DESIGN FORMULA

TERMS AND DEFINITIONS

V_{sat} – Saturation voltage of the output switch.

 V_{F} - Forward voltage drop of the output rectifier.

The following power supply characteristics must be chosen:

Vin – Nominal input voltage.

 V_{out} – Desired output voltage, $|V_{out}| = 1.25 \left(1 + \frac{R_2}{R_1} \right)$


f_{min} – Minimum desired output switching frequency at the selected values of V_{in} and I_{out}.

*V*_{*ripple(p-p)} – Desired peak-to-peak output ripple voltage.* In practice, the calculated capacitor value will need to be increased due to its equivalent series resistance and board layout. The ripple voltage should be kept to a low value since it will directly affect the line and load regulation.</sub>



MC33063

PACKAGE





Important statement:

Huaguan Semiconductor Co,Ltd. reserves the right to change the products and services provided without notice. Customers should obtain the latest relevant information before ordering, and verify the timeliness and accuracy of this information.

Customers are responsible for complying with safety standards and taking safety measures when using our products for system design and machine manufacturing to avoid potential risks that may result in personal injury or property damage.

Our products are not licensed for applications in life support, military, aerospace, etc., so we do not bear the consequences of the application of these products in these fields.

Our documentation is only permitted to be copied without any tampering with the content, so we do not accept any responsibility or liability for the altered documents.