

Specifications	Range	
Model	UT302C	
Temperature Range	-32°C~650°C	
	-26°F~1202°F	
Accuracy	±1.8°C or ±1.8%	
Repeatability	±0.5°C or ±0.5%	
Resolution	0.1°C/0.1°F	
Distance to Spot Size		20:01
Response Time	250ms (95% of reading)	
Emissivity	0.10~1.0 Adjustable	
Laser Type	Class 2 (II)	
Laser Power	<1mW	
Laser Wavelength	630nm ~670nm	
Spectral Response	8μm~14μm	
Features		
°C/°F Selections	√	
Laser switch	√	
Display Hold (s)	8 seconds	
Auto Power Off	√	
Low Battery Indication	√	

MAX Mode	√
MIN Mode	√
DIFF Mode	√
AVG Mode	√
LCD Backlight	√
Electricity Cut-off Memory	√
Tripod Mount	√

General Characteristics

Power 9V battery (6F22)

LCD Size 32mm X 29mm

Product Color Red and grey

Product Net Weight 322g

Product Size 169mm X 138mm X 53mm

Standard Accessories Battery

Standard Individual
Packing Blister, English Manual,
Carrying Bag

Standard Quantity Per
Carton 20pcs

Standard Carton
Measurement 605×360×468mm (0.101 CBM
Per Standard Carton)

Standard Carton Gross Weight 12.4kg