

# CMF23V-473111

### **Description:**

The CMF23 Series provides exceptional common-mode suppression and exceptional stray inductance to suppress differential-mode noise. In effect, the CMF23 Series combines the features of two separate components into one.

## **Construction:**

Constructed with UL rated 130°C (Class B) materials.


#### Electrical Specifications (@20°C) @ 10kHz

Inductance(1)	Lstray typ	Amps <sub>(2)</sub> (A)	Max. DC (Ω) Resistance
47mH	970uH	1.1	0.884

1. Inductance Tolerance: -30/+50%

- 2. Inductance per winding.
- 3. Operating Temperature: -40 105°C
- 4. Storage Temperature:  $-25^{\circ}C +40^{\circ}C$ ,  $\leq 75\%$  RH
- 5. Rated Voltage: 300VAC (50/60Hz)
- 6. Weight: 18g

## CMF23 Series – Frequency Response Curve



Safety: 2000VAC Dielectric Strength between windings.


RoHS Compliance: As of manufacturing date February 2016, all standard products meet the requirements of 2015/863/EU, known as the RoHS 3 initiative.


\*Upon printing, this document is considered "uncontrolled". Please contact Triad Magnetics website for the most current version. For soldering and washing information please see http://www.triadmagnetics.com


Web: www.TriadMagnetics.com Phone 951-277-0757 Fax 951-277-2757

460 Harley Knox Blvd. Perris, California 92571











Publish Date: April 17, 2019